

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P489626

Luminaire Tested: **CLM-24-4-INS-A19156-LD4-2LO-30-120-EDD-90**

Issue Date: 3/11/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P489626
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-115-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/11/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: CLM-24-4-INS-A19156-LD4-2LO-30-120-EDD-90
Description: 2X4 CLM LED LUMINAIRE WITH A19156 LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4488.1 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.21 / 1.34
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 46.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P489626

CATALOG NUMBER: CLM-24-4-INS-A19156-LD4-2LO-30-120-EDD-90

Luminous Intensity Polar Plot





TEST NUMBER: P489626

CATALOG NUMBER: CLM-24-4-INS-A19156-LD4-2LO-30-120-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	51
5	77	64	55	48	75	63	54	48	61	53	48	59	52	47	57	51	47	45
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41	39
7	66	52	44	38	64	51	43	37	50	43	37	49	42	37	47	41	37	35
8	61	48	39	34	60	47	39	33	46	38	33	45	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2297	2297	2297
5°	2276	2297	2283
10°	2255	2278	2267
15°	2224	2260	2244
20°	2189	2241	2214
25°	2146	2208	2183
30°	2103	2174	2154
35°	2055	2137	2117
40°	2002	2094	2067
45°	1946	2044	2005
50°	1887	1979	1927
55°	1819	1904	1845
60°	1741	1813	1757
65°	1641	1704	1642
70°	1510	1571	1493
75°	1330	1390	1310
80°	1080	1127	1068
85°	752	801	783



TEST NUMBER: P489626

CATALOG NUMBER: CLM-24-4-INS-A19156-LD4-2LO-30-120-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	3.6
10°-20°	455.6	10.2
20°-30°	679.5	15.1
30°-40°	805.2	17.9
40°-50°	814.8	18.2
50°-60°	711.6	15.9
60°-70°	520.0	11.6
70°-80°	276.7	6.2
80°-90°	63.9	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1295.9	28.9
0°-40°	2101.1	46.8
0°-60°	3627.5	80.8
0°-90°	4488.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4488.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1707	1707	1707	1707	1707	
5°	1685	1688	1701	1705	1690	160
15°	1596	1607	1622	1632	1611	450
25°	1446	1463	1488	1493	1470	666
35°	1251	1271	1301	1310	1289	783
45°	1022	1041	1074	1075	1054	789
55°	775	791	812	800	787	693
65°	515	526	535	524	516	510
75°	256	262	267	258	252	272
85°	49	50	52	52	51	62
90°	0	0	0	0	0	



TEST NUMBER: P489626

CATALOG NUMBER: CLM-24-4-INS-A19156-LD4-2LO-30-120-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1707.1	1707.1	1707.1	1707.1	1707.1
2.5°	1693.8	1699.3	1705.0	1707.5	1693.6
5°	1684.9	1688.1	1700.7	1704.6	1690.2
7.5°	1670.3	1675.1	1687.4	1689.1	1675.3
10°	1650.4	1658.9	1667.1	1676.0	1659.1
12.5°	1624.9	1636.5	1650.4	1652.0	1639.2
15°	1596.3	1607.0	1622.1	1631.9	1610.7
17.5°	1564.3	1574.6	1594.2	1596.0	1583.1
20°	1528.5	1541.3	1564.8	1568.9	1546.0
22.5°	1488.0	1505.2	1524.8	1528.7	1511.8
25°	1445.5	1463.3	1487.5	1493.0	1470.4
27.5°	1401.0	1418.1	1445.3	1449.2	1430.2
30°	1353.3	1369.4	1399.2	1405.8	1386.4
32.5°	1305.0	1321.0	1354.1	1359.6	1340.7
35°	1251.3	1270.8	1300.9	1309.9	1288.8
37.5°	1196.5	1215.5	1249.7	1257.8	1235.1
40°	1139.7	1158.6	1192.2	1199.0	1177.1
42.5°	1081.8	1100.6	1136.5	1137.6	1119.5
45°	1022.5	1040.7	1074.1	1075.0	1053.8
47.5°	962.4	980.7	1010.6	1007.2	987.3
50°	901.6	919.0	945.2	938.4	920.4
52.5°	838.6	855.5	880.2	869.2	852.3
55°	775.3	790.9	811.6	799.8	786.7
57.5°	711.4	727.3	743.1	731.2	719.8
60°	647.1	660.9	673.9	661.8	653.1
62.5°	581.6	593.5	604.7	593.2	585.0
65°	515.4	525.9	535.2	524.5	515.8
67.5°	449.6	458.5	467.1	456.0	447.0
70°	383.8	391.5	399.3	387.9	379.6
72.5°	318.9	325.7	332.6	321.6	314.3
75°	255.8	261.6	267.3	257.5	251.9
77.5°	195.5	200.4	204.4	198.1	192.6
80°	139.4	143.2	145.5	143.0	137.8
82.5°	89.6	92.3	93.6	93.4	90.0
85°	48.7	49.6	51.9	52.5	50.7
87.5°	18.9	20.1	20.6	22.2	20.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)