

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P489760

Luminaire Tested: **CLM-24-4-INS-P12125-LD4-1HI-35-120-EDD-90**

Issue Date: 3/11/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P489760
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P387254)
Test Lab: INNOVATION CENTER
Issue Date: 3/11/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: CLM-24-4-INS-P12125-LD4-1HI-35-120-EDD-90
Description: 2X4 CLM LED LUMINAIRE WITH P12125 LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3826.0 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.04 / 1.23
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 43.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P489760

CATALOG NUMBER: CLM-24-4-INS-P12125-LD4-1HI-35-120-EDD-90

Luminous Intensity Polar Plot





TEST NUMBER: P489760

CATALOG NUMBER: CLM-24-4-INS-P12125-LD4-1HI-35-120-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	70
3	90	80	72	65	88	78	71	65	75	69	64	73	67	62	70	65	61	59
4	83	71	62	55	81	70	61	55	67	60	54	65	59	54	63	57	53	51
5	76	63	54	48	74	62	54	48	60	53	47	58	52	46	56	51	46	44
6	70	57	48	42	68	56	48	42	54	47	41	53	46	41	51	45	40	38
7	65	52	43	37	64	51	43	37	49	42	37	48	41	36	47	41	36	34
8	61	47	39	33	59	47	39	33	45	38	33	44	37	33	43	37	32	30
9	57	43	35	30	55	43	35	30	42	35	30	41	34	29	40	34	29	27
10	53	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2216	2216	2216
5°	2128	2113	2113
10°	1981	1962	1978
15°	1879	1876	1894
20°	1810	1823	1837
25°	1758	1787	1798
30°	1716	1759	1769
35°	1687	1736	1754
40°	1657	1724	1738
45°	1623	1707	1728
50°	1587	1686	1708
55°	1543	1662	1668
60°	1487	1616	1613
65°	1410	1554	1543
70°	1316	1449	1431
75°	1162	1284	1271
80°	944	1046	995
85°	655	667	642



TEST NUMBER: P489760

CATALOG NUMBER: CLM-24-4-INS-P12125-LD4-1HI-35-120-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.5	3.8
10°-20°	381.2	10.0
20°-30°	554.4	14.5
30°-40°	659.7	17.2
40°-50°	685.0	17.9
50°-60°	620.6	16.2
60°-70°	468.3	12.2
70°-80°	255.2	6.7
80°-90°	56.1	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1081.2	28.3
0°-40°	1740.9	45.5
0°-60°	3046.5	79.6
0°-90°	3826.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3826.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1647	1647	1647	1647	1647	
5°	1576	1572	1564	1564	1564	146
15°	1349	1346	1347	1356	1360	381
25°	1184	1194	1204	1214	1211	546
35°	1027	1039	1057	1073	1068	642
45°	853	868	897	907	908	659
55°	658	673	708	713	711	587
65°	443	456	488	487	485	438
75°	224	232	247	249	244	238
85°	42	43	43	43	42	53
90°	0	0	0	0	0	



TEST NUMBER: P489760

CATALOG NUMBER: CLM-24-4-INS-P12125-LD4-1HI-35-120-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1647.2	1647.2	1647.2	1647.2	1647.2
2.5°	1632.7	1631.1	1625.7	1623.7	1623.3
5°	1575.5	1571.8	1564.4	1563.6	1564.4
7.5°	1507.2	1503.1	1495.7	1498.6	1502.3
10°	1449.6	1439.3	1436.4	1440.5	1447.5
12.5°	1398.1	1389.9	1387.4	1398.1	1403.1
15°	1349.1	1345.9	1346.7	1355.8	1359.9
17.5°	1306.8	1304.7	1310.1	1317.1	1319.1
20°	1264.4	1268.5	1273.4	1280.9	1283.3
22.5°	1222.8	1230.6	1238.9	1248.7	1245.4
25°	1184.5	1194.4	1203.9	1213.8	1210.9
27.5°	1143.8	1155.3	1168.5	1179.2	1175.1
30°	1104.7	1119.1	1131.9	1145.0	1138.8
32.5°	1066.0	1079.6	1094.8	1110.9	1103.9
35°	1026.9	1039.2	1056.9	1073.0	1067.7
37.5°	983.7	998.9	1019.1	1033.1	1029.4
40°	943.3	957.3	981.6	990.7	989.8
42.5°	902.6	914.1	939.6	949.9	948.3
45°	852.8	868.0	897.2	907.1	907.9
47.5°	808.8	821.5	852.8	860.6	862.3
50°	758.1	774.2	805.5	814.9	816.2
52.5°	708.3	725.6	757.7	764.3	765.6
55°	657.7	673.3	708.3	713.3	711.2
57.5°	604.6	623.5	655.7	658.1	660.2
60°	552.7	569.2	600.5	603.8	599.3
62.5°	496.4	513.2	545.4	546.2	542.5
65°	442.8	455.6	488.1	487.3	484.8
67.5°	386.9	402.5	426.4	427.2	425.2
70°	334.6	345.3	368.4	368.8	363.8
72.5°	278.2	289.8	308.3	305.8	304.6
75°	223.5	232.5	247.0	248.6	244.5
77.5°	173.3	179.9	190.6	189.3	184.8
80°	121.8	127.2	135.0	133.4	128.4
82.5°	77.8	81.1	86.0	84.0	81.9
85°	42.4	42.8	43.2	42.8	41.6
87.5°	15.6	16.1	16.1	15.6	14.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)