

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P489773

Luminaire Tested: **CLM-24-4-INS-P12125-LD4-1LO-35-120-EDD**

Issue Date: 3/11/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P489773
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P387254)
Test Lab: INNOVATION CENTER
Issue Date: 3/11/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: CLM-24-4-INS-P12125-LD4-1LO-35-120-EDD
Description: 2X4 CLM LED LUMINAIRE WITH P12125 LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2476.8 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.04 / 1.24
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 23.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P489773

CATALOG NUMBER: CLM-24-4-INS-P12125-LD4-1LO-35-120-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P489773

CATALOG NUMBER: CLM-24-4-INS-P12125-LD4-1LO-35-120-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	70
3	90	80	72	65	88	78	71	65	75	69	64	73	67	62	70	65	61	59
4	83	71	62	55	81	70	61	55	67	60	54	65	59	54	63	57	53	51
5	76	63	54	48	74	62	54	48	60	53	47	58	52	46	56	51	46	44
6	70	57	48	42	68	56	48	42	54	47	41	53	46	41	51	45	40	38
7	65	52	43	37	64	51	43	37	49	42	37	48	41	36	47	41	36	34
8	61	47	39	33	59	47	39	33	45	38	33	44	37	33	43	37	32	30
9	57	43	35	30	55	43	35	30	42	35	30	41	34	29	40	34	29	27
10	53	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1435	1435	1435
5°	1378	1368	1368
10°	1282	1270	1280
15°	1217	1214	1226
20°	1172	1180	1190
25°	1138	1157	1164
30°	1111	1138	1145
35°	1092	1124	1135
40°	1073	1116	1126
45°	1051	1105	1118
50°	1027	1091	1106
55°	999	1076	1080
60°	963	1046	1044
65°	913	1006	999
70°	852	938	926
75°	752	831	823
80°	611	677	644
85°	423	432	415



TEST NUMBER: P489773

CATALOG NUMBER: CLM-24-4-INS-P12125-LD4-1LO-35-120-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.2	3.8
10°-20°	246.8	10.0
20°-30°	358.9	14.5
30°-40°	427.1	17.2
40°-50°	443.4	17.9
50°-60°	401.7	16.2
60°-70°	303.1	12.2
70°-80°	165.2	6.7
80°-90°	36.3	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	699.9	28.3
0°-40°	1127.0	45.5
0°-60°	1972.2	79.6
0°-90°	2476.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2476.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1066	1066	1066	1066	1066	
5°	1020	1018	1013	1012	1013	95
15°	873	871	872	878	880	247
25°	767	773	779	786	784	353
35°	665	673	684	695	691	416
45°	552	562	581	587	588	427
55°	426	436	458	462	460	380
65°	287	295	316	316	314	283
75°	145	150	160	161	158	154
85°	27	28	28	28	27	35
90°	0	0	0	0	0	



TEST NUMBER: P489773

CATALOG NUMBER: CLM-24-4-INS-P12125-LD4-1LO-35-120-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1066.3	1066.3	1066.3	1066.3	1066.3
2.5°	1057.0	1055.9	1052.4	1051.1	1050.8
5°	1019.9	1017.5	1012.7	1012.2	1012.7
7.5°	975.7	973.0	968.3	970.1	972.5
10°	938.4	931.7	929.9	932.5	937.1
12.5°	905.1	899.8	898.2	905.1	908.3
15°	873.4	871.3	871.8	877.7	880.3
17.5°	846.0	844.6	848.1	852.6	854.0
20°	818.5	821.2	824.4	829.2	830.8
22.5°	791.6	796.7	802.0	808.4	806.3
25°	766.8	773.2	779.3	785.7	783.9
27.5°	740.4	747.9	756.4	763.4	760.7
30°	715.1	724.4	732.7	741.2	737.2
32.5°	690.1	698.9	708.7	719.1	714.6
35°	664.8	672.8	684.2	694.6	691.2
37.5°	636.8	646.7	659.7	668.8	666.4
40°	610.7	619.7	635.5	641.3	640.8
42.5°	584.3	591.8	608.3	614.9	613.9
45°	552.1	561.9	580.8	587.2	587.8
47.5°	523.6	531.8	552.1	557.1	558.2
50°	490.8	501.2	521.4	527.5	528.4
52.5°	458.5	469.7	490.5	494.8	495.6
55°	425.8	435.9	458.5	461.8	460.4
57.5°	391.4	403.7	424.5	426.0	427.4
60°	357.8	368.5	388.7	390.9	387.9
62.5°	321.3	332.2	353.0	353.6	351.2
65°	286.7	294.9	316.0	315.5	313.9
67.5°	250.4	260.6	276.0	276.6	275.2
70°	216.6	223.5	238.5	238.7	235.5
72.5°	180.1	187.6	199.6	198.0	197.2
75°	144.7	150.5	159.9	160.9	158.3
77.5°	112.2	116.4	123.4	122.6	119.6
80°	78.9	82.3	87.4	86.3	83.1
82.5°	50.3	52.5	55.7	54.4	53.0
85°	27.4	27.7	28.0	27.7	26.9
87.5°	10.1	10.4	10.4	10.1	9.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)