



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Eaton Lighting Division
(formerly Cooper Lighting)

Brand: FAIL-SAFE

Report Number: P212915

Luminaire Tested: **FPS-4-LD4-3HI-50-CLR**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Eaton or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P212915
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35459-R3)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: EATON (FORMERLY COOPER LIGHTING)
Product Line: FAIL-SAFE
Catalog Number: FPS-4-LD4-3HI-50-CLR
Description: FPS 4' LED FIXTURE WITH CLEAR LENS
Light Source: (252) EATON 5000K CCT, 85 CRI LEDS
Ballast/Driver: -

Luminaire Equipment:	<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
	a	good	reflector
	b	good	lens
	c	good	housing
	d	good	cord

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15066.1 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 4.1' x H: 0.33')
IES Classification: Type V - Short - Non-Cutoff
BUG Rating: B3 - U5 - G4


Input Watts (W): 133.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P212915
 CATALOG NUMBER: FPS-4-LD4-3HI-50-CLR

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 - - - 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 4.9 fc
 Type V - Short - Non-Cutoff



REPORT NUMBER: P212915
CATALOG NUMBER: FPS-4-LD4-3HI-50-CLR

Luminous Intensity Polar Plot



— Vertical Plane Through 22.5-Deg Lateral - - - Horizontal Cone Through 15-Deg Vertical



REPORT NUMBER: P212915

CATALOG NUMBER: FPS-4-LD4-3HI-50-CLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6629.4	903.6	7533.0
	% Fixture	44.0	6.0	50.0
Street Side	Lumens	6629.4	903.6	7533.0
	% Fixture	44.0	6.0	50.0
Total	Lumens	13258.8	1807.2	15066.1
	% Fixture	88.0	12.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	298.9	2.0
10°-20°	867.2	5.8
20°-30°	1306.6	8.7
30°-40°	1709.5	11.3
40°-50°	2110.0	14.0
50°-60°	2277.2	15.1
60°-70°	2029.2	13.5
70°-80°	1611.7	10.7
80°-90°	1048.6	7.0
90°-100°	662.0	4.4
100°-110°	490.0	3.3
110°-120°	312.0	2.1
120°-130°	179.3	1.2
130°-140°	93.5	0.6
140°-150°	49.7	0.3
150°-160°	19.8	0.1
160°-170°	0.9	0.0
170°-180°	0.0	0.0
0°-90°	13258.8	88.0
0°-180°	15066.1	100.0





REPORT NUMBER: P212915


CATALOG NUMBER: FPS-4-LD4-3HI-50-CLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1236.3	8.2			
FM	(30°-60°)	3048.4	20.2			
FH	(60°-80°)	1820.4	12.1			G2/5000
FVH	(80°-90°)	524.3	3.5			G4/750
BL	(0°-30°)	1236.3	8.2	B3/2500		
BM	(30°-60°)	3048.4	20.2	B3/5000		
BH	(60°-80°)	1820.4	12.1	B3/2500		G2/5000
BVH	(80°-90°)	524.3	3.5			G4/750
UL	(90°-100°)	662.0	4.4		U4/1000	
UH	(100°-180°)	903.6	6.0		U4/1000	

BUG Rating: B3-U5-G4

Type V Short





REPORT NUMBER: P212915

CATALOG NUMBER: FPS-4-LD4-3HI-50-CLR

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3056.3	3056.3	3056.3	3056.3	3056.3
2.5°	3090.1	3094.2	3076.6	3079.3	3073.9
5°	3100.9	3113.1	3137.4	3152.3	3138.8
7.5°	3117.1	3156.3	3182.0	3138.8	3110.4
10°	3155.0	3217.2	3159.0	3079.3	3053.6
12.5°	3163.1	3241.5	3144.2	3057.7	3099.6
15°	3172.6	3263.1	3105.0	3040.1	2849.5
17.5°	3167.2	3234.7	3130.7	2775.2	2623.8
20°	3155.0	3176.6	3036.0	2610.2	2534.5
22.5°	3100.9	3146.9	2872.5	2603.5	2592.7
25°	3022.5	3040.1	2708.9	2680.5	2671.1
27.5°	2956.3	2942.8	2576.4	2753.5	2771.1
30°	2871.1	2830.6	2577.8	2826.5	2753.5
32.5°	2783.3	2738.7	2562.9	2826.5	2780.6
35°	2685.9	2676.5	2604.8	2857.6	2863.0
37.5°	2565.6	2607.5	2611.6	2925.2	2846.8
40°	2467.0	2517.0	2640.0	2890.0	2887.3
42.5°	2350.7	2425.0	2729.2	3026.6	2980.6
45°	2237.2	2353.4	2819.8	3172.6	2986.0
47.5°	2126.3	2300.7	2949.5	3217.2	2880.6
50°	1980.3	2257.4	3077.9	3186.1	2754.9
52.5°	1857.3	2229.0	3061.7	3076.6	2679.2
55°	1730.2	2172.3	2992.8	2957.6	2576.4
57.5°	1596.4	2088.5	2861.7	2838.7	2360.2
60°	1469.4	1972.2	2677.8	2638.6	2177.7
62.5°	1323.4	1860.0	2533.2	2492.6	2091.2
65°	1169.3	1728.9	2366.9	2422.3	2052.0
67.5°	1030.0	1609.9	2265.5	2377.7	2049.3
70°	880.0	1508.6	2165.5	2266.9	1960.0
72.5°	746.2	1407.2	2006.0	2065.5	1766.7
75°	609.6	1278.8	1811.3	1887.0	1615.3
77.5°	482.6	1135.5	1631.6	1723.5	1488.3
80°	363.6	978.7	1468.0	1564.0	1336.9
82.5°	258.2	859.7	1328.8	1411.2	1209.8
85°	177.1	729.9	1176.0	1292.3	1074.6
87.5°	108.1	625.9	1038.1	1154.4	962.4
90°	70.3	509.6	893.5	1019.2	866.5
92.5°	66.2	443.4	780.0	919.2	773.2
95°	67.6	410.9	725.9	840.8	704.3
97.5°	68.9	381.2	686.7	808.3	673.2
100°	67.6	360.9	669.1	784.0	652.9
102.5°	66.2	332.5	646.1	736.7	611.0
105°	63.5	289.3	598.8	673.2	552.9
107.5°	60.8	259.5	525.8	590.7	492.0
110°	58.1	247.4	467.7	512.3	435.3



REPORT NUMBER: P212915

CATALOG NUMBER: FPS-4-LD4-3HI-50-CLR

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	56.8	233.9	432.6	469.1	400.1
115°	54.1	214.9	400.1	433.9	370.4
117.5°	50.0	191.9	362.3	394.7	337.9
120°	44.6	166.3	325.8	358.2	308.2
122.5°	40.6	141.9	286.6	317.7	278.5
125°	36.5	119.0	248.7	275.8	246.0
127.5°	33.8	96.0	217.6	239.3	219.0
130°	31.1	79.8	190.6	210.9	196.0
132.5°	29.7	67.6	166.3	190.6	179.8
135°	27.0	55.4	144.6	177.1	169.0
137.5°	25.7	46.0	125.7	162.2	158.2
140°	24.3	37.8	109.5	150.0	148.7
142.5°	24.3	29.7	94.6	139.2	139.2
145°	23.0	27.0	82.5	127.1	128.4
147.5°	23.0	25.7	71.6	114.9	117.6
150°	21.6	24.3	59.5	98.7	104.1
152.5°	21.6	24.3	47.3	82.5	87.9
155°	20.3	23.0	33.8	64.9	71.6
157.5°	20.3	21.6	20.3	46.0	51.4
160°	18.9	21.6	14.9	24.3	28.4
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)