

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P550507

Luminaire Tested: **FCC-X-2-LD4-1HI-35-UNV-81-86-ED1D-90**

Issue Date: 7/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P550507
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2105-248-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FCC-X-2-LD4-1HI-35-UNV-81-86-ED1D-90
Description: FCC CORNER MOUNT LUMINAIRE WITH .156 CLEAR PC FIXTURE SIDE AND .250 CLEAR PC ENVIRONMENTAL SIDE LENSES AND 3500K, AND 90 CRI LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1495.0 lumens
Efficiency: N/A
Efficacy: 68.9 lumens/watt
Spacing Criteria (0/90/45): 1.66 / 1.25 / 1.59
Luminous Opening: Rectangular w/ Sides (W: 2' x L: 0.5' x H: 0.25')
CIE Type: Semi-Direct

Input Watts (W): 21.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P550507

CATALOG NUMBER: FCC-X-2-LD4-1HI-35-UNV-81-86-ED1D-90

Luminous Intensity Polar Plot





TEST NUMBER: P550507

CATALOG NUMBER: FCC-X-2-LD4-1HI-35-UNV-81-86-ED1D-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	113	113	113	113	105	105	105	99	99	99	93	93	93	93	93	93	90
1	103	96	91	86	99	93	88	83	87	83	79	81	78	74	76	73	70	76	73	70	67
2	92	82	74	67	88	79	72	65	74	67	62	69	64	59	64	60	56	64	60	56	53
3	83	71	61	54	79	68	60	53	64	56	50	59	53	48	55	50	46	55	50	46	43
4	75	62	52	44	72	60	51	44	56	48	42	52	45	40	49	43	38	49	43	38	36
5	69	55	45	38	66	53	44	37	50	42	35	46	39	34	43	38	33	43	38	33	30
6	63	49	39	32	61	47	38	32	44	36	31	42	35	29	39	33	28	39	33	28	26
7	58	44	35	28	56	43	34	28	40	32	27	38	31	26	36	29	25	36	29	25	23
8	54	40	31	25	52	39	30	24	37	29	24	34	28	23	32	26	22	32	26	22	20
9	51	36	28	22	49	35	27	22	33	26	21	32	25	20	30	24	20	30	24	20	18
10	47	33	25	20	45	33	25	19	31	24	19	29	23	18	28	22	18	28	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	3255	3255	3255
5°	3574	3208	2676
10°	4044	3168	2206
15°	4531	3128	1719
20°	5111	3077	1266
25°	5591	3018	831
30°	5948	2939	468
35°	6257	2853	206
40°	6532	2748	49
45°	6767	2617	0
50°	6964	2443	0
55°	7115	2221	0
60°	7191	1963	0
65°	7221	1671	0
70°	7197	1363	0
75°	7105	1004	6
80°	6817	613	31
85°	6590	295	42



TEST NUMBER: P550507

CATALOG NUMBER: FCC-X-2-LD4-1HI-35-UNV-81-86-ED1D-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.0	1.9
10°-20°	86.7	5.8
20°-30°	140.5	9.4
30°-40°	180.4	12.1
40°-50°	204.2	13.7
50°-60°	211.6	14.2
60°-70°	199.6	13.3
70°-80°	167.2	11.2
80°-90°	121.2	8.1
90°-100°	79.7	5.3
100°-110°	46.0	3.1
110°-120°	20.3	1.4
120°-130°	5.5	0.4
130°-140°	1.3	0.1
140°-150°	0.8	0.1
150°-160°	0.6	0.0
160°-170°	0.3	0.0
170°-180°	0.1	0.0
0°-30°	256.1	17.1
0°-40°	436.6	29.2
0°-60°	852.4	57.0
0°-90°	1340.4	89.7
90°-120°	146.0	9.8
90°-150°	153.6	10.3
90°-180°	155.0	10.4
0°-180°	1495.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	302	302	302	302	302	
5°	345	332	300	272	258	35
15°	461	404	290	210	175	133
25°	580	474	269	138	86	268
35°	643	511	236	67	21	403
45°	667	506	193	15	0	515
55°	650	474	140	0	0	580
65°	588	420	83	0	0	581
75°	490	339	35	0	0	514
85°	358	246	6	2	2	306
90°	310	197	2	2	3	170
95°	267	154	1	3	4	209
105°	183	80	1	2	3	193
115°	100	26	1	1	2	100
125°	30	4	2	1	2	30
135°	2	1	2	2	1	3
145°	0	1	2	1	1	0
155°	1	2	2	1	0	0
165°	1	1	2	1	0	0
175°	1	1	2	1	0	0
180°	1	1	1	1	1	



TEST NUMBER: P550507

CATALOG NUMBER: FCC-X-2-LD4-1HI-35-UNV-81-86-ED1D-90

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	112.5°
0°	302.4	302.4	302.4	302.4	302.4	302.4	302.4	302.4	302.4	302.4	302.4
2.5°	327.8	327.4	326.3	324.4	321.7	317.0	313.2	309.7	305.1	301.2	293.9
5°	345.2	343.2	341.7	339.8	333.6	329.4	322.4	314.7	307.4	300.1	285.5
7.5°	372.9	369.8	367.5	362.1	353.6	344.0	333.2	325.9	320.9	300.5	275.4
10°	402.6	399.9	395.2	385.6	375.2	361.3	345.9	328.6	313.2	296.2	266.6
12.5°	431.8	428.0	421.4	409.1	394.5	377.1	355.9	335.5	313.6	293.5	256.2
15°	461.1	456.9	449.9	434.9	415.7	392.9	367.1	341.3	315.5	290.1	245.4
17.5°	493.1	487.3	476.9	460.0	435.7	407.6	377.1	345.9	314.7	285.8	233.8
20°	527.4	519.3	508.1	485.4	456.9	423.7	387.2	350.6	314.3	280.8	220.7
22.5°	555.9	547.8	535.5	512.0	477.7	437.2	395.6	353.6	312.8	275.1	208.4
25°	580.5	574.0	560.5	533.5	497.3	451.5	403.7	355.9	310.5	268.9	195.3
27.5°	599.8	593.6	578.6	550.9	513.9	464.2	409.9	357.1	307.4	262.7	181.8
30°	616.7	610.6	592.5	564.0	525.1	474.2	416.0	357.5	303.6	253.5	167.2
32.5°	629.8	624.1	605.6	575.1	532.8	481.1	419.5	357.1	298.6	246.9	151.4
35°	642.9	637.2	615.6	583.2	538.5	484.2	422.2	355.2	292.4	236.1	136.4
37.5°	653.0	646.4	624.5	588.6	541.2	485.0	421.8	352.5	285.8	227.3	121.3
40°	659.9	653.0	629.5	591.7	542.0	483.8	418.7	347.9	278.1	216.1	105.6
42.5°	664.5	656.8	631.8	596.3	540.5	480.8	414.1	342.1	269.7	206.5	90.5
45°	666.8	658.7	632.2	592.5	537.8	475.0	407.2	334.8	260.4	193.4	75.5
47.5°	665.7	656.8	630.2	588.2	532.8	468.8	399.5	325.9	249.2	181.8	61.3
50°	663.7	654.5	626.0	582.8	525.8	461.1	391.0	315.1	237.7	167.6	48.5
52.5°	657.6	648.3	621.4	575.1	517.7	452.3	379.4	303.9	225.4	153.7	37.0
55°	649.9	641.4	613.3	568.2	507.3	441.5	368.7	292.0	213.4	139.5	26.6
57.5°	637.9	630.2	603.3	557.0	496.9	429.5	356.7	278.9	198.4	125.2	18.5
60°	623.3	615.6	589.4	544.3	485.0	416.0	343.6	265.4	184.9	110.9	11.6
62.5°	607.9	600.6	573.2	528.5	470.0	401.8	329.4	251.9	170.7	97.8	6.9
65°	587.5	580.5	555.9	509.7	453.4	386.4	313.6	235.8	156.0	83.2	3.9
67.5°	565.9	559.7	534.7	492.3	434.1	369.4	297.4	220.0	140.6	70.5	1.9
70°	542.8	535.1	512.0	468.8	414.5	350.2	279.7	203.8	126.0	58.2	0.0
72.5°	515.8	510.0	487.7	446.9	391.8	329.8	261.6	186.1	109.8	46.2	0.4
75°	489.6	482.3	461.9	423.4	369.4	308.2	241.5	169.5	94.0	35.4	0.4
77.5°	455.7	453.4	434.1	396.8	348.2	287.4	219.6	149.5	79.0	25.4	0.4
80°	421.8	419.5	404.5	370.2	323.6	262.7	199.2	130.6	64.3	16.9	0.4
82.5°	388.3	385.2	371.0	342.5	298.6	241.9	178.0	111.7	50.8	10.4	0.4
85°	358.3	354.4	339.0	312.8	272.7	218.4	156.0	93.2	37.8	5.8	0.8
87.5°	332.5	329.8	312.8	285.8	246.5	196.5	136.8	75.5	26.6	2.7	1.2
90°	310.5	304.7	289.7	261.2	221.9	172.2	116.3	60.5	17.7	1.5	1.5
92.5°	288.9	283.9	267.3	238.1	199.9	151.4	96.7	46.2	11.2	0.8	1.9
95°	266.6	261.2	245.0	218.0	177.6	130.2	79.4	33.9	6.2	0.8	1.9
97.5°	244.6	239.6	222.7	195.7	157.6	111.7	62.8	23.9	3.1	0.8	1.5
100°	224.2	218.4	203.0	176.0	137.5	93.2	48.5	15.4	1.9	0.8	1.5
102.5°	202.6	198.0	182.2	156.0	116.7	75.9	36.2	9.6	0.8	0.8	1.2
105°	183.4	177.6	162.2	135.2	99.4	59.7	25.4	5.8	0.8	0.8	1.2



TEST NUMBER: P550507

CATALOG NUMBER: FCC-X-2-LD4-1HI-35-UNV-81-86-ED1D-90

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	112.5°
112.5°	119.4	114.8	101.3	78.6	50.5	23.5	6.9	1.2	1.2	1.2	1.2
115°	99.8	92.8	80.9	60.9	37.4	15.4	3.5	1.2	1.2	1.2	1.2
117.5°	79.7	74.0	65.5	46.2	24.7	10.0	1.9	1.2	1.2	1.2	1.2
120°	62.4	57.0	47.4	32.0	16.6	5.8	0.8	1.2	1.2	1.2	1.2
122.5°	44.7	40.4	32.0	20.8	10.0	2.7	1.2	1.2	1.5	1.5	1.2
125°	29.7	27.4	21.2	12.7	6.2	1.2	1.2	1.2	1.5	1.5	1.2
127.5°	19.3	17.3	12.3	7.3	2.7	1.2	1.2	1.5	1.5	1.5	1.2
130°	10.8	9.6	7.3	4.2	1.2	1.2	1.2	1.5	1.5	1.5	1.2
132.5°	6.2	5.8	3.9	0.8	1.2	1.2	1.2	1.5	1.5	1.5	1.5
135°	1.5	0.8	0.8	0.8	1.2	1.2	1.5	1.5	1.9	1.9	1.5
137.5°	0.4	0.4	0.8	0.8	1.2	1.2	1.5	1.9	1.9	1.9	1.5
140°	0.4	0.4	0.8	1.2	1.2	1.2	1.5	1.9	1.9	1.9	1.5
142.5°	0.4	0.8	0.8	1.2	1.2	1.5	1.5	1.9	1.9	1.5	1.5
145°	0.4	0.8	0.8	1.2	1.2	1.5	1.5	1.9	1.5	1.5	1.5
147.5°	0.8	0.8	0.8	1.2	1.2	1.5	1.5	1.9	1.9	1.5	1.5
150°	0.4	0.8	0.8	1.2	1.5	1.5	1.5	1.9	1.5	1.5	1.5
152.5°	0.4	0.8	0.8	1.2	1.5	1.5	1.5	1.9	1.5	1.5	1.5
155°	0.8	0.8	0.8	1.2	1.5	1.5	1.5	1.9	1.5	1.5	1.9
157.5°	0.8	0.8	0.8	1.2	1.5	1.5	1.5	1.9	1.5	1.5	1.9
160°	0.8	0.8	0.8	1.2	1.2	1.5	1.5	1.5	1.5	1.5	1.5
162.5°	0.8	0.8	0.8	1.2	1.2	1.5	1.5	1.5	1.5	1.5	1.5
165°	0.8	0.8	0.8	0.8	1.2	1.2	1.5	1.5	1.5	1.5	1.5
167.5°	0.8	0.8	0.8	1.2	1.2	1.2	1.5	1.5	1.5	1.5	1.5
170°	0.8	0.8	0.8	1.2	1.2	1.2	1.5	1.9	1.9	1.9	1.9
172.5°	0.8	0.8	0.8	1.2	1.2	1.5	1.5	1.9	1.9	1.9	1.9
175°	0.8	0.8	0.8	1.2	1.2	1.5	1.5	1.9	1.9	1.9	1.9
177.5°	0.4	0.8	0.8	1.2	1.2	1.5	1.5	1.9	1.9	1.9	1.5
180°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2



TEST NUMBER: P550507

CATALOG NUMBER: FCC-X-2-LD4-1HI-35-UNV-81-86-ED1D-90

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
0°	302.4	302.4	302.4
2.5°	287.8	282.4	280.8
5°	272.4	263.5	258.5
7.5°	256.9	245.0	239.2
10°	242.7	225.7	219.6
12.5°	225.7	206.1	196.5
15°	209.6	184.1	174.9
17.5°	191.5	163.0	152.2
20°	174.5	141.8	130.6
22.5°	155.2	121.0	108.6
25°	137.9	100.2	86.3
27.5°	118.6	79.0	67.0
30°	100.5	60.5	48.5
32.5°	83.2	44.3	33.5
35°	67.0	30.0	21.2
37.5°	51.6	18.5	10.8
40°	37.4	9.6	5.0
42.5°	25.0	4.6	2.7
45°	15.4	2.3	0.0
47.5°	8.9	0.0	0.0
50°	4.6	0.0	0.0
52.5°	1.9	0.0	0.0
55°	0.0	0.0	0.0
57.5°	0.0	0.0	0.0
60°	0.0	0.0	0.0
62.5°	0.0	0.0	0.0
65°	0.0	0.0	0.0
67.5°	0.0	0.0	0.0
70°	0.0	0.0	0.0
72.5°	0.0	0.0	0.0
75°	0.4	0.4	0.4
77.5°	0.4	0.8	1.2
80°	0.8	1.5	1.9
82.5°	1.5	1.9	1.9
85°	1.5	1.9	2.3
87.5°	1.9	2.3	2.7
90°	2.3	2.7	2.7
92.5°	2.3	3.1	3.1
95°	2.7	3.1	3.5
97.5°	3.1	3.5	3.5
100°	2.7	3.5	3.9
102.5°	2.3	3.5	3.5
105°	1.9	2.7	3.1



TEST NUMBER: P550507

CATALOG NUMBER: FCC-X-2-LD4-1HI-35-UNV-81-86-ED1D-90

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
112.5°	1.5	1.9	1.9
115°	1.2	1.5	1.9
117.5°	1.2	1.5	1.5
120°	1.2	1.2	1.5
122.5°	1.2	1.2	1.5
125°	1.2	1.2	1.5
127.5°	1.5	1.2	1.2
130°	1.2	1.2	1.2
132.5°	1.5	1.2	1.2
135°	1.5	1.2	1.2
137.5°	1.5	1.2	1.2
140°	1.5	1.2	1.2
142.5°	1.5	1.2	1.2
145°	1.2	1.2	1.2
147.5°	1.2	1.2	1.2
150°	1.2	1.2	0.8
152.5°	1.2	0.8	0.8
155°	1.2	0.8	0.4
157.5°	1.5	0.8	0.4
160°	1.2	0.8	0.4
162.5°	1.2	0.8	0.4
165°	1.2	0.8	0.0
167.5°	1.2	0.8	0.4
170°	1.2	0.8	0.4
172.5°	1.2	0.8	0.4
175°	1.2	0.4	0.4
177.5°	1.2	0.4	0.4
180°	1.2	1.2	1.2



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	161.8	157.2	141.8	116.3	81.3	45.5	16.9	3.1	0.8	1.2	1.2
110°	141.0	137.1	121.3	96.7	65.5	33.9	11.2	1.9	1.2	1.2	1.2





107.5°	1.5	2.3	2.7
110°	1.5	1.9	2.3



(END OF REPORT)