

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P550606

Luminaire Tested: **FCC-X-2-LD4-1HI-40-UNV-93-87-ED1D**

Issue Date: 7/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P550606
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2105-248-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FCC-X-2-LD4-1HI-40-UNV-93-87-ED1D
Description: FCC CORNER MOUNT LUMINAIRE WITH .156 CLEAR TEMPERED GLASS FIXTURE
SIDE AND .375 CLEAR PC ENVIRONMENTAL SIDE LENSES AND 4000K, AND 80 CRI
LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1840.9 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 1.66 / 1.25 / 1.59
Luminous Opening: Rectangular w/ Sides (W: 2' x L: 0.5' x H: 0.25')
CIE Type: Semi-Direct

Input Watts (W): 21.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P550606

CATALOG NUMBER: FCC-X-2-LD4-1HI-40-UNV-93-87-ED1D

Luminous Intensity Polar Plot





TEST NUMBER: P550606

CATALOG NUMBER: FCC-X-2-LD4-1HI-40-UNV-93-87-ED1D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	117	117	117	117	113	113	113	113	105	105	105	99	99	99	93	93	93	90																			
1	103	96	91	86	99	93	88	83	87	83	79	81	78	74	76	73	70	67																			
2	92	82	74	67	88	79	72	65	74	67	62	69	64	59	64	60	56	53																			
3	83	71	61	54	79	68	60	53	64	56	50	59	53	48	55	50	46	43																			
4	75	62	52	44	72	60	51	44	56	48	42	52	45	40	49	43	38	36																			
5	69	55	45	38	66	53	44	37	50	42	35	46	39	34	43	38	33	30																			
6	63	49	39	32	61	47	38	32	44	36	31	42	35	29	39	33	28	26																			
7	58	44	35	28	56	43	34	28	40	32	27	38	31	26	36	29	25	23																			
8	54	40	31	25	52	39	30	24	37	29	24	34	28	23	32	26	22	20																			
9	51	36	28	22	49	35	27	22	33	26	21	32	25	20	30	24	20	18																			
10	47	33	25	20	45	33	25	19	31	24	19	29	23	18	28	22	18	16																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	4008	4008	4008
5°	4400	3949	3295
10°	4979	3901	2716
15°	5580	3852	2117
20°	6293	3789	1558
25°	6885	3716	1024
30°	7325	3618	577
35°	7705	3514	254
40°	8043	3384	61
45°	8334	3222	0
50°	8577	3008	0
55°	8762	2734	0
60°	8856	2417	0
65°	8891	2059	0
70°	8862	1677	0
75°	8749	1236	7
80°	8394	758	39
85°	8115	361	51



TEST NUMBER: P550606

CATALOG NUMBER: FCC-X-2-LD4-1HI-40-UNV-93-87-ED1D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.7	1.9
10°-20°	106.8	5.8
20°-30°	173.0	9.4
30°-40°	222.2	12.1
40°-50°	251.5	13.7
50°-60°	260.6	14.2
60°-70°	245.7	13.3
70°-80°	205.9	11.2
80°-90°	149.3	8.1
90°-100°	98.1	5.3
100°-110°	56.7	3.1
110°-120°	25.0	1.4
120°-130°	6.8	0.4
130°-140°	1.5	0.1
140°-150°	1.0	0.1
150°-160°	0.7	0.0
160°-170°	0.4	0.0
170°-180°	0.1	0.0
0°-30°	315.4	17.1
0°-40°	537.6	29.2
0°-60°	1049.7	57.0
0°-90°	1650.6	89.7
90°-120°	179.8	9.8
90°-150°	189.1	10.3
90°-180°	190.0	10.3
0°-180°	1840.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	372	372	372	372	372	
5°	425	408	370	335	318	43
15°	568	498	357	258	215	164
25°	715	584	331	170	106	330
35°	792	630	291	82	26	497
45°	821	624	238	19	0	634
55°	800	584	172	0	0	715
65°	723	517	102	0	0	716
75°	603	417	44	0	0	632
85°	441	302	7	2	3	377
90°	382	243	2	3	3	210
95°	328	190	1	3	4	258
105°	226	98	1	2	4	238
115°	123	32	1	1	2	123
125°	36	4	2	1	2	36
135°	2	1	2	2	1	3
145°	0	2	2	1	1	0
155°	1	2	2	1	0	0
165°	1	1	2	1	0	0
175°	1	2	2	1	0	0
180°	1	1	1	1	1	



TEST NUMBER: P550606

CATALOG NUMBER: FCC-X-2-LD4-1HI-40-UNV-93-87-ED1D

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	112.5°
0°	372.4	372.4	372.4	372.4	372.4	372.4	372.4	372.4	372.4	372.4	372.4
2.5°	403.7	403.2	401.8	399.4	396.1	390.4	385.7	381.4	375.7	371.0	362.0
5°	425.0	422.7	420.8	418.4	410.8	405.6	397.1	387.6	378.6	369.5	351.5
7.5°	459.2	455.4	452.6	445.9	435.5	423.6	410.3	401.3	395.2	370.0	339.2
10°	495.7	492.4	486.7	474.9	462.0	445.0	426.0	404.6	385.7	364.8	328.3
12.5°	531.8	527.0	519.0	503.8	485.8	464.4	438.3	413.2	386.1	361.5	315.5
15°	567.8	562.6	554.1	535.6	511.9	483.9	452.1	420.3	388.5	357.2	302.2
17.5°	607.2	600.1	587.3	566.4	536.5	501.9	464.4	426.0	387.6	352.0	288.0
20°	649.4	639.5	625.7	597.7	562.6	521.8	476.8	431.7	387.1	345.8	271.8
22.5°	684.5	674.6	659.4	630.5	588.2	538.4	487.2	435.5	385.2	338.7	256.6
25°	714.9	706.8	690.2	657.0	612.4	556.0	497.2	438.3	382.4	331.1	240.5
27.5°	738.6	731.0	712.5	678.4	632.8	571.6	504.7	439.8	378.6	323.5	223.9
30°	759.5	751.9	729.6	694.5	646.6	584.0	512.3	440.2	373.8	312.1	205.9
32.5°	775.6	768.5	745.7	708.3	656.1	592.5	516.6	439.8	367.6	304.1	186.4
35°	791.7	784.6	758.1	718.2	663.2	596.3	519.9	437.4	360.1	290.8	167.9
37.5°	804.1	796.0	769.0	724.9	666.5	597.2	519.4	434.1	352.0	279.9	149.4
40°	812.6	804.1	775.1	728.7	667.5	595.8	515.7	428.4	342.5	266.1	130.0
42.5°	818.3	808.8	778.0	734.3	665.6	592.0	510.0	421.3	332.1	254.3	111.5
45°	821.2	811.2	778.5	729.6	662.2	584.9	501.4	412.2	320.7	238.1	93.0
47.5°	819.7	808.8	776.1	724.4	656.1	577.3	491.9	401.3	306.9	223.9	75.4
50°	817.4	806.0	770.9	717.7	647.5	567.8	481.5	388.0	292.7	206.4	59.8
52.5°	809.8	798.4	765.2	708.3	637.6	556.9	467.3	374.3	277.5	189.3	45.5
55°	800.3	789.8	755.2	699.7	624.8	543.6	454.0	359.6	262.8	171.7	32.7
57.5°	785.6	776.1	742.9	686.0	612.0	528.9	439.3	343.5	244.3	154.2	22.8
60°	767.6	758.1	725.8	670.3	597.2	512.3	423.1	326.8	227.7	136.6	14.2
62.5°	748.6	739.6	705.9	650.9	578.7	494.8	405.6	310.2	210.2	120.5	8.5
65°	723.4	714.9	684.5	627.6	558.3	475.8	386.1	290.3	192.1	102.5	4.7
67.5°	696.9	689.3	658.4	606.3	534.6	454.9	366.2	270.9	173.1	86.8	2.4
70°	668.4	658.9	630.5	577.3	510.4	431.2	344.4	250.9	155.1	71.6	0.0
72.5°	635.2	628.1	600.6	550.3	482.4	406.1	322.1	229.1	135.2	56.9	0.5
75°	602.9	593.9	568.8	521.3	454.9	379.5	297.4	208.7	115.7	43.6	0.5
77.5°	561.2	558.3	534.6	488.6	428.8	353.9	270.4	184.1	97.2	31.3	0.5
80°	519.4	516.6	498.1	455.9	398.5	323.5	245.3	160.8	79.2	20.9	0.5
82.5°	478.2	474.4	456.8	421.7	367.6	297.9	219.2	137.6	62.6	12.8	0.5
85°	441.2	436.4	417.5	385.2	335.9	269.0	192.1	114.8	46.5	7.1	0.9
87.5°	409.4	406.1	385.2	352.0	303.6	241.9	168.4	93.0	32.7	3.3	1.4
90°	382.4	375.2	356.7	321.6	273.2	212.0	143.3	74.5	21.8	1.9	1.9
92.5°	355.8	349.6	329.2	293.2	246.2	186.4	119.1	56.9	13.8	0.9	2.4
95°	328.3	321.6	301.7	268.5	218.7	160.3	97.7	41.7	7.6	0.9	2.4
97.5°	301.2	295.1	274.2	241.0	194.0	137.6	77.3	29.4	3.8	0.9	1.9
100°	276.1	269.0	250.0	216.8	169.4	114.8	59.8	19.0	2.4	0.9	1.9
102.5°	249.5	243.8	224.4	192.1	143.7	93.5	44.6	11.9	0.9	0.9	1.4
105°	225.8	218.7	199.7	166.5	122.4	73.5	31.3	7.1	0.9	0.9	1.4



TEST NUMBER: P550606

CATALOG NUMBER: FCC-X-2-LD4-1HI-40-UNV-93-87-ED1D

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	112.5°
112.5°	147.1	141.4	124.8	96.8	62.1	28.9	8.5	1.4	1.4	1.4	1.4
115°	122.9	114.3	99.6	75.0	46.0	19.0	4.3	1.4	1.4	1.4	1.4
117.5°	98.2	91.1	80.6	56.9	30.4	12.3	2.4	1.4	1.4	1.4	1.4
120°	76.8	70.2	58.3	39.4	20.4	7.1	0.9	1.4	1.4	1.4	1.4
122.5°	55.0	49.8	39.4	25.6	12.3	3.3	1.4	1.4	1.9	1.9	1.4
125°	36.5	33.7	26.1	15.7	7.6	1.4	1.4	1.4	1.9	1.9	1.4
127.5°	23.7	21.3	15.2	9.0	3.3	1.4	1.4	1.9	1.9	1.9	1.4
130°	13.3	11.9	9.0	5.2	1.4	1.4	1.4	1.9	1.9	1.9	1.4
132.5°	7.6	7.1	4.7	0.9	1.4	1.4	1.4	1.9	1.9	1.9	1.9
135°	1.9	0.9	0.9	0.9	1.4	1.4	1.9	1.9	2.4	2.4	1.9
137.5°	0.5	0.5	0.9	0.9	1.4	1.4	1.9	2.4	2.4	2.4	1.9
140°	0.5	0.5	0.9	1.4	1.4	1.4	1.9	2.4	2.4	2.4	1.9
142.5°	0.5	0.9	0.9	1.4	1.4	1.9	1.9	2.4	2.4	1.9	1.9
145°	0.5	0.9	0.9	1.4	1.4	1.9	1.9	2.4	1.9	1.9	1.9
147.5°	0.9	0.9	0.9	1.4	1.4	1.9	1.9	2.4	2.4	1.9	1.9
150°	0.5	0.9	0.9	1.4	1.9	1.9	1.9	2.4	1.9	1.9	1.9
152.5°	0.5	0.9	0.9	1.4	1.9	1.9	1.9	2.4	1.9	1.9	1.9
155°	0.9	0.9	0.9	1.4	1.9	1.9	1.9	2.4	1.9	1.9	2.4
157.5°	0.9	0.9	0.9	1.4	1.9	1.9	1.9	2.4	1.9	1.9	2.4
160°	0.9	0.9	0.9	1.4	1.4	1.9	1.9	1.9	1.9	1.9	1.9
162.5°	0.9	0.9	0.9	1.4	1.4	1.9	1.9	1.9	1.9	1.9	1.9
165°	0.9	0.9	0.9	0.9	1.4	1.4	1.9	1.9	1.9	1.9	1.9
167.5°	0.9	0.9	0.9	1.4	1.4	1.4	1.9	1.9	1.9	1.9	1.9
170°	0.9	0.9	0.9	1.4	1.4	1.4	1.9	2.4	2.4	2.4	2.4
172.5°	0.9	0.9	0.9	1.4	1.4	1.9	1.9	2.4	2.4	2.4	2.4
175°	0.9	0.9	0.9	1.4	1.4	1.9	1.9	2.4	2.4	2.4	2.4
177.5°	0.5	0.9	0.9	1.4	1.4	1.9	1.9	2.4	2.4	2.4	1.9
180°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4



TEST NUMBER: P550606

CATALOG NUMBER: FCC-X-2-LD4-1HI-40-UNV-93-87-ED1D

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
0°	372.4	372.4	372.4
2.5°	354.4	347.7	345.8
5°	335.4	324.5	318.3
7.5°	316.4	301.7	294.6
10°	298.9	278.0	270.4
12.5°	278.0	253.8	241.9
15°	258.1	226.8	215.4
17.5°	235.8	200.7	187.4
20°	214.9	174.6	160.8
22.5°	191.2	149.0	133.8
25°	169.8	123.3	106.3
27.5°	146.1	97.2	82.5
30°	123.8	74.5	59.8
32.5°	102.5	54.6	41.3
35°	82.5	37.0	26.1
37.5°	63.6	22.8	13.3
40°	46.0	11.9	6.2
42.5°	30.8	5.7	3.3
45°	19.0	2.8	0.0
47.5°	10.9	0.0	0.0
50°	5.7	0.0	0.0
52.5°	2.4	0.0	0.0
55°	0.0	0.0	0.0
57.5°	0.0	0.0	0.0
60°	0.0	0.0	0.0
62.5°	0.0	0.0	0.0
65°	0.0	0.0	0.0
67.5°	0.0	0.0	0.0
70°	0.0	0.0	0.0
72.5°	0.0	0.0	0.0
75°	0.5	0.5	0.5
77.5°	0.5	0.9	1.4
80°	0.9	1.9	2.4
82.5°	1.9	2.4	2.4
85°	1.9	2.4	2.8
87.5°	2.4	2.8	3.3
90°	2.8	3.3	3.3
92.5°	2.8	3.8	3.8
95°	3.3	3.8	4.3
97.5°	3.8	4.3	4.3
100°	3.3	4.3	4.7
102.5°	2.8	4.3	4.3
105°	2.4	3.3	3.8



TEST NUMBER: P550606

CATALOG NUMBER: FCC-X-2-LD4-1HI-40-UNV-93-87-ED1D

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
112.5°	1.9	2.4	2.4
115°	1.4	1.9	2.4
117.5°	1.4	1.9	1.9
120°	1.4	1.4	1.9
122.5°	1.4	1.4	1.9
125°	1.4	1.4	1.9
127.5°	1.9	1.4	1.4
130°	1.4	1.4	1.4
132.5°	1.9	1.4	1.4
135°	1.9	1.4	1.4
137.5°	1.9	1.4	1.4
140°	1.9	1.4	1.4
142.5°	1.9	1.4	1.4
145°	1.4	1.4	1.4
147.5°	1.4	1.4	1.4
150°	1.4	1.4	0.9
152.5°	1.4	0.9	0.9
155°	1.4	0.9	0.5
157.5°	1.9	0.9	0.5
160°	1.4	0.9	0.5
162.5°	1.4	0.9	0.5
165°	1.4	0.9	0.0
167.5°	1.4	0.9	0.5
170°	1.4	0.9	0.5
172.5°	1.4	0.9	0.5
175°	1.4	0.5	0.5
177.5°	1.4	0.5	0.5
180°	1.4	1.4	1.4



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	199.2	193.5	174.6	143.3	100.1	56.0	20.9	3.8	0.9	1.4	1.4
110°	173.6	168.9	149.4	119.1	80.6	41.7	13.8	2.4	1.4	1.4	1.4





107.5°	1.9	2.8	3.3
110°	1.9	2.4	2.8



(END OF REPORT)