

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P550795

Luminaire Tested: **FCC-X-2-LD4-1LO-35-UNV-93-86-ED1D-90**

Issue Date: 7/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P550795  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2105-248-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FCC-X-2-LD4-1LO-35-UNV-93-86-ED1D-90  
Description: FCC CORNER MOUNT LUMINAIRE WITH .156 CLEAR TEMPERED GLASS FIXTURE  
SIDE AND .250 CLEAR PC ENVIRONMENTAL SIDE LENSES AND 3500K, AND 90 CRI  
LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 959.9 lumens  
Efficiency: N/A  
Efficacy: 82.0 lumens/watt  
Spacing Criteria (0/90/45): 1.66 / 1.25 / 1.59  
Luminous Opening: Rectangular w/ Sides (W: 2' x L: 0.5' x H: 0.25')  
CIE Type: Semi-Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P550795

CATALOG NUMBER: FCC-X-2-LD4-1LO-35-UNV-93-86-ED1D-90

### Luminous Intensity Polar Plot





TEST NUMBER: P550795

CATALOG NUMBER: FCC-X-2-LD4-1LO-35-UNV-93-86-ED1D-90

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	113	113	113	113	105	105	105	99	99	99	93	93	93	93	93	93	90
1	103	96	91	86	99	93	88	83	87	83	79	81	78	74	76	73	70	70	70	70	67
2	92	82	74	67	88	79	72	65	74	67	62	69	64	59	64	60	56	56	56	56	53
3	83	71	61	54	79	68	60	53	64	56	50	59	53	48	55	50	46	46	46	46	43
4	75	62	52	44	72	60	51	44	56	48	42	52	45	40	49	43	38	38	38	38	36
5	69	55	45	38	66	53	44	37	50	42	35	46	39	34	43	38	33	33	33	33	30
6	63	49	39	32	61	47	38	32	44	36	31	42	35	29	39	33	28	28	28	28	26
7	58	44	35	28	56	43	34	28	40	32	27	38	31	26	36	29	25	25	25	25	23
8	54	40	31	25	52	39	30	24	37	29	24	34	28	23	32	26	22	22	22	22	20
9	51	36	28	22	49	35	27	22	33	26	21	32	25	20	30	24	20	20	20	20	18
10	47	33	25	20	45	33	25	19	31	24	19	29	23	18	28	22	18	18	18	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	2090	2090	2090
5°	2294	2060	1718
10°	2596	2034	1416
15°	2910	2009	1104
20°	3281	1975	813
25°	3590	1938	534
30°	3819	1887	301
35°	4019	1832	132
40°	4194	1765	32
45°	4346	1681	0
50°	4472	1568	0
55°	4569	1425	0
60°	4617	1260	0
65°	4636	1073	0
70°	4620	876	0
75°	4562	647	3
80°	4378	395	19
85°	4232	188	28



TEST NUMBER: P550795

CATALOG NUMBER: FCC-X-2-LD4-1LO-35-UNV-93-86-ED1D-90

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	18.6	1.9
10°-20°	55.7	5.8
20°-30°	90.2	9.4
30°-40°	115.9	12.1
40°-50°	131.2	13.7
50°-60°	135.9	14.2
60°-70°	128.1	13.3
70°-80°	107.4	11.2
80°-90°	77.8	8.1
90°-100°	51.2	5.3
100°-110°	29.5	3.1
110°-120°	13.0	1.4
120°-130°	3.5	0.4
130°-140°	0.8	0.1
140°-150°	0.5	0.1
150°-160°	0.4	0.0
160°-170°	0.2	0.0
170°-180°	0.1	0.0
0°-30°	164.5	17.1
0°-40°	280.3	29.2
0°-60°	547.4	57.0
0°-90°	860.7	89.7
90°-120°	93.7	9.8
90°-150°	98.5	10.3
90°-180°	99.0	10.3
0°-180°	959.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	194	194	194	194	194	
5°	222	213	193	175	166	22
15°	296	260	186	135	112	85
25°	373	305	173	89	55	172
35°	413	328	152	43	14	259
45°	428	325	124	10	0	331
55°	417	305	90	0	0	373
65°	377	270	53	0	0	373
75°	314	218	23	0	0	330
85°	230	158	4	1	2	196
90°	199	127	1	2	2	109
95°	171	99	0	2	2	134
105°	118	51	0	1	2	124
115°	64	17	1	1	1	64
125°	19	2	1	1	1	19
135°	1	1	1	1	1	2
145°	0	1	1	1	1	0
155°	0	1	1	1	0	0
165°	0	1	1	1	0	0
175°	0	1	1	1	0	0
180°	1	1	1	1	1	



TEST NUMBER: P550795

CATALOG NUMBER: FCC-X-2-LD4-1LO-35-UNV-93-86-ED1D-90

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	112.5°
0°	194.2	194.2	194.2	194.2	194.2	194.2	194.2	194.2	194.2	194.2	194.2
2.5°	210.5	210.3	209.5	208.3	206.6	203.6	201.1	198.9	195.9	193.4	188.7
5°	221.6	220.4	219.4	218.2	214.2	211.5	207.0	202.1	197.4	192.7	183.3
7.5°	239.5	237.5	236.0	232.5	227.1	220.9	214.0	209.3	206.1	192.9	176.9
10°	258.5	256.8	253.8	247.6	240.9	232.0	222.1	211.0	201.1	190.2	171.2
12.5°	277.3	274.8	270.6	262.7	253.3	242.2	228.6	215.5	201.4	188.5	164.5
15°	296.1	293.4	288.9	279.3	266.9	252.3	235.7	219.2	202.6	186.3	157.6
17.5°	316.6	312.9	306.2	295.4	279.8	261.7	242.2	222.1	202.1	183.5	150.2
20°	338.6	333.5	326.3	311.7	293.4	272.1	248.6	225.1	201.9	180.3	141.7
22.5°	357.0	351.8	343.8	328.8	306.7	280.8	254.0	227.1	200.9	176.6	133.8
25°	372.8	368.6	359.9	342.6	319.4	289.9	259.2	228.6	199.4	172.7	125.4
27.5°	385.2	381.2	371.5	353.7	330.0	298.1	263.2	229.3	197.4	168.7	116.8
30°	396.0	392.1	380.5	362.1	337.2	304.5	267.2	229.6	194.9	162.8	107.4
32.5°	404.4	400.7	388.9	369.3	342.1	309.0	269.4	229.3	191.7	158.6	97.2
35°	412.9	409.1	395.3	374.5	345.8	310.9	271.1	228.1	187.8	151.6	87.6
37.5°	419.3	415.1	401.0	378.0	347.6	311.4	270.9	226.3	183.5	145.9	77.9
40°	423.7	419.3	404.2	380.0	348.0	310.7	268.9	223.4	178.6	138.8	67.8
42.5°	426.7	421.8	405.7	382.9	347.1	308.7	265.9	219.7	173.2	132.6	58.1
45°	428.2	423.0	405.9	380.5	345.3	305.0	261.5	215.0	167.2	124.2	48.5
47.5°	427.5	421.8	404.7	377.7	342.1	301.0	256.5	209.3	160.0	116.8	39.3
50°	426.2	420.3	402.0	374.3	337.7	296.1	251.1	202.3	152.6	107.6	31.2
52.5°	422.3	416.3	399.0	369.3	332.5	290.4	243.7	195.2	144.7	98.7	23.7
55°	417.3	411.9	393.8	364.9	325.8	283.5	236.7	187.5	137.0	89.5	17.1
57.5°	409.6	404.7	387.4	357.7	319.1	275.8	229.1	179.1	127.4	80.4	11.9
60°	400.2	395.3	378.5	349.5	311.4	267.2	220.7	170.4	118.7	71.2	7.4
62.5°	390.3	385.6	368.1	339.4	301.8	258.0	211.5	161.8	109.6	62.8	4.5
65°	377.2	372.8	357.0	327.3	291.2	248.1	201.4	151.4	100.2	53.4	2.5
67.5°	363.4	359.4	343.3	316.1	278.8	237.2	191.0	141.2	90.3	45.3	1.2
70°	348.5	343.6	328.8	301.0	266.2	224.9	179.6	130.9	80.9	37.4	0.0
72.5°	331.2	327.5	313.2	286.9	251.6	211.7	168.0	119.5	70.5	29.7	0.2
75°	314.4	309.7	296.6	271.9	237.2	197.9	155.1	108.8	60.4	22.8	0.2
77.5°	292.6	291.2	278.8	254.8	223.6	184.5	141.0	96.0	50.7	16.3	0.2
80°	270.9	269.4	259.7	237.7	207.8	168.7	127.9	83.9	41.3	10.9	0.2
82.5°	249.3	247.4	238.2	219.9	191.7	155.3	114.3	71.7	32.7	6.7	0.2
85°	230.1	227.6	217.7	200.9	175.1	140.3	100.2	59.9	24.2	3.7	0.5
87.5°	213.5	211.7	200.9	183.5	158.3	126.2	87.8	48.5	17.1	1.7	0.7
90°	199.4	195.7	186.0	167.7	142.5	110.6	74.7	38.8	11.4	1.0	1.0
92.5°	185.5	182.3	171.7	152.9	128.4	97.2	62.1	29.7	7.2	0.5	1.2
95°	171.2	167.7	157.3	140.0	114.0	83.6	51.0	21.8	4.0	0.5	1.2
97.5°	157.1	153.9	143.0	125.7	101.2	71.7	40.3	15.3	2.0	0.5	1.0
100°	144.0	140.3	130.4	113.0	88.3	59.9	31.2	9.9	1.2	0.5	1.0
102.5°	130.1	127.1	117.0	100.2	75.0	48.7	23.3	6.2	0.5	0.5	0.7
105°	117.7	114.0	104.1	86.8	63.8	38.3	16.3	3.7	0.5	0.5	0.7



TEST NUMBER: P550795

CATALOG NUMBER: FCC-X-2-LD4-1LO-35-UNV-93-86-ED1D-90

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	30°	40°	50°	60°	70°	80°	90°	112.5°
112.5°	76.7	73.7	65.1	50.5	32.4	15.1	4.5	0.7	0.7	0.7	0.7
115°	64.1	59.6	51.9	39.1	24.0	9.9	2.2	0.7	0.7	0.7	0.7
117.5°	51.2	47.5	42.1	29.7	15.8	6.4	1.2	0.7	0.7	0.7	0.7
120°	40.1	36.6	30.4	20.5	10.6	3.7	0.5	0.7	0.7	0.7	0.7
122.5°	28.7	26.0	20.5	13.4	6.4	1.7	0.7	0.7	1.0	1.0	0.7
125°	19.0	17.6	13.6	8.2	4.0	0.7	0.7	0.7	1.0	1.0	0.7
127.5°	12.4	11.1	7.9	4.7	1.7	0.7	0.7	1.0	1.0	1.0	0.7
130°	6.9	6.2	4.7	2.7	0.7	0.7	0.7	1.0	1.0	1.0	0.7
132.5°	4.0	3.7	2.5	0.5	0.7	0.7	0.7	1.0	1.0	1.0	1.0
135°	1.0	0.5	0.5	0.5	0.7	0.7	1.0	1.0	1.2	1.2	1.0
137.5°	0.2	0.2	0.5	0.5	0.7	0.7	1.0	1.2	1.2	1.2	1.0
140°	0.2	0.2	0.5	0.7	0.7	0.7	1.0	1.2	1.2	1.2	1.0
142.5°	0.2	0.5	0.5	0.7	0.7	1.0	1.0	1.2	1.2	1.0	1.0
145°	0.2	0.5	0.5	0.7	0.7	1.0	1.0	1.2	1.0	1.0	1.0
147.5°	0.5	0.5	0.5	0.7	0.7	1.0	1.0	1.2	1.2	1.0	1.0
150°	0.2	0.5	0.5	0.7	1.0	1.0	1.0	1.2	1.0	1.0	1.0
152.5°	0.2	0.5	0.5	0.7	1.0	1.0	1.0	1.2	1.0	1.0	1.0
155°	0.5	0.5	0.5	0.7	1.0	1.0	1.0	1.2	1.0	1.0	1.2
157.5°	0.5	0.5	0.5	0.7	1.0	1.0	1.0	1.2	1.0	1.0	1.2
160°	0.5	0.5	0.5	0.7	0.7	1.0	1.0	1.0	1.0	1.0	1.0
162.5°	0.5	0.5	0.5	0.7	0.7	1.0	1.0	1.0	1.0	1.0	1.0
165°	0.5	0.5	0.5	0.5	0.7	0.7	1.0	1.0	1.0	1.0	1.0
167.5°	0.5	0.5	0.5	0.7	0.7	0.7	1.0	1.0	1.0	1.0	1.0
170°	0.5	0.5	0.5	0.7	0.7	0.7	1.0	1.2	1.2	1.2	1.2
172.5°	0.5	0.5	0.5	0.7	0.7	1.0	1.0	1.2	1.2	1.2	1.2
175°	0.5	0.5	0.5	0.7	0.7	1.0	1.0	1.2	1.2	1.2	1.2
177.5°	0.2	0.5	0.5	0.7	0.7	1.0	1.0	1.2	1.2	1.2	1.0
180°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7



TEST NUMBER: P550795

CATALOG NUMBER: FCC-X-2-LD4-1LO-35-UNV-93-86-ED1D-90

**CANDELA DISTRIBUTION (continued):**

	135°	157.5°	180°
0°	194.2	194.2	194.2
2.5°	184.8	181.3	180.3
5°	174.9	169.2	166.0
7.5°	165.0	157.3	153.6
10°	155.8	145.0	141.0
12.5°	145.0	132.3	126.2
15°	134.6	118.2	112.3
17.5°	122.9	104.6	97.7
20°	112.1	91.0	83.9
22.5°	99.7	77.7	69.8
25°	88.6	64.3	55.4
27.5°	76.2	50.7	43.0
30°	64.6	38.8	31.2
32.5°	53.4	28.4	21.5
35°	43.0	19.3	13.6
37.5°	33.1	11.9	6.9
40°	24.0	6.2	3.2
42.5°	16.1	3.0	1.7
45°	9.9	1.5	0.0
47.5°	5.7	0.0	0.0
50°	3.0	0.0	0.0
52.5°	1.2	0.0	0.0
55°	0.0	0.0	0.0
57.5°	0.0	0.0	0.0
60°	0.0	0.0	0.0
62.5°	0.0	0.0	0.0
65°	0.0	0.0	0.0
67.5°	0.0	0.0	0.0
70°	0.0	0.0	0.0
72.5°	0.0	0.0	0.0
75°	0.2	0.2	0.2
77.5°	0.2	0.5	0.7
80°	0.5	1.0	1.2
82.5°	1.0	1.2	1.2
85°	1.0	1.2	1.5
87.5°	1.2	1.5	1.7
90°	1.5	1.7	1.7
92.5°	1.5	2.0	2.0
95°	1.7	2.0	2.2
97.5°	2.0	2.2	2.2
100°	1.7	2.2	2.5
102.5°	1.5	2.2	2.2
105°	1.2	1.7	2.0





TEST NUMBER: P550795

CATALOG NUMBER: FCC-X-2-LD4-1LO-35-UNV-93-86-ED1D-90

**CANDELA DISTRIBUTION (continued):**

	135°	157.5°	180°
112.5°	1.0	1.2	1.2
115°	0.7	1.0	1.2
117.5°	0.7	1.0	1.0
120°	0.7	0.7	1.0
122.5°	0.7	0.7	1.0
125°	0.7	0.7	1.0
127.5°	1.0	0.7	0.7
130°	0.7	0.7	0.7
132.5°	1.0	0.7	0.7
135°	1.0	0.7	0.7
137.5°	1.0	0.7	0.7
140°	1.0	0.7	0.7
142.5°	1.0	0.7	0.7
145°	0.7	0.7	0.7
147.5°	0.7	0.7	0.7
150°	0.7	0.7	0.5
152.5°	0.7	0.5	0.5
155°	0.7	0.5	0.2
157.5°	1.0	0.5	0.2
160°	0.7	0.5	0.2
162.5°	0.7	0.5	0.2
165°	0.7	0.5	0.0
167.5°	0.7	0.5	0.2
170°	0.7	0.5	0.2
172.5°	0.7	0.5	0.2
175°	0.7	0.2	0.2
177.5°	0.7	0.2	0.2
180°	0.7	0.7	0.7



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	103.9	100.9	91.0	74.7	52.2	29.2	10.9	2.0	0.5	0.7	0.7
110°	90.5	88.1	77.9	62.1	42.1	21.8	7.2	1.2	0.7	0.7	0.7







107.5°	1.0	1.5	1.7
110°	1.0	1.2	1.5



(END OF REPORT)