

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P550886

Luminaire Tested: **FCC-X-2-LD4-1LO-50-UNV-80-97-ED1D**

Issue Date: 7/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P550886
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2105-248-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FCC-X-2-LD4-1LO-50-UNV-80-97-ED1D
Description: FCC CORNER MOUNT LUMINAIRE WITH .125 PRISMATIC ACRYLIC FIXTURE SIDE AND .375 CLEAR TEMPERED GLASS ENVIRONMENTAL SIDE LENSES AND 5000K, AND 80 CRI LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1160.0 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.66 / 1.25 / 1.59
Luminous Opening: Rectangular w/ Sides (W: 2' x L: 0.5' x H: 0.25')
CIE Type: Semi-Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P550886

CATALOG NUMBER: FCC-X-2-LD4-1LO-50-UNV-80-97-ED1D

Luminous Intensity Polar Plot





TEST NUMBER: P550886

CATALOG NUMBER: FCC-X-2-LD4-1LO-50-UNV-80-97-ED1D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 117 | 117 | 117 | 117 | 113 | 113 | 113 | 113 | 105 | 105 | 105 | 99 | 99 | 99 | 93 | 93 | 93 | 90 | | | | | | | | | | | | | | | | | | | |
| 1 | 103 | 96 | 91 | 86 | 99 | 93 | 88 | 83 | 87 | 83 | 79 | 81 | 78 | 74 | 76 | 73 | 70 | 67 | | | | | | | | | | | | | | | | | | | |
| 2 | 92 | 82 | 74 | 67 | 88 | 79 | 72 | 65 | 74 | 67 | 62 | 69 | 64 | 59 | 64 | 60 | 56 | 53 | | | | | | | | | | | | | | | | | | | |
| 3 | 83 | 71 | 61 | 54 | 79 | 68 | 60 | 53 | 64 | 56 | 50 | 59 | 53 | 48 | 55 | 50 | 46 | 43 | | | | | | | | | | | | | | | | | | | |
| 4 | 75 | 62 | 52 | 44 | 72 | 60 | 51 | 44 | 56 | 48 | 42 | 52 | 45 | 40 | 49 | 43 | 38 | 36 | | | | | | | | | | | | | | | | | | | |
| 5 | 69 | 55 | 45 | 38 | 66 | 53 | 44 | 37 | 50 | 42 | 35 | 46 | 39 | 34 | 43 | 38 | 33 | 30 | | | | | | | | | | | | | | | | | | | |
| 6 | 63 | 49 | 39 | 32 | 61 | 47 | 38 | 32 | 44 | 36 | 31 | 42 | 35 | 29 | 39 | 33 | 28 | 26 | | | | | | | | | | | | | | | | | | | |
| 7 | 58 | 44 | 35 | 28 | 56 | 43 | 34 | 28 | 40 | 32 | 27 | 38 | 31 | 26 | 36 | 29 | 25 | 23 | | | | | | | | | | | | | | | | | | | |
| 8 | 54 | 40 | 31 | 25 | 52 | 39 | 30 | 24 | 37 | 29 | 24 | 34 | 28 | 23 | 32 | 26 | 22 | 20 | | | | | | | | | | | | | | | | | | | |
| 9 | 51 | 36 | 28 | 22 | 49 | 35 | 27 | 22 | 33 | 26 | 21 | 32 | 25 | 20 | 30 | 24 | 20 | 18 | | | | | | | | | | | | | | | | | | | |
| 10 | 47 | 33 | 25 | 20 | 45 | 33 | 25 | 19 | 31 | 24 | 19 | 29 | 23 | 18 | 28 | 22 | 18 | 16 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 90° | 180° |
|-----|------|------|------|
| 0° | 2525 | 2525 | 2525 |
| 5° | 2772 | 2488 | 2077 |
| 10° | 3138 | 2459 | 1712 |
| 15° | 3516 | 2427 | 1334 |
| 20° | 3966 | 2387 | 982 |
| 25° | 4338 | 2341 | 645 |
| 30° | 4615 | 2280 | 364 |
| 35° | 4856 | 2214 | 160 |
| 40° | 5068 | 2133 | 39 |
| 45° | 5251 | 2031 | 0 |
| 50° | 5404 | 1895 | 0 |
| 55° | 5521 | 1723 | 0 |
| 60° | 5579 | 1524 | 0 |
| 65° | 5602 | 1298 | 0 |
| 70° | 5584 | 1057 | 0 |
| 75° | 5513 | 780 | 4 |
| 80° | 5289 | 479 | 24 |
| 85° | 5113 | 229 | 33 |



TEST NUMBER: P550886

CATALOG NUMBER: FCC-X-2-LD4-1LO-50-UNV-80-97-ED1D

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 22.5 | 1.9 |
| 10°-20° | 67.3 | 5.8 |
| 20°-30° | 109.0 | 9.4 |
| 30°-40° | 140.0 | 12.1 |
| 40°-50° | 158.5 | 13.7 |
| 50°-60° | 164.2 | 14.2 |
| 60°-70° | 154.8 | 13.3 |
| 70°-80° | 129.8 | 11.2 |
| 80°-90° | 94.1 | 8.1 |
| 90°-100° | 61.8 | 5.3 |
| 100°-110° | 35.7 | 3.1 |
| 110°-120° | 15.8 | 1.4 |
| 120°-130° | 4.3 | 0.4 |
| 130°-140° | 1.0 | 0.1 |
| 140°-150° | 0.6 | 0.1 |
| 150°-160° | 0.5 | 0.0 |
| 160°-170° | 0.3 | 0.0 |
| 170°-180° | 0.1 | 0.0 |
| <hr/> | | |
| 0°-30° | 198.8 | 17.1 |
| 0°-40° | 338.7 | 29.2 |
| 0°-60° | 661.4 | 57.0 |
| 0°-90° | 1040.1 | 89.7 |
| 90°-120° | 113.3 | 9.8 |
| 90°-150° | 119.2 | 10.3 |
| 90°-180° | 120.0 | 10.3 |
| 0°-180° | 1160.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 45° | 90° | 135° | 180° | Flux |
|------|-----|-----|-----|------|------|------|
| 0° | 235 | 235 | 235 | 235 | 235 | |
| 5° | 268 | 257 | 233 | 211 | 201 | 27 |
| 15° | 358 | 314 | 225 | 163 | 136 | 103 |
| 25° | 450 | 368 | 209 | 107 | 67 | 208 |
| 35° | 499 | 397 | 183 | 52 | 16 | 313 |
| 45° | 517 | 393 | 150 | 12 | 0 | 399 |
| 55° | 504 | 368 | 108 | 0 | 0 | 450 |
| 65° | 456 | 326 | 65 | 0 | 0 | 451 |
| 75° | 380 | 263 | 28 | 0 | 0 | 398 |
| 85° | 278 | 191 | 4 | 1 | 2 | 237 |
| 90° | 241 | 153 | 1 | 2 | 2 | 132 |
| 95° | 207 | 119 | 1 | 2 | 3 | 162 |
| 105° | 142 | 62 | 1 | 2 | 2 | 150 |
| 115° | 77 | 20 | 1 | 1 | 2 | 78 |
| 125° | 23 | 3 | 1 | 1 | 1 | 23 |
| 135° | 1 | 1 | 2 | 1 | 1 | 2 |
| 145° | 0 | 1 | 1 | 1 | 1 | 0 |
| 155° | 1 | 1 | 1 | 1 | 0 | 0 |
| 165° | 1 | 1 | 1 | 1 | 0 | 0 |
| 175° | 1 | 1 | 2 | 1 | 0 | 0 |
| 180° | 1 | 1 | 1 | 1 | 1 | |



TEST NUMBER: P550886

CATALOG NUMBER: FCC-X-2-LD4-1LO-50-UNV-80-97-ED1D

CANDELA DISTRIBUTION (FULL):

| | 0° | 10° | 20° | 30° | 40° | 50° | 60° | 70° | 80° | 90° | 112.5° |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|--------|
| 0° | 234.6 | 234.6 | 234.6 | 234.6 | 234.6 | 234.6 | 234.6 | 234.6 | 234.6 | 234.6 | 234.6 |
| 2.5° | 254.4 | 254.1 | 253.2 | 251.7 | 249.6 | 246.0 | 243.0 | 240.3 | 236.7 | 233.7 | 228.1 |
| 5° | 267.8 | 266.3 | 265.1 | 263.6 | 258.9 | 255.6 | 250.2 | 244.2 | 238.5 | 232.8 | 221.5 |
| 7.5° | 289.3 | 286.9 | 285.2 | 281.0 | 274.4 | 266.9 | 258.6 | 252.9 | 249.0 | 233.1 | 213.7 |
| 10° | 312.4 | 310.3 | 306.7 | 299.2 | 291.1 | 280.4 | 268.4 | 255.0 | 243.0 | 229.9 | 206.8 |
| 12.5° | 335.1 | 332.1 | 327.0 | 317.4 | 306.1 | 292.6 | 276.2 | 260.3 | 243.3 | 227.8 | 198.8 |
| 15° | 357.8 | 354.5 | 349.1 | 337.5 | 322.5 | 304.9 | 284.9 | 264.8 | 244.8 | 225.1 | 190.4 |
| 17.5° | 382.6 | 378.1 | 370.0 | 356.9 | 338.1 | 316.2 | 292.6 | 268.4 | 244.2 | 221.8 | 181.4 |
| 20° | 409.2 | 402.9 | 394.3 | 376.6 | 354.5 | 328.8 | 300.4 | 272.0 | 243.9 | 217.9 | 171.3 |
| 22.5° | 431.3 | 425.0 | 415.5 | 397.2 | 370.6 | 339.3 | 307.0 | 274.4 | 242.7 | 213.4 | 161.7 |
| 25° | 450.4 | 445.4 | 434.9 | 414.0 | 385.9 | 350.3 | 313.3 | 276.2 | 240.9 | 208.6 | 151.5 |
| 27.5° | 465.4 | 460.6 | 449.0 | 427.4 | 398.7 | 360.2 | 318.0 | 277.1 | 238.5 | 203.9 | 141.1 |
| 30° | 478.5 | 473.8 | 459.7 | 437.6 | 407.4 | 368.0 | 322.8 | 277.4 | 235.5 | 196.7 | 129.7 |
| 32.5° | 488.7 | 484.2 | 469.9 | 446.3 | 413.4 | 373.3 | 325.5 | 277.1 | 231.7 | 191.6 | 117.5 |
| 35° | 498.9 | 494.4 | 477.6 | 452.5 | 417.9 | 375.7 | 327.6 | 275.6 | 226.9 | 183.2 | 105.8 |
| 37.5° | 506.6 | 501.6 | 484.5 | 456.7 | 420.0 | 376.3 | 327.3 | 273.5 | 221.8 | 176.4 | 94.2 |
| 40° | 512.0 | 506.6 | 488.4 | 459.1 | 420.6 | 375.4 | 324.9 | 269.9 | 215.8 | 167.7 | 81.9 |
| 42.5° | 515.6 | 509.6 | 490.2 | 462.7 | 419.4 | 373.0 | 321.3 | 265.4 | 209.2 | 160.2 | 70.2 |
| 45° | 517.4 | 511.1 | 490.5 | 459.7 | 417.3 | 368.5 | 315.9 | 259.7 | 202.1 | 150.1 | 58.6 |
| 47.5° | 516.5 | 509.6 | 489.0 | 456.4 | 413.4 | 363.8 | 310.0 | 252.9 | 193.4 | 141.1 | 47.5 |
| 50° | 515.0 | 507.8 | 485.7 | 452.2 | 408.0 | 357.8 | 303.4 | 244.5 | 184.4 | 130.0 | 37.7 |
| 52.5° | 510.2 | 503.1 | 482.1 | 446.3 | 401.7 | 350.9 | 294.4 | 235.8 | 174.9 | 119.3 | 28.7 |
| 55° | 504.3 | 497.7 | 475.9 | 440.9 | 393.7 | 342.5 | 286.1 | 226.6 | 165.6 | 108.2 | 20.6 |
| 57.5° | 495.0 | 489.0 | 468.1 | 432.2 | 385.6 | 333.3 | 276.8 | 216.4 | 153.9 | 97.1 | 14.3 |
| 60° | 483.6 | 477.6 | 457.3 | 422.4 | 376.3 | 322.8 | 266.6 | 205.9 | 143.5 | 86.1 | 9.0 |
| 62.5° | 471.7 | 466.0 | 444.8 | 410.1 | 364.7 | 311.8 | 255.6 | 195.5 | 132.4 | 75.9 | 5.4 |
| 65° | 455.8 | 450.4 | 431.3 | 395.5 | 351.8 | 299.8 | 243.3 | 182.9 | 121.1 | 64.6 | 3.0 |
| 67.5° | 439.1 | 434.3 | 414.9 | 382.0 | 336.9 | 286.6 | 230.8 | 170.7 | 109.1 | 54.7 | 1.5 |
| 70° | 421.2 | 415.2 | 397.2 | 363.8 | 321.6 | 271.7 | 217.0 | 158.1 | 97.7 | 45.1 | 0.0 |
| 72.5° | 400.2 | 395.7 | 378.4 | 346.7 | 304.0 | 255.9 | 203.0 | 144.4 | 85.2 | 35.9 | 0.3 |
| 75° | 379.9 | 374.2 | 358.4 | 328.5 | 286.6 | 239.1 | 187.4 | 131.5 | 72.9 | 27.5 | 0.3 |
| 77.5° | 353.6 | 351.8 | 336.9 | 307.9 | 270.2 | 223.0 | 170.4 | 116.0 | 61.3 | 19.7 | 0.3 |
| 80° | 327.3 | 325.5 | 313.8 | 287.2 | 251.1 | 203.9 | 154.5 | 101.3 | 49.9 | 13.2 | 0.3 |
| 82.5° | 301.3 | 298.9 | 287.8 | 265.7 | 231.7 | 187.7 | 138.1 | 86.7 | 39.5 | 8.1 | 0.3 |
| 85° | 278.0 | 275.0 | 263.0 | 242.7 | 211.6 | 169.5 | 121.1 | 72.3 | 29.3 | 4.5 | 0.6 |
| 87.5° | 258.0 | 255.9 | 242.7 | 221.8 | 191.3 | 152.4 | 106.1 | 58.6 | 20.6 | 2.1 | 0.9 |
| 90° | 240.9 | 236.4 | 224.8 | 202.7 | 172.2 | 133.6 | 90.3 | 46.9 | 13.7 | 1.2 | 1.2 |
| 92.5° | 224.2 | 220.3 | 207.4 | 184.7 | 155.1 | 117.5 | 75.0 | 35.9 | 8.7 | 0.6 | 1.5 |
| 95° | 206.8 | 202.7 | 190.1 | 169.2 | 137.8 | 101.0 | 61.6 | 26.3 | 4.8 | 0.6 | 1.5 |
| 97.5° | 189.8 | 185.9 | 172.8 | 151.8 | 122.3 | 86.7 | 48.7 | 18.5 | 2.4 | 0.6 | 1.2 |
| 100° | 174.0 | 169.5 | 157.5 | 136.6 | 106.7 | 72.3 | 37.7 | 12.0 | 1.5 | 0.6 | 1.2 |
| 102.5° | 157.2 | 153.6 | 141.4 | 121.1 | 90.6 | 58.9 | 28.1 | 7.5 | 0.6 | 0.6 | 0.9 |
| 105° | 142.3 | 137.8 | 125.8 | 104.9 | 77.1 | 46.3 | 19.7 | 4.5 | 0.6 | 0.6 | 0.9 |



TEST NUMBER: P550886

CATALOG NUMBER: FCC-X-2-LD4-1LO-50-UNV-80-97-ED1D

CANDELA DISTRIBUTION (continued):

| | 0° | 10° | 20° | 30° | 40° | 50° | 60° | 70° | 80° | 90° | 112.5° |
|--------|------|------|------|------|------|------|-----|-----|-----|-----|--------|
| 112.5° | 92.7 | 89.1 | 78.6 | 61.0 | 39.2 | 18.2 | 5.4 | 0.9 | 0.9 | 0.9 | 0.9 |
| 115° | 77.4 | 72.0 | 62.8 | 47.2 | 29.0 | 12.0 | 2.7 | 0.9 | 0.9 | 0.9 | 0.9 |
| 117.5° | 61.9 | 57.4 | 50.8 | 35.9 | 19.1 | 7.8 | 1.5 | 0.9 | 0.9 | 0.9 | 0.9 |
| 120° | 48.4 | 44.2 | 36.8 | 24.8 | 12.9 | 4.5 | 0.6 | 0.9 | 0.9 | 0.9 | 0.9 |
| 122.5° | 34.7 | 31.4 | 24.8 | 16.1 | 7.8 | 2.1 | 0.9 | 0.9 | 1.2 | 1.2 | 0.9 |
| 125° | 23.0 | 21.2 | 16.4 | 9.9 | 4.8 | 0.9 | 0.9 | 0.9 | 1.2 | 1.2 | 0.9 |
| 127.5° | 14.9 | 13.5 | 9.6 | 5.7 | 2.1 | 0.9 | 0.9 | 1.2 | 1.2 | 1.2 | 0.9 |
| 130° | 8.4 | 7.5 | 5.7 | 3.3 | 0.9 | 0.9 | 0.9 | 1.2 | 1.2 | 1.2 | 0.9 |
| 132.5° | 4.8 | 4.5 | 3.0 | 0.6 | 0.9 | 0.9 | 0.9 | 1.2 | 1.2 | 1.2 | 1.2 |
| 135° | 1.2 | 0.6 | 0.6 | 0.6 | 0.9 | 0.9 | 1.2 | 1.2 | 1.5 | 1.5 | 1.2 |
| 137.5° | 0.3 | 0.3 | 0.6 | 0.6 | 0.9 | 0.9 | 1.2 | 1.5 | 1.5 | 1.5 | 1.2 |
| 140° | 0.3 | 0.3 | 0.6 | 0.9 | 0.9 | 0.9 | 1.2 | 1.5 | 1.5 | 1.5 | 1.2 |
| 142.5° | 0.3 | 0.6 | 0.6 | 0.9 | 0.9 | 1.2 | 1.2 | 1.5 | 1.5 | 1.2 | 1.2 |
| 145° | 0.3 | 0.6 | 0.6 | 0.9 | 0.9 | 1.2 | 1.2 | 1.5 | 1.2 | 1.2 | 1.2 |
| 147.5° | 0.6 | 0.6 | 0.6 | 0.9 | 0.9 | 1.2 | 1.2 | 1.5 | 1.5 | 1.2 | 1.2 |
| 150° | 0.3 | 0.6 | 0.6 | 0.9 | 1.2 | 1.2 | 1.2 | 1.5 | 1.2 | 1.2 | 1.2 |
| 152.5° | 0.3 | 0.6 | 0.6 | 0.9 | 1.2 | 1.2 | 1.2 | 1.5 | 1.2 | 1.2 | 1.2 |
| 155° | 0.6 | 0.6 | 0.6 | 0.9 | 1.2 | 1.2 | 1.2 | 1.5 | 1.2 | 1.2 | 1.5 |
| 157.5° | 0.6 | 0.6 | 0.6 | 0.9 | 1.2 | 1.2 | 1.2 | 1.5 | 1.2 | 1.2 | 1.5 |
| 160° | 0.6 | 0.6 | 0.6 | 0.9 | 0.9 | 1.2 | 1.2 | 1.2 | 1.2 | 1.2 | 1.2 |
| 162.5° | 0.6 | 0.6 | 0.6 | 0.9 | 0.9 | 1.2 | 1.2 | 1.2 | 1.2 | 1.2 | 1.2 |
| 165° | 0.6 | 0.6 | 0.6 | 0.6 | 0.9 | 0.9 | 1.2 | 1.2 | 1.2 | 1.2 | 1.2 |
| 167.5° | 0.6 | 0.6 | 0.6 | 0.9 | 0.9 | 0.9 | 1.2 | 1.2 | 1.2 | 1.2 | 1.2 |
| 170° | 0.6 | 0.6 | 0.6 | 0.9 | 0.9 | 0.9 | 1.2 | 1.5 | 1.5 | 1.5 | 1.5 |
| 172.5° | 0.6 | 0.6 | 0.6 | 0.9 | 0.9 | 1.2 | 1.2 | 1.5 | 1.5 | 1.5 | 1.5 |
| 175° | 0.6 | 0.6 | 0.6 | 0.9 | 0.9 | 1.2 | 1.2 | 1.5 | 1.5 | 1.5 | 1.5 |
| 177.5° | 0.3 | 0.6 | 0.6 | 0.9 | 0.9 | 1.2 | 1.2 | 1.5 | 1.5 | 1.5 | 1.2 |
| 180° | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 |



TEST NUMBER: P550886

CATALOG NUMBER: FCC-X-2-LD4-1LO-50-UNV-80-97-ED1D

CANDELA DISTRIBUTION (continued):

| | 135° | 157.5° | 180° |
|--------|-------|--------|-------|
| 0° | 234.6 | 234.6 | 234.6 |
| 2.5° | 223.3 | 219.1 | 217.9 |
| 5° | 211.3 | 204.5 | 200.6 |
| 7.5° | 199.4 | 190.1 | 185.6 |
| 10° | 188.3 | 175.2 | 170.4 |
| 12.5° | 175.2 | 159.9 | 152.4 |
| 15° | 162.6 | 142.9 | 135.7 |
| 17.5° | 148.6 | 126.4 | 118.1 |
| 20° | 135.4 | 110.0 | 101.3 |
| 22.5° | 120.5 | 93.9 | 84.3 |
| 25° | 107.0 | 77.7 | 67.0 |
| 27.5° | 92.1 | 61.3 | 52.0 |
| 30° | 78.0 | 46.9 | 37.7 |
| 32.5° | 64.6 | 34.4 | 26.0 |
| 35° | 52.0 | 23.3 | 16.4 |
| 37.5° | 40.1 | 14.3 | 8.4 |
| 40° | 29.0 | 7.5 | 3.9 |
| 42.5° | 19.4 | 3.6 | 2.1 |
| 45° | 12.0 | 1.8 | 0.0 |
| 47.5° | 6.9 | 0.0 | 0.0 |
| 50° | 3.6 | 0.0 | 0.0 |
| 52.5° | 1.5 | 0.0 | 0.0 |
| 55° | 0.0 | 0.0 | 0.0 |
| 57.5° | 0.0 | 0.0 | 0.0 |
| 60° | 0.0 | 0.0 | 0.0 |
| 62.5° | 0.0 | 0.0 | 0.0 |
| 65° | 0.0 | 0.0 | 0.0 |
| 67.5° | 0.0 | 0.0 | 0.0 |
| 70° | 0.0 | 0.0 | 0.0 |
| 72.5° | 0.0 | 0.0 | 0.0 |
| 75° | 0.3 | 0.3 | 0.3 |
| 77.5° | 0.3 | 0.6 | 0.9 |
| 80° | 0.6 | 1.2 | 1.5 |
| 82.5° | 1.2 | 1.5 | 1.5 |
| 85° | 1.2 | 1.5 | 1.8 |
| 87.5° | 1.5 | 1.8 | 2.1 |
| 90° | 1.8 | 2.1 | 2.1 |
| 92.5° | 1.8 | 2.4 | 2.4 |
| 95° | 2.1 | 2.4 | 2.7 |
| 97.5° | 2.4 | 2.7 | 2.7 |
| 100° | 2.1 | 2.7 | 3.0 |
| 102.5° | 1.8 | 2.7 | 2.7 |
| 105° | 1.5 | 2.1 | 2.4 |



TEST NUMBER: P550886

CATALOG NUMBER: FCC-X-2-LD4-1LO-50-UNV-80-97-ED1D

CANDELA DISTRIBUTION (continued):

| | 135° | 157.5° | 180° |
|--------|------|--------|------|
| 112.5° | 1.2 | 1.5 | 1.5 |
| 115° | 0.9 | 1.2 | 1.5 |
| 117.5° | 0.9 | 1.2 | 1.2 |
| 120° | 0.9 | 0.9 | 1.2 |
| 122.5° | 0.9 | 0.9 | 1.2 |
| 125° | 0.9 | 0.9 | 1.2 |
| 127.5° | 1.2 | 0.9 | 0.9 |
| 130° | 0.9 | 0.9 | 0.9 |
| 132.5° | 1.2 | 0.9 | 0.9 |
| 135° | 1.2 | 0.9 | 0.9 |
| 137.5° | 1.2 | 0.9 | 0.9 |
| 140° | 1.2 | 0.9 | 0.9 |
| 142.5° | 1.2 | 0.9 | 0.9 |
| 145° | 0.9 | 0.9 | 0.9 |
| 147.5° | 0.9 | 0.9 | 0.9 |
| 150° | 0.9 | 0.9 | 0.6 |
| 152.5° | 0.9 | 0.6 | 0.6 |
| 155° | 0.9 | 0.6 | 0.3 |
| 157.5° | 1.2 | 0.6 | 0.3 |
| 160° | 0.9 | 0.6 | 0.3 |
| 162.5° | 0.9 | 0.6 | 0.3 |
| 165° | 0.9 | 0.6 | 0.0 |
| 167.5° | 0.9 | 0.6 | 0.3 |
| 170° | 0.9 | 0.6 | 0.3 |
| 172.5° | 0.9 | 0.6 | 0.3 |
| 175° | 0.9 | 0.3 | 0.3 |
| 177.5° | 0.9 | 0.3 | 0.3 |
| 180° | 0.9 | 0.9 | 0.9 |



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







| | | | | | | | | | | | |
|--------|-------|-------|-------|------|------|------|------|-----|-----|-----|-----|
| 107.5° | 125.5 | 122.0 | 110.0 | 90.3 | 63.1 | 35.3 | 13.2 | 2.4 | 0.6 | 0.9 | 0.9 |
| 110° | 109.4 | 106.4 | 94.2 | 75.0 | 50.8 | 26.3 | 8.7 | 1.5 | 0.9 | 0.9 | 0.9 |





| | | | |
|--------|-----|-----|-----|
| 107.5° | 1.2 | 1.8 | 2.1 |
| 110° | 1.2 | 1.5 | 1.8 |



(END OF REPORT)