

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P544667

Luminaire Tested: **FMR-12-1-LD4-1HI-35-UNV-80-88-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P544667
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-12-1-LD4-1HI-35-UNV-80-88-EDD
Description: 1X1 FMR TROFFER WITH .125 PRISMATIC ACRYLIC FIXTURE SIDE AND .500 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 695.0 lumens
Efficiency: N/A
Efficacy: 64.4 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
CIE Type: Direct

Input Watts (W): 10.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P544667

CATALOG NUMBER: FMR-12-1-LD4-1HI-35-UNV-80-88-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P544667

CATALOG NUMBER: FMR-12-1-LD4-1HI-35-UNV-80-88-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87																			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75																			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	47	72	61	53	47	59	52	47	57	51	47	56	50	46	44																			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33																			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3810	3810	3810
5°	3759	3755	3750
10°	3726	3722	3695
15°	3626	3589	3539
20°	3493	3436	3342
25°	3349	3277	3072
30°	3174	3072	2767
35°	3007	2840	2560
40°	2836	2588	2330
45°	2673	2393	2105
50°	2473	2220	1877
55°	2289	2012	1681
60°	2097	1798	1507
65°	1844	1574	1335
70°	1520	1378	1133
75°	1210	1056	1106
80°	812	762	713
85°	506	605	704



TEST NUMBER: P544667

CATALOG NUMBER: FMR-12-1-LD4-1HI-35-UNV-80-88-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.0	4.7
10°-20°	90.4	13.0
20°-30°	125.2	18.0
30°-40°	133.5	19.2
40°-50°	121.8	17.5
50°-60°	95.4	13.7
60°-70°	62.2	8.9
70°-80°	27.6	4.0
80°-90°	5.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	248.6	35.8
0°-40°	382.1	55.0
0°-60°	599.3	86.2
0°-90°	695.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	695.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	354	354	354	354	354	
5°	348	348	348	347	347	33
15°	325	325	322	319	318	91
25°	282	280	276	266	259	129
35°	229	227	216	200	195	143
45°	176	172	157	144	138	135
55°	122	118	107	94	90	109
65°	72	68	62	63	52	71
75°	29	27	25	24	27	31
85°	4	4	5	5	6	6
90°	0	0	0	0	0	



TEST NUMBER: P544667

CATALOG NUMBER: FMR-12-1-LD4-1HI-35-UNV-80-88-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	354.0	354.0	354.0	354.0	354.0
2.5°	351.6	351.6	351.6	351.2	351.2
5°	347.9	347.5	347.5	347.1	347.1
7.5°	345.0	344.6	344.2	343.8	343.0
10°	340.9	340.9	340.5	338.5	338.1
12.5°	334.4	334.0	332.3	329.5	328.6
15°	325.4	325.4	322.1	318.8	317.6
17.5°	315.6	315.1	311.0	307.8	306.1
20°	304.9	304.1	300.0	294.7	291.8
22.5°	293.0	293.0	288.1	281.2	278.3
25°	282.0	280.4	275.9	266.0	258.7
27.5°	269.3	266.8	261.9	248.0	239.4
30°	255.4	254.2	247.2	229.2	222.6
32.5°	242.3	240.2	232.9	214.1	208.7
35°	228.8	227.1	216.1	199.7	194.8
37.5°	215.3	213.2	199.3	186.2	180.1
40°	201.8	199.3	184.2	172.3	165.8
42.5°	189.1	185.8	171.1	158.4	151.0
45°	175.6	171.9	157.2	144.1	138.3
47.5°	162.1	158.8	145.3	131.8	125.2
50°	147.7	144.9	132.6	119.1	112.1
52.5°	135.9	131.4	119.5	106.0	100.3
55°	122.0	118.3	107.2	94.5	89.6
57.5°	109.3	105.6	95.4	83.5	79.4
60°	97.4	92.1	83.5	73.3	70.0
62.5°	84.3	80.2	72.9	64.3	68.3
65°	72.4	68.3	61.8	63.0	52.4
67.5°	59.3	57.3	51.6	45.8	44.2
70°	48.3	45.8	43.8	37.7	36.0
72.5°	38.5	36.0	33.2	29.9	28.6
75°	29.1	27.0	25.4	24.1	26.6
77.5°	20.1	19.2	18.0	16.8	16.4
80°	13.1	12.7	12.3	11.9	11.5
82.5°	7.8	7.8	7.8	7.8	7.8
85°	4.1	4.5	4.9	5.3	5.7
87.5°	2.5	2.5	2.9	3.3	3.7
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)