

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P544897

Luminaire Tested: **FMR-12-1-LD4-1STD-40-UNV-81-86-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P544897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-12-1-LD4-1STD-40-UNV-81-86-EDD
Description: 1X1 FMR TROFFER WITH .156 CLEAR PC FIXTURE SIDE AND .250 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 627.0 lumens
Efficiency: N/A
Efficacy: 75.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
CIE Type: Direct

Input Watts (W): 8.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P544897

CATALOG NUMBER: FMR-12-1-LD4-1STD-40-UNV-81-86-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P544897

CATALOG NUMBER: FMR-12-1-LD4-1STD-40-UNV-81-86-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87																			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75																			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44																			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33																			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3438	3438	3438
5°	3391	3387	3383
10°	3362	3358	3334
15°	3271	3238	3193
20°	3151	3100	3016
25°	3021	2956	2772
30°	2864	2772	2497
35°	2712	2562	2310
40°	2557	2335	2101
45°	2411	2159	1900
50°	2232	2003	1695
55°	2064	1815	1518
60°	1892	1621	1358
65°	1666	1421	1205
70°	1372	1243	1023
75°	1090	952	998
80°	731	688	638
85°	457	543	642



TEST NUMBER: P544897

CATALOG NUMBER: FMR-12-1-LD4-1STD-40-UNV-81-86-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.7	4.7
10°-20°	81.6	13.0
20°-30°	113.0	18.0
30°-40°	120.4	19.2
40°-50°	109.9	17.5
50°-60°	86.1	13.7
60°-70°	56.1	9.0
70°-80°	24.9	4.0
80°-90°	5.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	224.3	35.8
0°-40°	344.7	55.0
0°-60°	540.7	86.2
0°-90°	627.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	627.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	319	319	319	319	319	
5°	314	314	314	313	313	30
15°	294	294	291	288	286	83
25°	254	253	249	240	233	117
35°	206	205	195	180	176	129
45°	158	155	142	130	125	122
55°	110	107	97	85	81	99
65°	65	62	56	57	47	64
75°	26	24	23	22	24	28
85°	4	4	4	5	5	5
90°	0	0	0	0	0	



TEST NUMBER: P544897

CATALOG NUMBER: FMR-12-1-LD4-1STD-40-UNV-81-86-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	319.4	319.4	319.4	319.4	319.4
2.5°	317.2	317.2	317.2	316.8	316.8
5°	313.8	313.5	313.5	313.1	313.1
7.5°	311.3	310.9	310.5	310.2	309.4
10°	307.6	307.6	307.2	305.4	305.0
12.5°	301.7	301.3	299.8	297.2	296.5
15°	293.5	293.5	290.6	287.6	286.5
17.5°	284.7	284.3	280.6	277.7	276.2
20°	275.1	274.3	270.6	265.8	263.3
22.5°	264.4	264.4	259.9	253.7	251.1
25°	254.4	252.9	248.9	240.0	233.4
27.5°	243.0	240.7	236.3	223.8	216.0
30°	230.4	229.3	223.0	206.8	200.9
32.5°	218.6	216.7	210.1	193.1	188.3
35°	206.4	204.9	195.0	180.2	175.8
37.5°	194.2	192.4	179.8	168.0	162.5
40°	182.0	179.8	166.2	155.4	149.5
42.5°	170.6	167.6	154.3	142.9	136.2
45°	158.4	155.1	141.8	130.0	124.8
47.5°	146.2	143.3	131.1	118.9	113.0
50°	133.3	130.7	119.6	107.4	101.2
52.5°	122.6	118.5	107.8	95.6	90.5
55°	110.0	106.7	96.7	85.3	80.9
57.5°	98.6	95.3	86.0	75.3	71.6
60°	87.9	83.1	75.3	66.1	63.1
62.5°	76.1	72.4	65.7	58.0	61.7
65°	65.4	61.7	55.8	56.9	47.3
67.5°	53.5	51.7	46.5	41.4	39.9
70°	43.6	41.4	39.5	34.0	32.5
72.5°	34.7	32.5	29.9	27.0	25.8
75°	26.2	24.4	22.9	21.8	24.0
77.5°	18.1	17.4	16.2	15.1	14.8
80°	11.8	11.4	11.1	10.7	10.3
82.5°	7.0	7.0	7.0	7.0	7.0
85°	3.7	4.1	4.4	4.8	5.2
87.5°	2.2	2.2	2.6	3.0	3.3
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)