

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P544923

Luminaire Tested: **FMR-12-1-LD4-1STD-50-UNV-80-88-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P544923
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-12-1-LD4-1STD-50-UNV-80-88-EDD
Description: 1X1 FMR TROFFER WITH .125 PRISMATIC ACRYLIC FIXTURE SIDE AND .500 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 605.0 lumens
Efficiency: N/A
Efficacy: 72.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
CIE Type: Direct

Input Watts (W): 8.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P544923

CATALOG NUMBER: FMR-12-1-LD4-1STD-50-UNV-80-88-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P544923

CATALOG NUMBER: FMR-12-1-LD4-1STD-50-UNV-80-88-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87				87				
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75				75				
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65				65				
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56				56				
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50				50				
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44				44				
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40				40				
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36				36				
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33				33				
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30				30				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3317	3317	3317
5°	3272	3269	3264
10°	3244	3240	3217
15°	3156	3125	3081
20°	3040	2992	2909
25°	2916	2852	2675
30°	2763	2675	2409
35°	2618	2472	2229
40°	2467	2252	2028
45°	2326	2082	1833
50°	2153	1932	1634
55°	1993	1751	1464
60°	1826	1565	1311
65°	1607	1370	1161
70°	1322	1199	988
75°	1052	919	965
80°	707	663	620
85°	445	531	618



TEST NUMBER: P544923

CATALOG NUMBER: FMR-12-1-LD4-1STD-50-UNV-80-88-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.7	4.7
10°-20°	78.7	13.0
20°-30°	109.0	18.0
30°-40°	116.2	19.2
40°-50°	106.0	17.5
50°-60°	83.1	13.7
60°-70°	54.1	8.9
70°-80°	24.0	4.0
80°-90°	5.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	216.4	35.8
0°-40°	332.6	55.0
0°-60°	521.7	86.2
0°-90°	605.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	605.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	308	308	308	308	308	
5°	303	302	302	302	302	29
15°	283	283	280	278	276	80
25°	246	244	240	232	225	113
35°	199	198	188	174	170	125
45°	153	150	137	125	120	118
55°	106	103	93	82	78	95
65°	63	60	54	55	46	62
75°	25	24	22	21	23	27
85°	4	4	4	5	5	5
90°	0	0	0	0	0	



TEST NUMBER: P544923

CATALOG NUMBER: FMR-12-1-LD4-1STD-50-UNV-80-88-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	308.2	308.2	308.2	308.2	308.2
2.5°	306.0	306.0	306.0	305.7	305.7
5°	302.8	302.5	302.5	302.1	302.1
7.5°	300.3	300.0	299.6	299.3	298.6
10°	296.8	296.8	296.4	294.6	294.3
12.5°	291.1	290.7	289.3	286.8	286.1
15°	283.2	283.2	280.4	277.5	276.5
17.5°	274.7	274.3	270.8	267.9	266.5
20°	265.4	264.7	261.2	256.5	254.0
22.5°	255.1	255.1	250.8	244.8	242.3
25°	245.5	244.0	240.1	231.6	225.2
27.5°	234.4	232.3	228.0	215.9	208.4
30°	222.3	221.2	215.2	199.5	193.8
32.5°	210.9	209.1	202.7	186.3	181.7
35°	199.2	197.7	188.1	173.9	169.6
37.5°	187.4	185.6	173.5	162.1	156.8
40°	175.6	173.5	160.3	150.0	144.3
42.5°	164.6	161.7	148.9	137.9	131.5
45°	152.8	149.6	136.8	125.4	120.4
47.5°	141.1	138.2	126.5	114.7	109.0
50°	128.6	126.1	115.4	103.7	97.6
52.5°	118.3	114.4	104.0	92.3	87.3
55°	106.2	103.0	93.3	82.3	78.0
57.5°	95.1	91.9	83.0	72.7	69.1
60°	84.8	80.2	72.7	63.8	60.9
62.5°	73.4	69.8	63.4	55.9	59.5
65°	63.1	59.5	53.8	54.9	45.6
67.5°	51.7	49.9	44.9	39.9	38.5
70°	42.0	39.9	38.1	32.8	31.4
72.5°	33.5	31.4	28.9	26.0	24.9
75°	25.3	23.5	22.1	21.0	23.2
77.5°	17.5	16.7	15.7	14.6	14.3
80°	11.4	11.0	10.7	10.3	10.0
82.5°	6.8	6.8	6.8	6.8	6.8
85°	3.6	3.9	4.3	4.6	5.0
87.5°	2.1	2.1	2.5	2.9	3.2
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)