

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P544827

Luminaire Tested: **FMR-12-1-LD4-1LO-50-UNV-80-88-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P544827
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-12-1-LD4-1LO-50-UNV-80-88-EDD
Description: 1X1 FMR TROFFER WITH .125 PRISMATIC ACRYLIC FIXTURE SIDE AND .500 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 452.0 lumens
Efficiency: N/A
Efficacy: 77.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
CIE Type: Direct

Input Watts (W): 5.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P544827

CATALOG NUMBER: FMR-12-1-LD4-1LO-50-UNV-80-88-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P544827

CATALOG NUMBER: FMR-12-1-LD4-1LO-50-UNV-80-88-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87																			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75																			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44																			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33																			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2478	2478	2478
5°	2445	2442	2439
10°	2423	2421	2403
15°	2358	2335	2302
20°	2271	2235	2174
25°	2178	2131	1998
30°	2064	1999	1800
35°	1955	1846	1665
40°	1844	1683	1515
45°	1738	1556	1370
50°	1609	1443	1221
55°	1488	1308	1094
60°	1365	1169	980
65°	1200	1024	869
70°	988	897	736
75°	786	686	719
80°	527	496	465
85°	333	395	457



TEST NUMBER: P544827

CATALOG NUMBER: FMR-12-1-LD4-1LO-50-UNV-80-88-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.4	4.7
10°-20°	58.8	13.0
20°-30°	81.4	18.0
30°-40°	86.8	19.2
40°-50°	79.2	17.5
50°-60°	62.0	13.7
60°-70°	40.5	8.9
70°-80°	17.9	4.0
80°-90°	3.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	161.7	35.8
0°-40°	248.5	55.0
0°-60°	389.8	86.2
0°-90°	452.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	452.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	230	230	230	230	230	
5°	226	226	226	226	226	21
15°	212	212	210	207	207	59
25°	183	182	179	173	168	84
35°	149	148	140	130	127	93
45°	114	112	102	94	90	88
55°	79	77	70	62	58	71
65°	47	44	40	41	34	46
75°	19	18	16	16	17	20
85°	3	3	3	4	4	4
90°	0	0	0	0	0	



TEST NUMBER: P544827

CATALOG NUMBER: FMR-12-1-LD4-1LO-50-UNV-80-88-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	230.2	230.2	230.2	230.2	230.2
2.5°	228.6	228.6	228.6	228.4	228.4
5°	226.3	226.0	226.0	225.7	225.7
7.5°	224.4	224.1	223.9	223.6	223.1
10°	221.7	221.7	221.5	220.1	219.9
12.5°	217.5	217.2	216.1	214.3	213.7
15°	211.6	211.6	209.5	207.4	206.6
17.5°	205.2	205.0	202.3	200.2	199.1
20°	198.3	197.8	195.1	191.6	189.8
22.5°	190.6	190.6	187.4	182.9	181.0
25°	183.4	182.3	179.4	173.0	168.2
27.5°	175.1	173.5	170.4	161.3	155.7
30°	166.1	165.3	160.8	149.1	144.8
32.5°	157.6	156.2	151.5	139.2	135.8
35°	148.8	147.7	140.5	129.9	126.7
37.5°	140.0	138.7	129.6	121.1	117.1
40°	131.2	129.6	119.8	112.1	107.8
42.5°	123.0	120.8	111.3	103.0	98.2
45°	114.2	111.8	102.2	93.7	90.0
47.5°	105.4	103.3	94.5	85.7	81.5
50°	96.1	94.2	86.2	77.5	72.9
52.5°	88.4	85.4	77.7	68.9	65.2
55°	79.3	76.9	69.7	61.5	58.3
57.5°	71.1	68.7	62.0	54.3	51.6
60°	63.4	59.9	54.3	47.6	45.5
62.5°	54.8	52.2	47.4	41.8	44.5
65°	47.1	44.5	40.2	41.0	34.1
67.5°	38.6	37.3	33.5	29.8	28.7
70°	31.4	29.8	28.5	24.5	23.4
72.5°	25.0	23.4	21.6	19.4	18.6
75°	18.9	17.6	16.5	15.7	17.3
77.5°	13.0	12.5	11.7	10.9	10.6
80°	8.5	8.3	8.0	7.7	7.5
82.5°	5.1	5.1	5.1	5.1	5.1
85°	2.7	2.9	3.2	3.5	3.7
87.5°	1.6	1.6	1.9	2.1	2.4
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)