

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P545318

Luminaire Tested: **FMR-12-2-LD4-1HI-50-UNV-81-97-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P545318
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-12-2-LD4-1HI-50-UNV-81-97-EDD
Description: 1X2 FMR TROFFER WITH .156 CLEAR PC FIXTURE SIDE AND .375 CLEAR
TEMPERED GLASS ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1548.0 lumens
Efficiency: N/A
Efficacy: 71.7 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 21.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P545318

CATALOG NUMBER: FMR-12-2-LD4-1HI-50-UNV-81-97-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P545318

CATALOG NUMBER: FMR-12-2-LD4-1HI-50-UNV-81-97-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87																			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75																			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44																			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33																			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4244	4244	4244
5°	4186	4181	4176
10°	4150	4145	4115
15°	4038	3997	3942
20°	3889	3827	3723
25°	3730	3649	3421
30°	3535	3422	3082
35°	3348	3162	2851
40°	3157	2882	2594
45°	2977	2665	2345
50°	2756	2473	2092
55°	2549	2241	1873
60°	2336	2002	1678
65°	2055	1754	1486
70°	1693	1534	1262
75°	1345	1175	1233
80°	905	846	790
85°	562	673	790



TEST NUMBER: P545318

CATALOG NUMBER: FMR-12-2-LD4-1HI-50-UNV-81-97-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.4	4.7
10°-20°	201.4	13.0
20°-30°	278.9	18.0
30°-40°	297.4	19.2
40°-50°	271.3	17.5
50°-60°	212.5	13.7
60°-70°	138.5	8.9
70°-80°	61.4	4.0
80°-90°	13.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	553.7	35.8
0°-40°	851.1	55.0
0°-60°	1334.9	86.2
0°-90°	1548.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1548.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	788	788	788	788	788	
5°	775	774	774	773	773	74
15°	725	725	717	710	707	204
25°	628	624	614	592	576	288
35°	510	506	481	445	434	319
45°	391	383	350	321	308	301
55°	272	264	239	211	200	244
65°	161	152	138	140	117	159
75°	65	60	56	54	59	69
85°	9	10	11	12	13	13
90°	0	0	0	0	0	



TEST NUMBER: P545318

CATALOG NUMBER: FMR-12-2-LD4-1HI-50-UNV-81-97-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	788.5	788.5	788.5	788.5	788.5
2.5°	783.1	783.1	783.1	782.1	782.1
5°	774.9	773.9	773.9	773.0	773.0
7.5°	768.5	767.6	766.7	765.7	763.9
10°	759.4	759.4	758.4	753.9	753.0
12.5°	744.8	743.9	740.2	733.8	732.0
15°	724.7	724.7	717.4	710.1	707.4
17.5°	702.8	701.9	692.8	685.5	681.9
20°	679.1	677.3	668.2	656.3	650.0
22.5°	652.7	652.7	641.8	626.3	619.9
25°	628.1	624.4	614.4	592.5	576.1
27.5°	599.8	594.4	583.4	552.4	533.3
30°	568.8	566.1	550.6	510.5	495.9
32.5°	539.7	535.1	518.7	476.8	464.9
35°	509.6	505.9	481.3	444.9	433.9
37.5°	479.5	474.9	443.9	414.8	401.1
40°	449.4	443.9	410.2	383.8	369.2
42.5°	421.2	413.9	381.0	352.8	336.4
45°	391.1	382.9	350.1	320.9	308.1
47.5°	361.0	353.7	323.6	293.5	278.9
50°	329.1	322.7	295.4	265.3	249.8
52.5°	302.6	292.6	266.2	236.1	223.3
55°	271.7	263.5	238.8	210.6	199.6
57.5°	243.4	235.2	212.4	186.0	176.8
60°	217.0	205.1	186.0	163.2	155.9
62.5°	187.8	178.7	162.3	143.1	152.2
65°	161.4	152.2	137.7	140.4	116.7
67.5°	132.2	127.6	114.9	102.1	98.5
70°	107.6	102.1	97.5	83.9	80.2
72.5°	85.7	80.2	73.8	66.5	63.8
75°	64.7	60.2	56.5	53.8	59.3
77.5°	44.7	42.8	40.1	37.4	36.5
80°	29.2	28.3	27.3	26.4	25.5
82.5°	17.3	17.3	17.3	17.3	17.3
85°	9.1	10.0	10.9	11.9	12.8
87.5°	5.5	5.5	6.4	7.3	8.2
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)