

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P545425

Luminaire Tested: **FMR-12-2-LD4-1LO-50-UNV-93-86-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P545425
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-12-2-LD4-1LO-50-UNV-93-86-EDD
Description: 1X2 FMR TROFFER WITH .156 CLEAR TEMPERED GLASS FIXTURE SIDE AND .250 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1008.0 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P545425

CATALOG NUMBER: FMR-12-2-LD4-1LO-50-UNV-93-86-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P545425

CATALOG NUMBER: FMR-12-2-LD4-1LO-50-UNV-93-86-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87																			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75																			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44																			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33																			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2764	2764	2764
5°	2726	2723	2720
10°	2702	2699	2679
15°	2629	2603	2566
20°	2533	2492	2424
25°	2429	2376	2228
30°	2302	2228	2007
35°	2180	2059	1857
40°	2056	1877	1689
45°	1939	1735	1527
50°	1794	1610	1361
55°	1660	1459	1220
60°	1521	1304	1093
65°	1338	1141	968
70°	1102	999	821
75°	875	765	803
80°	589	552	514
85°	364	438	513



TEST NUMBER: P545425

CATALOG NUMBER: FMR-12-2-LD4-1LO-50-UNV-93-86-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.8	4.7
10°-20°	131.2	13.0
20°-30°	181.6	18.0
30°-40°	193.6	19.2
40°-50°	176.6	17.5
50°-60°	138.4	13.7
60°-70°	90.2	8.9
70°-80°	40.0	4.0
80°-90°	8.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	360.6	35.8
0°-40°	554.2	55.0
0°-60°	869.2	86.2
0°-90°	1008.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1008.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	514	514	514	514	514	
5°	505	504	504	503	503	48
15°	472	472	467	462	461	133
25°	409	407	400	386	375	188
35°	332	329	313	290	283	207
45°	255	249	228	209	201	196
55°	177	172	156	137	130	159
65°	105	99	90	91	76	104
75°	42	39	37	35	39	45
85°	6	6	7	8	8	8
90°	0	0	0	0	0	



TEST NUMBER: P545425

CATALOG NUMBER: FMR-12-2-LD4-1LO-50-UNV-93-86-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	513.5	513.5	513.5	513.5	513.5
2.5°	509.9	509.9	509.9	509.3	509.3
5°	504.6	504.0	504.0	503.4	503.4
7.5°	500.4	499.8	499.2	498.6	497.4
10°	494.5	494.5	493.9	490.9	490.3
12.5°	485.0	484.4	482.0	477.8	476.7
15°	471.9	471.9	467.2	462.4	460.6
17.5°	457.7	457.1	451.1	446.4	444.0
20°	442.2	441.0	435.1	427.4	423.2
22.5°	425.0	425.0	417.9	407.8	403.6
25°	409.0	406.6	400.1	385.8	375.2
27.5°	390.6	387.0	379.9	359.7	347.3
30°	370.4	368.6	358.5	332.4	322.9
32.5°	351.4	348.4	337.8	310.5	302.7
35°	331.8	329.4	313.4	289.7	282.6
37.5°	312.2	309.3	289.1	270.1	261.2
40°	292.6	289.1	267.1	249.9	240.4
42.5°	274.2	269.5	248.1	229.7	219.0
45°	254.7	249.3	227.9	208.9	200.6
47.5°	235.1	230.3	210.7	191.1	181.6
50°	214.3	210.1	192.3	172.7	162.6
52.5°	197.1	190.5	173.3	153.7	145.4
55°	176.9	171.5	155.5	137.1	130.0
57.5°	158.5	153.1	138.3	121.1	115.2
60°	141.3	133.6	121.1	106.3	101.5
62.5°	122.3	116.3	105.7	93.2	99.1
65°	105.1	99.1	89.6	91.4	76.0
67.5°	86.1	83.1	74.8	66.5	64.1
70°	70.0	66.5	63.5	54.6	52.2
72.5°	55.8	52.2	48.1	43.3	41.6
75°	42.1	39.2	36.8	35.0	38.6
77.5°	29.1	27.9	26.1	24.3	23.7
80°	19.0	18.4	17.8	17.2	16.6
82.5°	11.3	11.3	11.3	11.3	11.3
85°	5.9	6.5	7.1	7.7	8.3
87.5°	3.6	3.6	4.2	4.7	5.3
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)