

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P545404

Luminaire Tested: **FMR-12-2-LD4-1LO-50-UNV-80-94-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P545404  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/15/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FMR-12-2-LD4-1LO-50-UNV-80-94-EDD  
Description: 1X2 FMR TROFFER WITH .125 PRISMATIC ACRYLIC FIXTURE SIDE AND .187 CLEAR TEMPERED GLASS ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 5000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1040.0 lumens  
Efficiency: N/A  
Efficacy: 88.9 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15  
Luminous Opening: Rectangular (W 1' x L: 2' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P545404

CATALOG NUMBER: FMR-12-2-LD4-1LO-50-UNV-80-94-EDD

### Luminous Intensity Polar Plot





TEST NUMBER: P545404

CATALOG NUMBER: FMR-12-2-LD4-1LO-50-UNV-80-94-EDD

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87																			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75																			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44																			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33																			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2851	2851	2851
5°	2813	2809	2806
10°	2788	2785	2765
15°	2713	2686	2648
20°	2613	2571	2501
25°	2506	2451	2299
30°	2375	2299	2071
35°	2250	2125	1915
40°	2121	1936	1742
45°	1999	1790	1576
50°	1851	1661	1405
55°	1712	1506	1258
60°	1569	1344	1127
65°	1380	1178	998
70°	1138	1031	848
75°	905	790	828
80°	607	570	530
85°	377	451	531



TEST NUMBER: P545404

CATALOG NUMBER: FMR-12-2-LD4-1LO-50-UNV-80-94-EDD

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.3	4.7
10°-20°	135.3	13.0
20°-30°	187.4	18.0
30°-40°	199.8	19.2
40°-50°	182.3	17.5
50°-60°	142.8	13.7
60°-70°	93.1	8.9
70°-80°	41.2	4.0
80°-90°	8.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	372.0	35.8
0°-40°	571.8	55.0
0°-60°	896.9	86.2
0°-90°	1040.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1040.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	530	530	530	530	530	
5°	521	520	520	519	519	49
15°	487	487	482	477	475	137
25°	422	420	413	398	387	194
35°	342	340	323	299	292	214
45°	263	257	235	216	207	202
55°	182	177	160	142	134	164
65°	108	102	92	94	78	107
75°	44	40	38	36	40	47
85°	6	7	7	8	9	8
90°	0	0	0	0	0	



TEST NUMBER: P545404

CATALOG NUMBER: FMR-12-2-LD4-1LO-50-UNV-80-94-EDD

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	529.8	529.8	529.8	529.8	529.8
2.5°	526.1	526.1	526.1	525.5	525.5
5°	520.6	520.0	520.0	519.4	519.4
7.5°	516.3	515.7	515.1	514.5	513.2
10°	510.2	510.2	509.6	506.5	505.9
12.5°	500.4	499.8	497.3	493.0	491.8
15°	486.9	486.9	482.0	477.1	475.3
17.5°	472.2	471.6	465.5	460.6	458.1
20°	456.3	455.0	448.9	441.0	436.7
22.5°	438.5	438.5	431.2	420.7	416.5
25°	422.0	419.5	412.8	398.1	387.1
27.5°	403.0	399.3	392.0	371.1	358.3
30°	382.2	380.3	369.9	343.0	333.2
32.5°	362.6	359.5	348.5	320.3	312.3
35°	342.4	339.9	323.4	298.9	291.5
37.5°	322.1	319.1	298.3	278.7	269.5
40°	301.9	298.3	275.6	257.8	248.0
42.5°	282.9	278.0	256.0	237.0	226.0
45°	262.7	257.2	235.2	215.6	207.0
47.5°	242.5	237.6	217.4	197.2	187.4
50°	221.1	216.8	198.4	178.2	167.8
52.5°	203.3	196.6	178.8	158.6	150.0
55°	182.5	177.0	160.5	141.5	134.1
57.5°	163.5	158.0	142.7	124.9	118.8
60°	145.8	137.8	124.9	109.6	104.7
62.5°	126.2	120.0	109.0	96.2	102.3
65°	108.4	102.3	92.5	94.3	78.4
67.5°	88.8	85.7	77.2	68.6	66.1
70°	72.3	68.6	65.5	56.3	53.9
72.5°	57.6	53.9	49.6	44.7	42.9
75°	43.5	40.4	38.0	36.1	39.8
77.5°	30.0	28.8	26.9	25.1	24.5
80°	19.6	19.0	18.4	17.8	17.1
82.5°	11.6	11.6	11.6	11.6	11.6
85°	6.1	6.7	7.3	8.0	8.6
87.5°	3.7	3.7	4.3	4.9	5.5
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°    - - 45°-225°    - - - - 90°-270°







(END OF REPORT)