

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P545519

Luminaire Tested: **FMR-12-2-LD4-1STD-50-UNV-93-84-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P545519
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-12-2-LD4-1STD-50-UNV-93-84-EDD
Description: 1X2 FMR TROFFER WITH .156 CLEAR TEMPERED GLASS FIXTURE SIDE AND .125 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1392.0 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 16.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P545519

CATALOG NUMBER: FMR-12-2-LD4-1STD-50-UNV-93-84-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P545519

CATALOG NUMBER: FMR-12-2-LD4-1STD-50-UNV-93-84-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87																			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75																			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44																			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33																			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3816	3816	3816
5°	3764	3760	3755
10°	3731	3727	3700
15°	3631	3594	3544
20°	3498	3442	3348
25°	3354	3281	3077
30°	3179	3077	2771
35°	3010	2844	2564
40°	2839	2592	2333
45°	2677	2396	2109
50°	2478	2224	1881
55°	2292	2016	1684
60°	2100	1800	1509
65°	1848	1577	1336
70°	1522	1380	1135
75°	1210	1056	1108
80°	812	762	713
85°	506	605	710



TEST NUMBER: P545519

CATALOG NUMBER: FMR-12-2-LD4-1STD-50-UNV-93-84-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.0	4.7
10°-20°	181.1	13.0
20°-30°	250.8	18.0
30°-40°	267.4	19.2
40°-50°	244.0	17.5
50°-60°	191.1	13.7
60°-70°	124.6	8.9
70°-80°	55.2	4.0
80°-90°	11.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	497.9	35.8
0°-40°	765.3	55.0
0°-60°	1200.4	86.2
0°-90°	1392.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1392.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	709	709	709	709	709	
5°	697	696	696	695	695	66
15°	652	652	645	639	636	183
25°	565	562	552	533	518	259
35°	458	455	433	400	390	286
45°	352	344	315	288	277	271
55°	244	237	215	189	180	219
65°	145	137	124	126	105	143
75°	58	54	51	48	53	62
85°	8	9	10	11	12	11
90°	0	0	0	0	0	



TEST NUMBER: P545519

CATALOG NUMBER: FMR-12-2-LD4-1STD-50-UNV-93-84-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	709.1	709.1	709.1	709.1	709.1
2.5°	704.1	704.1	704.1	703.3	703.3
5°	696.8	696.0	696.0	695.1	695.1
7.5°	691.0	690.2	689.4	688.6	686.9
10°	682.8	682.8	682.0	677.9	677.1
12.5°	669.7	668.9	665.6	659.9	658.2
15°	651.7	651.7	645.1	638.6	636.1
17.5°	632.0	631.2	623.0	616.4	613.2
20°	610.7	609.1	600.9	590.2	584.5
22.5°	586.9	586.9	577.1	563.2	557.4
25°	564.8	561.5	552.5	532.8	518.1
27.5°	539.4	534.5	524.6	496.8	479.5
30°	511.5	509.1	495.1	459.0	445.9
32.5°	485.3	481.2	466.4	428.7	418.1
35°	458.2	454.9	432.8	400.0	390.2
37.5°	431.2	427.1	399.2	373.0	360.7
40°	404.1	399.2	368.9	345.1	332.0
42.5°	378.7	372.2	342.6	317.2	302.5
45°	351.7	344.3	314.8	288.5	277.1
47.5°	324.6	318.1	291.0	264.0	250.8
50°	295.9	290.2	265.6	238.5	224.6
52.5°	272.2	263.1	239.4	212.3	200.8
55°	244.3	236.9	214.8	189.4	179.5
57.5°	218.9	211.5	191.0	167.2	159.0
60°	195.1	184.4	167.2	146.7	140.2
62.5°	168.9	160.7	145.9	128.7	136.9
65°	145.1	136.9	123.8	126.2	104.9
67.5°	118.9	114.8	103.3	91.8	88.5
70°	96.7	91.8	87.7	75.4	72.1
72.5°	77.1	72.1	66.4	59.8	57.4
75°	58.2	54.1	50.8	48.4	53.3
77.5°	40.2	38.5	36.1	33.6	32.8
80°	26.2	25.4	24.6	23.8	23.0
82.5°	15.6	15.6	15.6	15.6	15.6
85°	8.2	9.0	9.8	10.7	11.5
87.5°	4.9	4.9	5.7	6.6	7.4
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)