

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P545510

Luminaire Tested: **FMR-12-2-LD4-1STD-50-UNV-81-97-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P545510
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-12-2-LD4-1STD-50-UNV-81-97-EDD
Description: 1X2 FMR TROFFER WITH .156 CLEAR PC FIXTURE SIDE AND .375 CLEAR
TEMPERED GLASS ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1262.0 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 16.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P545510

CATALOG NUMBER: FMR-12-2-LD4-1STD-50-UNV-81-97-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P545510

CATALOG NUMBER: FMR-12-2-LD4-1STD-50-UNV-81-97-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87				87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75				75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65				65
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56				56
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50				50
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44				44
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40				40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36				36
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33				33
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30				30

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3460	3460	3460
5°	3413	3409	3405
10°	3383	3379	3355
15°	3292	3259	3213
20°	3171	3120	3035
25°	3040	2975	2789
30°	2882	2790	2513
35°	2729	2578	2325
40°	2574	2349	2115
45°	2426	2172	1912
50°	2246	2016	1705
55°	2078	1827	1528
60°	1904	1632	1368
65°	1675	1429	1211
70°	1380	1251	1029
75°	1098	959	1004
80°	738	691	645
85°	457	550	642



TEST NUMBER: P545510

CATALOG NUMBER: FMR-12-2-LD4-1STD-50-UNV-81-97-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.8	4.7
10°-20°	164.2	13.0
20°-30°	227.4	18.0
30°-40°	242.4	19.2
40°-50°	221.2	17.5
50°-60°	173.3	13.7
60°-70°	112.9	8.9
70°-80°	50.0	4.0
80°-90°	10.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	451.4	35.8
0°-40°	693.9	55.0
0°-60°	1088.3	86.2
0°-90°	1262.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1262.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	643	643	643	643	643	
5°	632	631	631	630	630	60
15°	591	591	585	579	577	166
25°	512	509	501	483	470	235
35°	415	412	392	363	354	260
45°	319	312	285	262	251	246
55°	222	215	195	172	163	199
65°	132	124	112	114	95	130
75°	53	49	46	44	48	57
85°	7	8	9	10	10	10
90°	0	0	0	0	0	



TEST NUMBER: P545510

CATALOG NUMBER: FMR-12-2-LD4-1STD-50-UNV-81-97-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	642.8	642.8	642.8	642.8	642.8
2.5°	638.4	638.4	638.4	637.6	637.6
5°	631.7	631.0	631.0	630.2	630.2
7.5°	626.5	625.8	625.0	624.3	622.8
10°	619.1	619.1	618.3	614.6	613.9
12.5°	607.2	606.4	603.5	598.3	596.8
15°	590.8	590.8	584.9	578.9	576.7
17.5°	573.0	572.2	564.8	558.9	555.9
20°	553.7	552.2	544.7	535.1	529.9
22.5°	532.1	532.1	523.2	510.6	505.4
25°	512.0	509.1	500.9	483.1	469.7
27.5°	489.0	484.5	475.6	450.4	434.8
30°	463.7	461.5	448.9	416.2	404.3
32.5°	440.0	436.2	422.9	388.7	379.0
35°	415.4	412.5	392.4	362.7	353.8
37.5°	390.9	387.2	361.9	338.1	327.0
40°	366.4	361.9	334.4	312.9	301.0
42.5°	343.3	337.4	310.6	287.6	274.2
45°	318.8	312.1	285.4	261.6	251.2
47.5°	294.3	288.4	263.8	239.3	227.4
50°	268.3	263.1	240.8	216.3	203.6
52.5°	246.7	238.6	217.0	192.5	182.1
55°	221.5	214.8	194.7	171.7	162.8
57.5°	198.4	191.7	173.2	151.6	144.2
60°	176.9	167.2	151.6	133.0	127.1
62.5°	153.1	145.7	132.3	116.7	124.1
65°	131.5	124.1	112.2	114.4	95.1
67.5°	107.8	104.0	93.6	83.2	80.3
70°	87.7	83.2	79.5	68.4	65.4
72.5°	69.9	65.4	60.2	54.3	52.0
75°	52.8	49.0	46.1	43.8	48.3
77.5°	36.4	34.9	32.7	30.5	29.7
80°	23.8	23.0	22.3	21.6	20.8
82.5°	14.1	14.1	14.1	14.1	14.1
85°	7.4	8.2	8.9	9.7	10.4
87.5°	4.5	4.5	5.2	5.9	6.7
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)