

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P545879

Luminaire Tested: **FMR-12-4-LD4-1HI-50-UNV-80-84-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P545879  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/15/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FMR-12-4-LD4-1HI-50-UNV-80-84-EDD  
Description: 1X4 FMR TROFFER WITH .125 PRISMATIC ACRYLIC FIXTURE SIDE AND .125 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 5000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3712.0 lumens  
Efficiency: N/A  
Efficacy: 85.9 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15  
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 43.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P545879

CATALOG NUMBER: FMR-12-4-LD4-1HI-50-UNV-80-84-EDD

### Luminous Intensity Polar Plot





TEST NUMBER: P545879

CATALOG NUMBER: FMR-12-4-LD4-1HI-50-UNV-80-84-EDD

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87																			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75																			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44																			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33																			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5088	5088	5088
5°	5019	5013	5007
10°	4976	4970	4934
15°	4841	4793	4726
20°	4664	4588	4463
25°	4472	4374	4102
30°	4238	4103	3695
35°	4014	3792	3418
40°	3786	3456	3110
45°	3569	3194	2812
50°	3304	2965	2507
55°	3056	2687	2246
60°	2800	2400	2012
65°	2464	2102	1782
70°	2029	1840	1514
75°	1614	1409	1477
80°	1085	1017	948
85°	676	809	945



TEST NUMBER: P545879

CATALOG NUMBER: FMR-12-4-LD4-1HI-50-UNV-80-84-EDD

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.0	4.7
10°-20°	483.0	13.0
20°-30°	668.7	18.0
30°-40°	713.1	19.2
40°-50°	650.5	17.5
50°-60°	509.6	13.7
60°-70°	332.2	8.9
70°-80°	147.2	4.0
80°-90°	31.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1327.8	35.8
0°-40°	2040.9	55.0
0°-60°	3201.1	86.2
0°-90°	3712.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3712.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1891	1891	1891	1891	1891	
5°	1858	1856	1856	1854	1854	176
15°	1738	1738	1720	1703	1696	489
25°	1506	1497	1473	1421	1382	691
35°	1222	1213	1154	1067	1040	764
45°	938	918	839	770	739	722
55°	651	632	573	505	479	584
65°	387	365	330	337	280	381
75°	155	144	136	129	142	166
85°	22	24	26	28	31	30
90°	0	0	0	0	0	



TEST NUMBER: P545879

CATALOG NUMBER: FMR-12-4-LD4-1HI-50-UNV-80-84-EDD

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1890.8	1890.8	1890.8	1890.8	1890.8
2.5°	1877.7	1877.7	1877.7	1875.5	1875.5
5°	1858.1	1855.9	1855.9	1853.7	1853.7
7.5°	1842.8	1840.6	1838.4	1836.2	1831.8
10°	1820.9	1820.9	1818.7	1807.8	1805.6
12.5°	1785.9	1783.7	1775.0	1759.7	1755.3
15°	1737.8	1737.8	1720.3	1702.9	1696.3
17.5°	1685.4	1683.2	1661.3	1643.8	1635.1
20°	1628.5	1624.2	1602.3	1573.9	1558.6
22.5°	1565.1	1565.1	1538.9	1501.7	1486.4
25°	1506.1	1497.4	1473.3	1420.9	1381.5
27.5°	1438.4	1425.2	1399.0	1324.7	1278.8
30°	1364.0	1357.5	1320.3	1224.1	1189.2
32.5°	1294.1	1283.2	1243.8	1143.2	1114.8
35°	1221.9	1213.2	1154.2	1066.7	1040.5
37.5°	1149.8	1138.9	1064.6	994.6	961.8
40°	1077.7	1064.6	983.7	920.3	885.3
42.5°	1009.9	992.4	913.7	846.0	806.6
45°	937.8	918.1	839.4	769.5	738.8
47.5°	865.6	848.1	776.0	703.9	668.9
50°	789.1	773.8	708.2	636.1	598.9
52.5°	725.7	701.7	638.3	566.2	535.6
55°	651.4	631.7	572.7	505.0	478.7
57.5°	583.6	564.0	509.3	445.9	424.1
60°	520.3	491.8	445.9	391.3	373.8
62.5°	450.3	428.4	389.1	343.2	365.1
65°	386.9	365.1	330.1	336.6	279.8
67.5°	317.0	306.0	275.4	244.8	236.1
70°	257.9	244.8	233.9	201.1	192.4
72.5°	205.5	192.4	177.1	159.6	153.0
75°	155.2	144.3	135.5	129.0	142.1
77.5°	107.1	102.7	96.2	89.6	87.4
80°	70.0	67.8	65.6	63.4	61.2
82.5°	41.5	41.5	41.5	41.5	41.5
85°	21.9	24.0	26.2	28.4	30.6
87.5°	13.1	13.1	15.3	17.5	19.7
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°    - - 45°-225°    - - - - 90°-270°







(END OF REPORT)