

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P546466

Luminaire Tested: **FMR-24-4-LD4-1HI-40-UNV-81-87-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P546466
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-24-4-LD4-1HI-40-UNV-81-87-EDD
Description: 2X4 FMR TROFFER WITH .156 CLEAR PC FIXTURE SIDE AND .375 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3689.0 lumens
Efficiency: N/A
Efficacy: 85.4 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 43.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P546466

CATALOG NUMBER: FMR-24-4-LD4-1HI-40-UNV-81-87-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P546466

CATALOG NUMBER: FMR-24-4-LD4-1HI-40-UNV-81-87-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87				87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75				75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65				65
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56				56
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50				50
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44				44
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40				40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36				36
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33				33
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30				30

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2528	2528	2528
5°	2494	2491	2488
10°	2472	2469	2452
15°	2406	2382	2348
20°	2317	2280	2218
25°	2222	2174	2038
30°	2106	2039	1836
35°	1995	1884	1699
40°	1881	1717	1545
45°	1773	1587	1397
50°	1641	1473	1246
55°	1519	1335	1116
60°	1391	1193	1000
65°	1224	1044	885
70°	1008	914	752
75°	802	700	734
80°	539	505	471
85°	335	403	469



TEST NUMBER: P546466

CATALOG NUMBER: FMR-24-4-LD4-1HI-40-UNV-81-87-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.9	4.7
10°-20°	480.1	13.0
20°-30°	664.6	18.0
30°-40°	708.7	19.2
40°-50°	646.5	17.5
50°-60°	506.5	13.7
60°-70°	330.1	8.9
70°-80°	146.3	4.0
80°-90°	31.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1319.6	35.8
0°-40°	2028.3	55.0
0°-60°	3181.3	86.2
0°-90°	3689.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3689.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1879	1879	1879	1879	1879	
5°	1846	1844	1844	1842	1842	175
15°	1727	1727	1710	1692	1686	486
25°	1497	1488	1464	1412	1373	687
35°	1214	1206	1147	1060	1034	759
45°	932	912	834	765	734	718
55°	647	628	569	502	476	581
65°	384	363	328	334	278	379
75°	154	143	135	128	141	165
85°	22	24	26	28	30	30
90°	0	0	0	0	0	



TEST NUMBER: P546466

CATALOG NUMBER: FMR-24-4-LD4-1HI-40-UNV-81-87-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1879.1	1879.1	1879.1	1879.1	1879.1
2.5°	1866.1	1866.1	1866.1	1863.9	1863.9
5°	1846.5	1844.4	1844.4	1842.2	1842.2
7.5°	1831.3	1829.2	1827.0	1824.8	1820.5
10°	1809.6	1809.6	1807.4	1796.6	1794.4
12.5°	1774.9	1772.7	1764.0	1748.8	1744.4
15°	1727.1	1727.1	1709.7	1692.3	1685.8
17.5°	1674.9	1672.7	1651.0	1633.6	1625.0
20°	1618.4	1614.1	1592.4	1564.1	1548.9
22.5°	1555.4	1555.4	1529.4	1492.4	1477.2
25°	1496.8	1488.1	1464.2	1412.1	1373.0
27.5°	1429.4	1416.4	1390.3	1316.5	1270.9
30°	1355.6	1349.1	1312.1	1216.5	1181.8
32.5°	1286.1	1275.2	1236.1	1136.2	1107.9
35°	1214.4	1205.7	1147.0	1060.1	1034.1
37.5°	1142.7	1131.8	1058.0	988.4	955.9
40°	1071.0	1058.0	977.6	914.6	879.8
42.5°	1003.6	986.3	908.1	840.7	801.6
45°	932.0	912.4	834.2	764.7	734.3
47.5°	860.3	842.9	771.2	699.5	664.8
50°	784.2	769.0	703.9	632.2	595.2
52.5°	721.2	697.3	634.3	562.7	532.2
55°	647.4	627.8	569.2	501.8	475.8
57.5°	580.0	560.5	506.2	443.2	421.4
60°	517.0	488.8	443.2	388.9	371.5
62.5°	447.5	425.8	386.7	341.1	362.8
65°	384.5	362.8	328.0	334.5	278.1
67.5°	315.0	304.1	273.7	243.3	234.6
70°	256.3	243.3	232.4	199.9	191.2
72.5°	204.2	191.2	176.0	158.6	152.1
75°	154.2	143.4	134.7	128.2	141.2
77.5°	106.4	102.1	95.6	89.1	86.9
80°	69.5	67.3	65.2	63.0	60.8
82.5°	41.3	41.3	41.3	41.3	41.3
85°	21.7	23.9	26.1	28.2	30.4
87.5°	13.0	13.0	15.2	17.4	19.6
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)