

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P546951

Luminaire Tested: **FMR-24-4-LD4-2STD-50-UNV-82-84-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P546951
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-24-4-LD4-2STD-50-UNV-82-84-EDD
Description: 2X4 FMR TROFFER WITH .187 CLEAR PC FIXTURE SIDE AND .125 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6613.0 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P546951

CATALOG NUMBER: FMR-24-4-LD4-2STD-50-UNV-82-84-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P546951

CATALOG NUMBER: FMR-24-4-LD4-2STD-50-UNV-82-84-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87				87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75				75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65				65
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56				56
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50				50
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44				44
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40				40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36				36
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33				33
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30				30

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4532	4532	4532
5°	4471	4466	4460
10°	4432	4427	4395
15°	4313	4269	4210
20°	4154	4087	3976
25°	3983	3897	3654
30°	3775	3654	3291
35°	3576	3377	3045
40°	3372	3078	2770
45°	3179	2845	2505
50°	2943	2641	2233
55°	2722	2393	2001
60°	2494	2138	1792
65°	2195	1872	1587
70°	1808	1639	1348
75°	1437	1255	1316
80°	965	905	845
85°	601	721	841



TEST NUMBER: P546951

CATALOG NUMBER: FMR-24-4-LD4-2STD-50-UNV-82-84-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	313.6	4.7
10°-20°	860.6	13.0
20°-30°	1191.4	18.0
30°-40°	1270.4	19.2
40°-50°	1158.9	17.5
50°-60°	907.9	13.7
60°-70°	591.8	8.9
70°-80°	262.2	4.0
80°-90°	56.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2365.5	35.8
0°-40°	3635.9	55.0
0°-60°	5702.8	86.2
0°-90°	6613.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6613.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3369	3369	3369	3369	3369	
5°	3310	3306	3306	3302	3302	314
15°	3096	3096	3065	3034	3022	870
25°	2683	2668	2625	2531	2461	1232
35°	2177	2161	2056	1900	1854	1361
45°	1671	1636	1495	1371	1316	1287
55°	1160	1126	1020	900	853	1041
65°	689	650	588	600	498	679
75°	276	257	241	230	253	296
85°	39	43	47	51	54	54
90°	0	0	0	0	0	



TEST NUMBER: P546951

CATALOG NUMBER: FMR-24-4-LD4-2STD-50-UNV-82-84-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3368.6	3368.6	3368.6	3368.6	3368.6
2.5°	3345.2	3345.2	3345.2	3341.3	3341.3
5°	3310.2	3306.3	3306.3	3302.4	3302.4
7.5°	3282.9	3279.0	3275.1	3271.2	3263.4
10°	3244.0	3244.0	3240.1	3220.6	3216.7
12.5°	3181.6	3177.8	3162.2	3134.9	3127.1
15°	3096.0	3096.0	3064.8	3033.7	3022.0
17.5°	3002.5	2998.6	2959.7	2928.5	2912.9
20°	2901.3	2893.5	2854.5	2803.9	2776.6
22.5°	2788.3	2788.3	2741.6	2675.4	2648.1
25°	2683.2	2667.6	2624.8	2531.3	2461.2
27.5°	2562.5	2539.1	2492.4	2359.9	2278.2
30°	2430.0	2418.4	2352.2	2180.8	2118.5
32.5°	2305.4	2286.0	2215.9	2036.7	1986.1
35°	2176.9	2161.3	2056.2	1900.4	1853.7
37.5°	2048.4	2028.9	1896.5	1771.9	1713.5
40°	1919.9	1896.5	1752.4	1639.5	1577.2
42.5°	1799.2	1768.0	1627.8	1507.1	1437.0
45°	1670.7	1635.6	1495.4	1370.8	1316.3
47.5°	1542.1	1511.0	1382.5	1254.0	1191.7
50°	1405.8	1378.6	1261.8	1133.2	1067.0
52.5°	1292.9	1250.1	1137.1	1008.6	954.1
55°	1160.5	1125.5	1020.3	899.6	852.9
57.5°	1039.8	1004.7	907.4	794.4	755.5
60°	926.8	876.2	794.4	697.1	665.9
62.5°	802.2	763.3	693.2	611.4	650.3
65°	689.3	650.3	588.0	599.7	498.5
67.5°	564.7	545.2	490.7	436.2	420.6
70°	459.5	436.2	416.7	358.3	342.7
72.5°	366.1	342.7	315.4	284.3	272.6
75°	276.5	257.0	241.4	229.8	253.1
77.5°	190.8	183.0	171.3	159.7	155.8
80°	124.6	120.7	116.8	112.9	109.0
82.5°	74.0	74.0	74.0	74.0	74.0
85°	38.9	42.8	46.7	50.6	54.5
87.5°	23.4	23.4	27.3	31.2	35.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)