

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P546740

Luminaire Tested: **FMR-24-4-LD4-2HI-40-UNV-93-94-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P546740
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-24-4-LD4-2HI-40-UNV-93-94-EDD
Description: 2X4 FMR TROFFER WITH .156 CLEAR TEMPERED GLASS FIXTURE SIDE AND .187 CLEAR TEMPERED GLASS ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8318.0 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 86.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P546740

CATALOG NUMBER: FMR-24-4-LD4-2HI-40-UNV-93-94-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P546740

CATALOG NUMBER: FMR-24-4-LD4-2HI-40-UNV-93-94-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87																			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75																			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44																			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33																			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5701	5701	5701
5°	5623	5617	5610
10°	5575	5568	5528
15°	5424	5370	5295
20°	5225	5141	5001
25°	5010	4901	4596
30°	4749	4597	4140
35°	4498	4248	3830
40°	4242	3872	3484
45°	3999	3579	3150
50°	3701	3322	2809
55°	3424	3011	2516
60°	3137	2689	2254
65°	2760	2355	1996
70°	2274	2062	1696
75°	1808	1579	1655
80°	1214	1139	1063
85°	756	908	1059



TEST NUMBER: P546740

CATALOG NUMBER: FMR-24-4-LD4-2HI-40-UNV-93-94-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	394.4	4.7
10°-20°	1082.4	13.0
20°-30°	1498.6	18.0
30°-40°	1597.9	19.2
40°-50°	1457.8	17.5
50°-60°	1142.0	13.7
60°-70°	744.3	8.9
70°-80°	329.8	4.0
80°-90°	70.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2975.4	35.8
0°-40°	4573.3	55.0
0°-60°	7173.1	86.2
0°-90°	8318.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8318.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4237	4237	4237	4237	4237	
5°	4164	4159	4159	4154	4154	395
15°	3894	3894	3855	3816	3801	1095
25°	3375	3355	3302	3184	3096	1549
35°	2738	2719	2586	2390	2332	1712
45°	2101	2057	1881	1724	1656	1619
55°	1460	1416	1283	1132	1073	1309
65°	867	818	740	754	627	854
75°	348	323	304	289	318	373
85°	49	54	59	64	69	68
90°	0	0	0	0	0	



TEST NUMBER: P546740

CATALOG NUMBER: FMR-24-4-LD4-2HI-40-UNV-93-94-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4237.1	4237.1	4237.1	4237.1	4237.1
2.5°	4207.7	4207.7	4207.7	4202.8	4202.8
5°	4163.6	4158.7	4158.7	4153.8	4153.8
7.5°	4129.3	4124.4	4119.5	4114.6	4104.8
10°	4080.3	4080.3	4075.4	4050.9	4046.0
12.5°	4002.0	3997.1	3977.5	3943.2	3933.4
15°	3894.2	3894.2	3855.0	3815.8	3801.1
17.5°	3776.6	3771.7	3722.8	3683.6	3664.0
20°	3649.3	3639.5	3590.5	3526.8	3492.5
22.5°	3507.2	3507.2	3448.4	3365.2	3330.9
25°	3375.0	3355.4	3301.5	3183.9	3095.8
27.5°	3223.1	3193.7	3134.9	2968.4	2865.5
30°	3056.6	3041.9	2958.6	2743.1	2664.7
32.5°	2899.8	2875.3	2787.2	2561.8	2498.2
35°	2738.2	2718.6	2586.3	2390.4	2331.6
37.5°	2576.5	2552.0	2385.5	2228.8	2155.3
40°	2414.9	2385.5	2204.3	2062.2	1983.8
42.5°	2263.0	2223.9	2047.5	1895.7	1807.5
45°	2101.4	2057.3	1881.0	1724.2	1655.6
47.5°	1939.7	1900.6	1738.9	1577.3	1498.9
50°	1768.3	1734.0	1587.1	1425.4	1342.1
52.5°	1626.3	1572.4	1430.3	1268.7	1200.1
55°	1459.7	1415.6	1283.4	1131.5	1072.7
57.5°	1307.9	1263.8	1141.3	999.3	950.3
60°	1165.8	1102.1	999.3	876.8	837.6
62.5°	1009.1	960.1	871.9	769.0	818.0
65°	867.0	818.0	739.7	754.3	627.0
67.5°	710.3	685.8	617.2	548.6	529.0
70°	578.0	548.6	524.1	450.6	431.1
72.5°	460.4	431.1	396.8	357.6	342.9
75°	347.8	323.3	303.7	289.0	318.4
77.5°	240.0	230.2	215.5	200.8	195.9
80°	156.7	151.8	147.0	142.1	137.2
82.5°	93.1	93.1	93.1	93.1	93.1
85°	49.0	53.9	58.8	63.7	68.6
87.5°	29.4	29.4	34.3	39.2	44.1
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)