

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P547126

Luminaire Tested: **FMR-24-4-LD4-3LO-40-UNV-93-97-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P547126
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-24-4-LD4-3LO-40-UNV-93-97-EDD
Description: 2X4 FMR TROFFER WITH .156 CLEAR TEMPERED GLASS FIXTURE SIDE AND .375 CLEAR TEMPERED GLASS ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7243.0 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 70.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P547126

CATALOG NUMBER: FMR-24-4-LD4-3LO-40-UNV-93-97-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P547126

CATALOG NUMBER: FMR-24-4-LD4-3LO-40-UNV-93-97-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87				87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75				75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65				65
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56				56
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50				50
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44				44
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40				40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36				36
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33				33
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30				30

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4964	4964	4964
5°	4897	4891	4885
10°	4854	4848	4813
15°	4723	4676	4611
20°	4550	4477	4355
25°	4363	4268	4002
30°	4135	4002	3605
35°	3916	3699	3335
40°	3693	3371	3034
45°	3482	3117	2743
50°	3223	2893	2446
55°	2982	2621	2191
60°	2732	2341	1963
65°	2404	2051	1738
70°	1980	1795	1476
75°	1574	1375	1441
80°	1058	992	925
85°	659	790	922



TEST NUMBER: P547126

CATALOG NUMBER: FMR-24-4-LD4-3LO-40-UNV-93-97-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	343.4	4.7
10°-20°	942.5	13.0
20°-30°	1304.9	18.0
30°-40°	1391.4	19.2
40°-50°	1269.4	17.5
50°-60°	994.4	13.7
60°-70°	648.1	8.9
70°-80°	287.1	4.0
80°-90°	61.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2590.9	35.8
0°-40°	3982.3	55.0
0°-60°	6246.1	86.2
0°-90°	7243.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7243.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3690	3690	3690	3690	3690	
5°	3626	3621	3621	3617	3617	344
15°	3391	3391	3357	3323	3310	953
25°	2939	2922	2875	2772	2696	1349
35°	2384	2367	2252	2082	2030	1491
45°	1830	1791	1638	1501	1442	1410
55°	1271	1233	1118	985	934	1140
65°	755	712	644	657	546	744
75°	303	282	264	252	277	325
85°	43	47	51	55	60	59
90°	0	0	0	0	0	



TEST NUMBER: P547126

CATALOG NUMBER: FMR-24-4-LD4-3LO-40-UNV-93-97-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3689.5	3689.5	3689.5	3689.5	3689.5
2.5°	3663.9	3663.9	3663.9	3659.6	3659.6
5°	3625.5	3621.2	3621.2	3617.0	3617.0
7.5°	3595.7	3591.4	3587.1	3582.9	3574.3
10°	3553.0	3553.0	3548.7	3527.4	3523.1
12.5°	3484.8	3480.5	3463.4	3433.6	3425.0
15°	3390.9	3390.9	3356.8	3322.7	3309.9
17.5°	3288.5	3284.3	3241.6	3207.5	3190.4
20°	3177.7	3169.1	3126.5	3071.0	3041.2
22.5°	3054.0	3054.0	3002.8	2930.3	2900.4
25°	2938.8	2921.7	2874.8	2772.4	2695.7
27.5°	2806.6	2781.0	2729.8	2584.8	2495.2
30°	2661.5	2648.8	2576.2	2388.6	2320.3
32.5°	2525.1	2503.7	2427.0	2230.8	2175.3
35°	2384.3	2367.2	2252.1	2081.5	2030.3
37.5°	2243.5	2222.2	2077.2	1940.7	1876.7
40°	2102.8	2077.2	1919.4	1795.7	1727.4
42.5°	1970.6	1936.4	1782.9	1650.7	1573.9
45°	1829.8	1791.4	1637.9	1501.4	1441.7
47.5°	1689.1	1654.9	1514.2	1373.4	1305.2
50°	1539.8	1509.9	1382.0	1241.2	1168.7
52.5°	1416.1	1369.2	1245.5	1104.7	1045.0
55°	1271.1	1232.7	1117.5	985.3	934.1
57.5°	1138.8	1100.4	993.8	870.1	827.5
60°	1015.1	959.7	870.1	763.5	729.4
62.5°	878.7	836.0	759.2	669.7	712.3
65°	755.0	712.3	644.1	656.9	546.0
67.5°	618.5	597.1	537.4	477.7	460.7
70°	503.3	477.7	456.4	392.4	375.3
72.5°	400.9	375.3	345.5	311.4	298.6
75°	302.8	281.5	264.4	251.7	277.2
77.5°	209.0	200.5	187.7	174.9	170.6
80°	136.5	132.2	128.0	123.7	119.4
82.5°	81.0	81.0	81.0	81.0	81.0
85°	42.7	46.9	51.2	55.4	59.7
87.5°	25.6	25.6	29.9	34.1	38.4
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)