

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P547134

Luminaire Tested: **FMR-24-4-LD4-3LO-50-UNV-80-97-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P547134
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-24-4-LD4-3LO-50-UNV-80-97-EDD
Description: 2X4 FMR TROFFER WITH .125 PRISMATIC ACRYLIC FIXTURE SIDE AND .375 CLEAR TEMPERED GLASS ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7612.0 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 70.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P547134

CATALOG NUMBER: FMR-24-4-LD4-3LO-50-UNV-80-97-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P547134

CATALOG NUMBER: FMR-24-4-LD4-3LO-50-UNV-80-97-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87																			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75																			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44																			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33																			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5217	5217	5217
5°	5146	5140	5134
10°	5102	5095	5059
15°	4964	4914	4845
20°	4782	4705	4576
25°	4585	4485	4206
30°	4346	4206	3789
35°	4116	3888	3505
40°	3881	3543	3189
45°	3659	3275	2883
50°	3387	3040	2571
55°	3134	2755	2303
60°	2871	2461	2063
65°	2526	2155	1827
70°	2081	1887	1552
75°	1655	1445	1515
80°	1111	1042	972
85°	692	831	969



TEST NUMBER: P547134

CATALOG NUMBER: FMR-24-4-LD4-3LO-50-UNV-80-97-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	360.9	4.7
10°-20°	990.6	13.0
20°-30°	1371.4	18.0
30°-40°	1462.3	19.2
40°-50°	1334.0	17.5
50°-60°	1045.1	13.7
60°-70°	681.2	8.9
70°-80°	301.8	4.0
80°-90°	64.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2722.9	35.8
0°-40°	4185.2	55.0
0°-60°	6564.3	86.2
0°-90°	7612.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7612.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3878	3878	3878	3878	3878	
5°	3810	3806	3806	3801	3801	362
15°	3564	3564	3528	3492	3478	1002
25°	3088	3071	3021	2914	2833	1418
35°	2506	2488	2367	2188	2134	1567
45°	1923	1883	1721	1578	1515	1481
55°	1336	1296	1174	1036	982	1198
65°	793	749	677	690	574	782
75°	318	296	278	264	291	341
85°	45	49	54	58	63	62
90°	0	0	0	0	0	



TEST NUMBER: P547134

CATALOG NUMBER: FMR-24-4-LD4-3LO-50-UNV-80-97-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3877.5	3877.5	3877.5	3877.5	3877.5
2.5°	3850.6	3850.6	3850.6	3846.1	3846.1
5°	3810.2	3805.7	3805.7	3801.2	3801.2
7.5°	3778.8	3774.4	3769.9	3765.4	3756.4
10°	3734.0	3734.0	3729.5	3707.1	3702.6
12.5°	3662.3	3657.8	3639.9	3608.5	3599.5
15°	3563.7	3563.7	3527.8	3491.9	3478.5
17.5°	3456.1	3451.6	3406.8	3370.9	3353.0
20°	3339.5	3330.6	3285.7	3227.5	3196.1
22.5°	3209.5	3209.5	3155.8	3079.5	3048.2
25°	3088.5	3070.6	3021.3	2913.7	2833.0
27.5°	2949.6	2922.7	2868.9	2716.5	2622.3
30°	2797.1	2783.7	2707.5	2510.3	2438.5
32.5°	2653.7	2631.3	2550.6	2344.4	2286.1
35°	2505.8	2487.8	2366.8	2187.5	2133.7
37.5°	2357.8	2335.4	2183.0	2039.6	1972.3
40°	2209.9	2183.0	2017.2	1887.2	1815.5
42.5°	2071.0	2035.1	1873.7	1734.8	1654.1
45°	1923.0	1882.7	1721.3	1577.9	1515.1
47.5°	1775.1	1739.2	1591.3	1443.4	1371.7
50°	1618.2	1586.8	1452.4	1304.4	1228.2
52.5°	1488.2	1438.9	1308.9	1161.0	1098.2
55°	1335.8	1295.5	1174.4	1035.5	981.7
57.5°	1196.9	1156.5	1044.4	914.5	869.6
60°	1066.9	1008.6	914.5	802.4	766.5
62.5°	923.4	878.6	797.9	703.8	748.6
65°	793.4	748.6	676.9	690.3	573.8
67.5°	650.0	627.6	564.8	502.1	484.1
70°	528.9	502.1	479.6	412.4	394.5
72.5°	421.4	394.5	363.1	327.2	313.8
75°	318.3	295.9	277.9	264.5	291.4
77.5°	219.6	210.7	197.2	183.8	179.3
80°	143.4	139.0	134.5	130.0	125.5
82.5°	85.2	85.2	85.2	85.2	85.2
85°	44.8	49.3	53.8	58.3	62.8
87.5°	26.9	26.9	31.4	35.9	40.3
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)