

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P547147

Luminaire Tested: **FMR-24-4-LD4-3LO-50-UNV-82-88-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P547147
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-24-4-LD4-3LO-50-UNV-82-88-EDD
Description: 2X4 FMR TROFFER WITH .187 CLEAR PC FIXTURE SIDE AND .500 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6254.0 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 70.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P547147

CATALOG NUMBER: FMR-24-4-LD4-3LO-50-UNV-82-88-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P547147

CATALOG NUMBER: FMR-24-4-LD4-3LO-50-UNV-82-88-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87																			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75																			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44																			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33																			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4286	4286	4286
5°	4228	4223	4218
10°	4192	4186	4156
15°	4078	4037	3981
20°	3929	3865	3760
25°	3767	3685	3456
30°	3570	3456	3113
35°	3381	3194	2880
40°	3189	2911	2620
45°	3006	2691	2369
50°	2783	2498	2112
55°	2575	2263	1892
60°	2359	2022	1695
65°	2075	1770	1501
70°	1710	1550	1275
75°	1359	1187	1245
80°	914	856	799
85°	568	682	797



TEST NUMBER: P547147

CATALOG NUMBER: FMR-24-4-LD4-3LO-50-UNV-82-88-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	296.5	4.7
10°-20°	813.8	13.0
20°-30°	1126.7	18.0
30°-40°	1201.4	19.2
40°-50°	1096.0	17.5
50°-60°	858.7	13.7
60°-70°	559.6	8.9
70°-80°	247.9	4.0
80°-90°	53.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2237.1	35.8
0°-40°	3438.5	55.0
0°-60°	5393.2	86.2
0°-90°	6254.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6254.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3186	3186	3186	3186	3186	
5°	3130	3127	3127	3123	3123	297
15°	2928	2928	2898	2869	2858	823
25°	2538	2523	2482	2394	2328	1165
35°	2059	2044	1945	1797	1753	1287
45°	1580	1547	1414	1296	1245	1217
55°	1098	1064	965	851	807	984
65°	652	615	556	567	471	642
75°	262	243	228	217	239	280
85°	37	40	44	48	52	51
90°	0	0	0	0	0	



TEST NUMBER: P547147

CATALOG NUMBER: FMR-24-4-LD4-3LO-50-UNV-82-88-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3185.7	3185.7	3185.7	3185.7	3185.7
2.5°	3163.6	3163.6	3163.6	3159.9	3159.9
5°	3130.5	3126.8	3126.8	3123.1	3123.1
7.5°	3104.7	3101.0	3097.3	3093.6	3086.3
10°	3067.9	3067.9	3064.2	3045.8	3042.1
12.5°	3008.9	3005.2	2990.5	2964.7	2957.4
15°	2927.9	2927.9	2898.4	2869.0	2857.9
17.5°	2839.5	2835.8	2799.0	2769.5	2754.8
20°	2743.8	2736.4	2699.6	2651.7	2625.9
22.5°	2637.0	2637.0	2592.8	2530.1	2504.4
25°	2537.5	2522.8	2482.3	2393.9	2327.6
27.5°	2423.3	2401.2	2357.1	2231.8	2154.5
30°	2298.1	2287.1	2224.5	2062.4	2003.5
32.5°	2180.3	2161.9	2095.6	1926.2	1878.3
35°	2058.7	2044.0	1944.6	1797.3	1753.1
37.5°	1937.2	1918.8	1793.6	1675.7	1620.5
40°	1815.7	1793.6	1657.3	1550.5	1491.6
42.5°	1701.5	1672.0	1539.5	1425.3	1359.0
45°	1580.0	1546.8	1414.2	1296.4	1244.8
47.5°	1458.4	1429.0	1307.4	1185.9	1127.0
50°	1329.5	1303.7	1193.3	1071.7	1009.1
52.5°	1222.7	1182.2	1075.4	953.9	902.3
55°	1097.5	1064.4	964.9	850.7	806.6
57.5°	983.3	950.2	858.1	751.3	714.5
60°	876.5	828.7	751.3	659.2	629.8
62.5°	758.7	721.8	655.6	578.2	615.0
65°	651.9	615.0	556.1	567.2	471.4
67.5°	534.0	515.6	464.0	412.5	397.8
70°	434.6	412.5	394.1	338.8	324.1
72.5°	346.2	324.1	298.3	268.9	257.8
75°	261.5	243.1	228.3	217.3	239.4
77.5°	180.5	173.1	162.0	151.0	147.3
80°	117.9	114.2	110.5	106.8	103.1
82.5°	70.0	70.0	70.0	70.0	70.0
85°	36.8	40.5	44.2	47.9	51.6
87.5°	22.1	22.1	25.8	29.5	33.1
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)