

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P546992

Luminaire Tested: **FMR-24-4-LD4-3HI-35-UNV-93-85-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P546992
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-24-4-LD4-3HI-35-UNV-93-85-EDD
Description: 2X4 FMR TROFFER WITH .156 CLEAR TEMPERED GLASS FIXTURE SIDE AND .187 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12031.0 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 129.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P546992

CATALOG NUMBER: FMR-24-4-LD4-3HI-35-UNV-93-85-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P546992

CATALOG NUMBER: FMR-24-4-LD4-3HI-35-UNV-93-85-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87				87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75				75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65				65
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56				56
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50				50
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44				44
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40				40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36				36
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33				33
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30				30

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8246	8246	8246
5°	8134	8124	8115
10°	8063	8053	7995
15°	7846	7767	7658
20°	7558	7436	7233
25°	7247	7089	6648
30°	6869	6648	5988
35°	6505	6144	5539
40°	6135	5600	5040
45°	5783	5177	4557
50°	5354	4805	4064
55°	4953	4354	3640
60°	4538	3889	3260
65°	3992	3406	2887
70°	3289	2982	2453
75°	2615	2284	2394
80°	1757	1647	1537
85°	1093	1312	1531



TEST NUMBER: P546992

CATALOG NUMBER: FMR-24-4-LD4-3HI-35-UNV-93-85-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	570.5	4.7
10°-20°	1565.6	13.0
20°-30°	2167.5	18.0
30°-40°	2311.2	19.2
40°-50°	2108.5	17.5
50°-60°	1651.8	13.7
60°-70°	1076.6	8.9
70°-80°	477.0	4.0
80°-90°	102.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4303.6	35.8
0°-40°	6614.8	55.0
0°-60°	10375.0	86.2
0°-90°	12031.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12031.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6128	6128	6128	6128	6128	
5°	6022	6015	6015	6008	6008	572
15°	5632	5632	5576	5519	5498	1583
25°	4882	4853	4775	4605	4478	2241
35°	3960	3932	3741	3457	3372	2476
45°	3039	2976	2721	2494	2395	2341
55°	2111	2048	1856	1637	1552	1894
65°	1254	1183	1070	1091	907	1236
75°	503	468	439	418	460	539
85°	71	78	85	92	99	98
90°	0	0	0	0	0	



TEST NUMBER: P546992

CATALOG NUMBER: FMR-24-4-LD4-3HI-35-UNV-93-85-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6128.4	6128.4	6128.4	6128.4	6128.4
2.5°	6085.9	6085.9	6085.9	6078.8	6078.8
5°	6022.2	6015.1	6015.1	6008.0	6008.0
7.5°	5972.6	5965.5	5958.4	5951.3	5937.1
10°	5901.7	5901.7	5894.6	5859.2	5852.1
12.5°	5788.4	5781.3	5752.9	5703.3	5689.2
15°	5632.5	5632.5	5575.8	5519.1	5497.9
17.5°	5462.5	5455.4	5384.5	5327.8	5299.5
20°	5278.2	5264.1	5193.2	5101.1	5051.5
22.5°	5072.8	5072.8	4987.8	4867.3	4817.7
25°	4881.5	4853.2	4775.2	4605.2	4477.7
27.5°	4661.9	4619.3	4534.3	4293.4	4144.7
30°	4421.0	4399.7	4279.3	3967.5	3854.2
32.5°	4194.3	4158.8	4031.3	3705.4	3613.3
35°	3960.5	3932.1	3740.8	3457.4	3372.4
37.5°	3726.7	3691.2	3450.3	3223.6	3117.4
40°	3492.9	3450.3	3188.2	2982.7	2869.4
42.5°	3273.2	3216.5	2961.5	2741.9	2614.3
45°	3039.4	2975.7	2720.6	2493.9	2394.7
47.5°	2805.6	2748.9	2515.1	2281.3	2168.0
50°	2557.6	2508.1	2295.5	2061.7	1941.3
52.5°	2352.2	2274.2	2068.8	1835.0	1735.8
55°	2111.3	2047.5	1856.2	1636.6	1551.6
57.5°	1891.7	1827.9	1650.8	1445.3	1374.5
60°	1686.2	1594.1	1445.3	1268.2	1211.5
62.5°	1459.5	1388.6	1261.1	1112.3	1183.2
65°	1254.0	1183.2	1069.8	1091.1	906.9
67.5°	1027.3	991.9	892.7	793.5	765.2
70°	836.0	793.5	758.1	651.8	623.5
72.5°	666.0	623.5	573.9	517.2	495.9
75°	503.0	467.6	439.3	418.0	460.5
77.5°	347.2	333.0	311.7	290.5	283.4
80°	226.7	219.6	212.5	205.5	198.4
82.5°	134.6	134.6	134.6	134.6	134.6
85°	70.8	77.9	85.0	92.1	99.2
87.5°	42.5	42.5	49.6	56.7	63.8
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)