

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P547074

Luminaire Tested: **FMR-24-4-LD4-3LO-35-UNV-81-87-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P547074
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-24-4-LD4-3LO-35-UNV-81-87-EDD
Description: 2X4 FMR TROFFER WITH .156 CLEAR PC FIXTURE SIDE AND .375 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6643.0 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 70.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P547074

CATALOG NUMBER: FMR-24-4-LD4-3LO-35-UNV-81-87-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P547074

CATALOG NUMBER: FMR-24-4-LD4-3LO-35-UNV-81-87-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87																			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75																			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44																			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33																			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4553	4553	4553
5°	4491	4486	4481
10°	4452	4447	4415
15°	4332	4288	4229
20°	4173	4106	3994
25°	4001	3914	3670
30°	3793	3671	3306
35°	3592	3393	3059
40°	3387	3092	2783
45°	3193	2858	2516
50°	2956	2653	2244
55°	2735	2404	2010
60°	2505	2147	1800
65°	2204	1881	1594
70°	1816	1647	1354
75°	1444	1261	1322
80°	970	910	848
85°	604	724	846



TEST NUMBER: P547074

CATALOG NUMBER: FMR-24-4-LD4-3LO-35-UNV-81-87-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	315.0	4.7
10°-20°	864.5	13.0
20°-30°	1196.8	18.0
30°-40°	1276.1	19.2
40°-50°	1164.2	17.5
50°-60°	912.1	13.7
60°-70°	594.4	8.9
70°-80°	263.4	4.0
80°-90°	56.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2376.3	35.8
0°-40°	3652.4	55.0
0°-60°	5728.6	86.2
0°-90°	6643.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6643.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3384	3384	3384	3384	3384	
5°	3325	3321	3321	3317	3317	316
15°	3110	3110	3079	3047	3036	874
25°	2695	2680	2637	2543	2472	1237
35°	2187	2171	2066	1909	1862	1367
45°	1678	1643	1502	1377	1322	1293
55°	1166	1131	1025	904	857	1046
65°	692	653	591	602	501	682
75°	278	258	242	231	254	298
85°	39	43	47	51	55	54
90°	0	0	0	0	0	



TEST NUMBER: P547074

CATALOG NUMBER: FMR-24-4-LD4-3LO-35-UNV-81-87-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3383.9	3383.9	3383.9	3383.9	3383.9
2.5°	3360.4	3360.4	3360.4	3356.5	3356.5
5°	3325.2	3321.3	3321.3	3317.4	3317.4
7.5°	3297.8	3293.9	3290.0	3286.1	3278.2
10°	3258.7	3258.7	3254.8	3235.2	3231.3
12.5°	3196.1	3192.2	3176.5	3149.1	3141.3
15°	3110.0	3110.0	3078.7	3047.4	3035.7
17.5°	3016.1	3012.2	2973.1	2941.8	2926.2
20°	2914.4	2906.6	2867.5	2816.6	2789.2
22.5°	2801.0	2801.0	2754.0	2687.5	2660.1
25°	2695.3	2679.7	2636.7	2542.8	2472.4
27.5°	2574.1	2550.6	2503.7	2370.7	2288.5
30°	2441.1	2429.3	2362.8	2190.7	2128.1
32.5°	2315.9	2296.3	2225.9	2046.0	1995.1
35°	2186.8	2171.1	2065.5	1909.0	1862.1
37.5°	2057.7	2038.1	1905.1	1779.9	1721.3
40°	1928.6	1905.1	1760.4	1646.9	1584.3
42.5°	1807.3	1776.0	1635.2	1513.9	1443.5
45°	1678.2	1643.0	1502.2	1377.0	1322.2
47.5°	1549.1	1517.8	1388.7	1259.7	1197.1
50°	1412.2	1384.8	1267.5	1138.4	1071.9
52.5°	1298.8	1255.7	1142.3	1013.2	958.4
55°	1165.8	1130.6	1024.9	903.7	856.7
57.5°	1044.5	1009.3	911.5	798.0	758.9
60°	931.0	880.2	798.0	700.2	668.9
62.5°	805.9	766.7	696.3	614.2	653.3
65°	692.4	653.3	590.7	602.4	500.7
67.5°	567.2	547.7	492.9	438.1	422.5
70°	461.6	438.1	418.6	359.9	344.3
72.5°	367.7	344.3	316.9	285.6	273.8
75°	277.7	258.2	242.5	230.8	254.3
77.5°	191.7	183.9	172.1	160.4	156.5
80°	125.2	121.3	117.4	113.4	109.5
82.5°	74.3	74.3	74.3	74.3	74.3
85°	39.1	43.0	46.9	50.9	54.8
87.5°	23.5	23.5	27.4	31.3	35.2
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)