

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P547222

Luminaire Tested: **FMR-24-4-LD4-3STD-40-UNV-93-97-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P547222
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-24-4-LD4-3STD-40-UNV-93-97-EDD
Description: 2X4 FMR TROFFER WITH .156 CLEAR TEMPERED GLASS FIXTURE SIDE AND .375
CLEAR TEMPERED GLASS ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 4000K CCT
LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9699.0 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 99.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P547222

CATALOG NUMBER: FMR-24-4-LD4-3STD-40-UNV-93-97-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P547222

CATALOG NUMBER: FMR-24-4-LD4-3STD-40-UNV-93-97-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87																			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75																			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44																			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33																			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6647	6647	6647
5°	6557	6549	6542
10°	6500	6493	6446
15°	6325	6261	6174
20°	6093	5995	5831
25°	5842	5715	5359
30°	5537	5360	4827
35°	5244	4953	4466
40°	4946	4514	4063
45°	4662	4173	3673
50°	4316	3874	3276
55°	3993	3510	2934
60°	3658	3136	2628
65°	3219	2746	2328
70°	2651	2404	1977
75°	2108	1841	1930
80°	1416	1327	1239
85°	881	1057	1235



TEST NUMBER: P547222

CATALOG NUMBER: FMR-24-4-LD4-3STD-40-UNV-93-97-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	459.9	4.7
10°-20°	1262.1	13.0
20°-30°	1747.4	18.0
30°-40°	1863.2	19.2
40°-50°	1699.8	17.5
50°-60°	1331.6	13.7
60°-70°	867.9	8.9
70°-80°	384.5	4.0
80°-90°	82.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3469.4	35.8
0°-40°	5332.6	55.0
0°-60°	8364.0	86.2
0°-90°	9699.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9699.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4940	4940	4940	4940	4940	
5°	4855	4849	4849	4843	4843	461
15°	4541	4541	4495	4449	4432	1277
25°	3935	3912	3850	3712	3610	1807
35°	3193	3170	3016	2787	2719	1996
45°	2450	2399	2193	2010	1930	1887
55°	1702	1651	1496	1319	1251	1527
65°	1011	954	862	880	731	996
75°	406	377	354	337	371	435
85°	57	63	68	74	80	79
90°	0	0	0	0	0	



TEST NUMBER: P547222

CATALOG NUMBER: FMR-24-4-LD4-3STD-40-UNV-93-97-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4940.5	4940.5	4940.5	4940.5	4940.5
2.5°	4906.3	4906.3	4906.3	4900.6	4900.6
5°	4854.9	4849.2	4849.2	4843.4	4843.4
7.5°	4814.9	4809.2	4803.5	4797.8	4786.3
10°	4757.8	4757.8	4752.1	4723.5	4717.8
12.5°	4666.4	4660.7	4637.8	4597.8	4586.4
15°	4540.7	4540.7	4495.0	4449.3	4432.2
17.5°	4403.6	4397.9	4340.8	4295.1	4272.3
20°	4255.1	4243.7	4186.6	4112.4	4072.4
22.5°	4089.5	4089.5	4021.0	3923.9	3883.9
25°	3935.3	3912.5	3849.6	3712.5	3609.7
27.5°	3758.2	3724.0	3655.4	3461.2	3341.3
30°	3564.0	3546.9	3449.8	3198.5	3107.1
32.5°	3381.3	3352.7	3249.9	2987.2	2912.9
35°	3192.8	3169.9	3015.7	2787.3	2718.7
37.5°	3004.3	2975.7	2781.6	2598.8	2513.1
40°	2815.8	2781.6	2570.2	2404.6	2313.2
42.5°	2638.8	2593.1	2387.5	2210.4	2107.6
45°	2450.3	2398.9	2193.3	2010.5	1930.5
47.5°	2261.8	2216.1	2027.6	1839.1	1747.8
50°	2061.9	2021.9	1850.6	1662.1	1565.0
52.5°	1896.3	1833.4	1667.8	1479.3	1399.3
55°	1702.1	1650.7	1496.4	1319.4	1250.8
57.5°	1525.0	1473.6	1330.8	1165.2	1108.1
60°	1359.4	1285.1	1165.2	1022.4	976.7
62.5°	1176.6	1119.5	1016.7	896.7	953.8
65°	1011.0	953.8	862.5	879.6	731.1
67.5°	828.2	799.6	719.7	639.7	616.9
70°	674.0	639.7	611.1	525.5	502.6
72.5°	536.9	502.6	462.6	416.9	399.8
75°	405.5	377.0	354.1	337.0	371.3
77.5°	279.9	268.4	251.3	234.2	228.5
80°	182.8	177.1	171.3	165.6	159.9
82.5°	108.5	108.5	108.5	108.5	108.5
85°	57.1	62.8	68.5	74.3	80.0
87.5°	34.3	34.3	40.0	45.7	51.4
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)