

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P547223

Luminaire Tested: **FMR-24-4-LD4-3STD-50-UNV-80-84-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P547223
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-24-4-LD4-3STD-50-UNV-80-84-EDD
Description: 2X4 FMR TROFFER WITH .125 PRISMATIC ACRYLIC FIXTURE SIDE AND .125 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10666.0 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 99.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P547223

CATALOG NUMBER: FMR-24-4-LD4-3STD-50-UNV-80-84-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P547223

CATALOG NUMBER: FMR-24-4-LD4-3STD-50-UNV-80-84-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87																			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75																			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44																			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33																			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7310	7310	7310
5°	7211	7202	7194
10°	7148	7140	7088
15°	6956	6886	6789
20°	6700	6592	6412
25°	6425	6285	5893
30°	6089	5894	5309
35°	5767	5447	4911
40°	5439	4964	4468
45°	5127	4589	4040
50°	4746	4260	3602
55°	4391	3860	3227
60°	4023	3448	2890
65°	3539	3019	2560
70°	2916	2644	2174
75°	2319	2024	2123
80°	1557	1460	1363
85°	969	1164	1357



TEST NUMBER: P547223

CATALOG NUMBER: FMR-24-4-LD4-3STD-50-UNV-80-84-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	505.7	4.7
10°-20°	1388.0	13.0
20°-30°	1921.6	18.0
30°-40°	2049.0	19.2
40°-50°	1869.3	17.5
50°-60°	1464.4	13.7
60°-70°	954.4	8.9
70°-80°	422.9	4.0
80°-90°	90.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3815.3	35.8
0°-40°	5864.3	55.0
0°-60°	9197.9	86.2
0°-90°	10666.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10666.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5433	5433	5433	5433	5433	
5°	5339	5333	5333	5326	5326	507
15°	4993	4993	4943	4893	4874	1404
25°	4328	4302	4233	4083	3970	1987
35°	3511	3486	3316	3065	2990	2195
45°	2695	2638	2412	2211	2123	2076
55°	1872	1815	1646	1451	1376	1679
65°	1112	1049	948	967	804	1096
75°	446	415	389	371	408	478
85°	63	69	75	82	88	87
90°	0	0	0	0	0	



TEST NUMBER: P547223

CATALOG NUMBER: FMR-24-4-LD4-3STD-50-UNV-80-84-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5433.1	5433.1	5433.1	5433.1	5433.1
2.5°	5395.4	5395.4	5395.4	5389.2	5389.2
5°	5338.9	5332.6	5332.6	5326.3	5326.3
7.5°	5294.9	5288.7	5282.4	5276.1	5263.5
10°	5232.1	5232.1	5225.8	5194.4	5188.2
12.5°	5131.6	5125.3	5100.2	5056.3	5043.7
15°	4993.4	4993.4	4943.2	4892.9	4874.1
17.5°	4842.7	4836.4	4773.6	4723.4	4698.2
20°	4679.4	4666.8	4604.0	4522.4	4478.4
22.5°	4497.2	4497.2	4421.9	4315.1	4271.1
25°	4327.7	4302.5	4233.4	4082.7	3969.6
27.5°	4132.9	4095.3	4019.9	3806.3	3674.4
30°	3919.4	3900.5	3793.8	3517.4	3416.9
32.5°	3718.4	3687.0	3573.9	3285.0	3203.3
35°	3511.1	3486.0	3316.4	3065.2	2989.8
37.5°	3303.8	3272.4	3058.9	2857.9	2763.7
40°	3096.6	3058.9	2826.5	2644.3	2543.8
42.5°	2901.9	2851.6	2625.5	2430.8	2317.7
45°	2694.6	2638.0	2411.9	2210.9	2123.0
47.5°	2487.3	2437.1	2229.8	2022.5	1922.0
50°	2267.5	2223.5	2035.1	1827.8	1721.0
52.5°	2085.3	2016.2	1834.1	1626.8	1538.9
55°	1871.8	1815.2	1645.6	1450.9	1375.6
57.5°	1677.0	1620.5	1463.5	1281.3	1218.5
60°	1494.9	1413.2	1281.3	1124.3	1074.1
62.5°	1293.9	1231.1	1118.0	986.1	1048.9
65°	1111.7	1048.9	948.4	967.3	804.0
67.5°	910.8	879.3	791.4	703.5	678.4
70°	741.2	703.5	672.1	577.9	552.7
72.5°	590.4	552.7	508.8	458.5	439.7
75°	446.0	414.6	389.4	370.6	408.3
77.5°	307.8	295.2	276.4	257.5	251.2
80°	201.0	194.7	188.4	182.2	175.9
82.5°	119.3	119.3	119.3	119.3	119.3
85°	62.8	69.1	75.4	81.7	87.9
87.5°	37.7	37.7	44.0	50.2	56.5
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)