

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P547356

Luminaire Tested: **FMR-24-4-LD4-4LO-35-UNV-80-94-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P547356
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-24-4-LD4-4LO-35-UNV-80-94-EDD
Description: 2X4 FMR TROFFER WITH .125 PRISMATIC ACRYLIC FIXTURE SIDE AND .187 CLEAR TEMPERED GLASS ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9967.0 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 93.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P547356

CATALOG NUMBER: FMR-24-4-LD4-4LO-35-UNV-80-94-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P547356

CATALOG NUMBER: FMR-24-4-LD4-4LO-35-UNV-80-94-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87																			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75																			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44																			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33																			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6831	6831	6831
5°	6738	6730	6722
10°	6680	6672	6624
15°	6500	6434	6344
20°	6261	6160	5992
25°	6004	5873	5507
30°	5690	5508	4961
35°	5389	5090	4589
40°	5082	4639	4175
45°	4791	4289	3775
50°	4435	3981	3366
55°	4103	3607	3015
60°	3759	3222	2701
65°	3308	2822	2392
70°	2725	2471	2032
75°	2166	1892	1983
80°	1455	1364	1273
85°	906	1087	1269



TEST NUMBER: P547356

CATALOG NUMBER: FMR-24-4-LD4-4LO-35-UNV-80-94-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	472.6	4.7
10°-20°	1297.0	13.0
20°-30°	1795.6	18.0
30°-40°	1914.7	19.2
40°-50°	1746.7	17.5
50°-60°	1368.4	13.7
60°-70°	891.9	8.9
70°-80°	395.1	4.0
80°-90°	84.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3565.3	35.8
0°-40°	5480.0	55.0
0°-60°	8595.1	86.2
0°-90°	9967.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9967.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5077	5077	5077	5077	5077	
5°	4989	4983	4983	4977	4977	474
15°	4666	4666	4619	4572	4555	1312
25°	4044	4021	3956	3815	3710	1857
35°	3281	3258	3099	2864	2794	2051
45°	2518	2465	2254	2066	1984	1940
55°	1749	1696	1538	1356	1285	1569
65°	1039	980	886	904	751	1024
75°	417	387	364	346	382	447
85°	59	65	70	76	82	81
90°	0	0	0	0	0	



TEST NUMBER: P547356

CATALOG NUMBER: FMR-24-4-LD4-4LO-35-UNV-80-94-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5077.1	5077.1	5077.1	5077.1	5077.1
2.5°	5041.8	5041.8	5041.8	5036.0	5036.0
5°	4989.0	4983.1	4983.1	4977.3	4977.3
7.5°	4947.9	4942.1	4936.2	4930.3	4918.6
10°	4889.2	4889.2	4883.4	4854.0	4848.1
12.5°	4795.3	4789.5	4766.0	4724.9	4713.2
15°	4666.2	4666.2	4619.2	4572.3	4554.7
17.5°	4525.3	4519.5	4460.8	4413.8	4390.3
20°	4372.7	4361.0	4302.3	4226.0	4184.9
22.5°	4202.5	4202.5	4132.1	4032.3	3991.2
25°	4044.0	4020.6	3956.0	3815.1	3709.5
27.5°	3862.1	3826.9	3756.4	3556.9	3433.6
30°	3662.5	3644.9	3545.1	3286.9	3193.0
32.5°	3474.7	3445.4	3339.7	3069.7	2993.4
35°	3281.0	3257.5	3099.1	2864.3	2793.8
37.5°	3087.3	3058.0	2858.4	2670.6	2582.5
40°	2893.6	2858.4	2641.2	2471.0	2377.1
42.5°	2711.7	2664.7	2453.4	2271.5	2165.8
45°	2518.0	2465.2	2253.9	2066.0	1983.9
47.5°	2324.3	2277.3	2083.6	1890.0	1796.0
50°	2118.9	2077.8	1901.7	1708.0	1608.2
52.5°	1948.7	1884.1	1713.9	1520.2	1438.0
55°	1749.1	1696.3	1537.8	1355.8	1285.4
57.5°	1567.1	1514.3	1367.6	1197.4	1138.7
60°	1396.9	1320.6	1197.4	1050.6	1003.7
62.5°	1209.1	1150.4	1044.8	921.5	980.2
65°	1038.9	980.2	886.3	903.9	751.3
67.5°	851.1	821.7	739.5	657.4	633.9
70°	692.6	657.4	628.0	540.0	516.5
72.5°	551.7	516.5	475.4	428.5	410.9
75°	416.7	387.4	363.9	346.3	381.5
77.5°	287.6	275.9	258.3	240.6	234.8
80°	187.8	182.0	176.1	170.2	164.3
82.5°	111.5	111.5	111.5	111.5	111.5
85°	58.7	64.6	70.4	76.3	82.2
87.5°	35.2	35.2	41.1	47.0	52.8
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)