

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P547469

Luminaire Tested: **FMR-24-4-LD4-4STD-35-UNV-82-96-EDD**

Issue Date: 6/15/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P547469
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 6/15/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FMR-24-4-LD4-4STD-35-UNV-82-96-EDD
Description: 2X4 FMR TROFFER WITH .187 CLEAR PC FIXTURE SIDE AND .250 CLEAR
TEMPERED GLASS ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12276.0 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 133.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P547469

CATALOG NUMBER: FMR-24-4-LD4-4STD-35-UNV-82-96-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P547469

CATALOG NUMBER: FMR-24-4-LD4-4STD-35-UNV-82-96-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87																			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75																			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44																			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33																			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8414	8414	8414
5°	8299	8290	8280
10°	8227	8218	8158
15°	8006	7925	7814
20°	7711	7587	7380
25°	7395	7234	6783
30°	7008	6784	6110
35°	6638	6270	5652
40°	6260	5714	5142
45°	5901	5282	4650
50°	5463	4903	4146
55°	5054	4443	3714
60°	4630	3969	3327
65°	4074	3475	2946
70°	3356	3043	2503
75°	2668	2330	2443
80°	1792	1681	1568
85°	1116	1340	1562



TEST NUMBER: P547469

CATALOG NUMBER: FMR-24-4-LD4-4STD-35-UNV-82-96-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	582.1	4.7
10°-20°	1597.5	13.0
20°-30°	2211.6	18.0
30°-40°	2358.2	19.2
40°-50°	2151.4	17.5
50°-60°	1685.5	13.7
60°-70°	1098.5	8.9
70°-80°	486.7	4.0
80°-90°	104.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4391.2	35.8
0°-40°	6749.5	55.0
0°-60°	10586.3	86.2
0°-90°	12276.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12276.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6253	6253	6253	6253	6253	
5°	6145	6138	6138	6130	6130	583
15°	5747	5747	5689	5632	5610	1616
25°	4981	4952	4872	4699	4569	2287
35°	4041	4012	3817	3528	3441	2526
45°	3101	3036	2776	2545	2444	2389
55°	2154	2089	1894	1670	1583	1932
65°	1280	1207	1092	1113	925	1261
75°	513	477	448	426	470	550
85°	72	80	87	94	101	100
90°	0	0	0	0	0	



TEST NUMBER: P547469

CATALOG NUMBER: FMR-24-4-LD4-4STD-35-UNV-82-96-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6253.2	6253.2	6253.2	6253.2	6253.2
2.5°	6209.9	6209.9	6209.9	6202.6	6202.6
5°	6144.8	6137.6	6137.6	6130.3	6130.3
7.5°	6094.2	6087.0	6079.7	6072.5	6058.0
10°	6021.9	6021.9	6014.7	5978.5	5971.3
12.5°	5906.2	5899.0	5870.1	5819.5	5805.0
15°	5747.2	5747.2	5689.4	5631.5	5609.8
17.5°	5573.7	5566.5	5494.2	5436.3	5407.4
20°	5385.7	5371.3	5299.0	5205.0	5154.4
22.5°	5176.1	5176.1	5089.3	4966.4	4915.8
25°	4980.9	4952.0	4872.5	4699.0	4568.8
27.5°	4756.8	4713.4	4626.7	4380.9	4229.1
30°	4511.0	4489.3	4366.4	4048.3	3932.7
32.5°	4279.7	4243.5	4113.4	3780.9	3686.9
35°	4041.1	4012.2	3817.0	3527.8	3441.1
37.5°	3802.5	3766.4	3520.6	3289.3	3180.8
40°	3564.0	3520.6	3253.1	3043.5	2927.8
42.5°	3339.9	3282.0	3021.8	2797.7	2667.6
45°	3101.3	3036.3	2776.0	2544.7	2443.5
47.5°	2862.8	2804.9	2566.4	2327.8	2212.1
50°	2609.7	2559.1	2342.3	2103.7	1980.8
52.5°	2400.1	2320.6	2110.9	1872.4	1771.1
55°	2154.3	2089.2	1894.0	1669.9	1583.2
57.5°	1930.2	1865.1	1684.4	1474.8	1402.5
60°	1720.5	1626.6	1474.8	1294.0	1236.2
62.5°	1489.2	1416.9	1286.8	1135.0	1207.3
65°	1279.6	1207.3	1091.6	1113.3	925.3
67.5°	1048.2	1012.1	910.9	809.7	780.8
70°	853.0	809.7	773.5	665.1	636.2
72.5°	679.5	636.2	585.6	527.7	506.0
75°	513.3	477.1	448.2	426.5	469.9
77.5°	354.2	339.8	318.1	296.4	289.2
80°	231.3	224.1	216.9	209.6	202.4
82.5°	137.4	137.4	137.4	137.4	137.4
85°	72.3	79.5	86.8	94.0	101.2
87.5°	43.4	43.4	50.6	57.8	65.1
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)