

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P558507

Luminaire Tested: FSR-12-1-LD4-1HI-35-UNV-93-94-EDD

Issue Date: 7/20/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P558507  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/20/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: FAIL-SAFE  
Catalog Number: FSR-12-1-LD4-1HI-35-UNV-93-94-EDD  
Description: 1X1 FSR TROFFER WITH .156 CLEAR TEMPERED GLASS FIXTURE SIDE AND .187 CLEAR TEMPER  
GLASS ENVIRONMENTAL SIDE LENSES WITH, 80 CRI AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 969.0 lumens  
Efficiency: N/A  
Efficacy: 89.7 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 10.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P558507

CATALOG NUMBER: FSR-12-1-LD4-1HI-35-UNV-93-94-EDD

### Luminous Intensity Polar Plot





TEST NUMBER: P558507

CATALOG NUMBER: FSR-12-1-LD4-1HI-35-UNV-93-94-EDD

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100												100																
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87												87																
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75												75																
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65												65																
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56												56																
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50												50																
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44												44																
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40												40																
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36												36																
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33												33																
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30												30																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5313	5313	5313
5°	5240	5235	5229
10°	5195	5190	5151
15°	5056	5005	4934
20°	4869	4792	4661
25°	4670	4568	4283
30°	4426	4284	3858
35°	4192	3959	3569
40°	3953	3608	3247
45°	3726	3335	2936
50°	3450	3096	2619
55°	3190	2806	2346
60°	2923	2506	2101
65°	2572	2195	1859
70°	2118	1923	1580
75°	1684	1472	1543
80°	1134	1060	992
85°	704	840	988

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3726 cd/sqm

TEST NUMBER: P558507

CATALOG NUMBER: FSR-12-1-LD4-1HI-35-UNV-93-94-EDD

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.9	4.7
10°-20°	126.1	13.0
20°-30°	174.6	18.0
30°-40°	186.1	19.2
40°-50°	169.8	17.5
50°-60°	133.0	13.7
60°-70°	86.7	8.9
70°-80°	38.4	4.0
80°-90°	8.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	346.6	35.8
0°-40°	532.8	55.0
0°-60°	835.6	86.2
0°-90°	969.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	969.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	494	494	494	494	494	
5°	485	484	484	484	484	46
15°	454	454	449	444	443	128
25°	393	391	385	371	361	181
35°	319	317	301	278	272	199
45°	245	240	219	201	193	189
55°	170	165	150	132	125	153
65°	101	95	86	88	73	100
75°	40	38	35	34	37	43
85°	6	6	7	7	8	8
90°	0	0	0	0	0	



TEST NUMBER: P558507

CATALOG NUMBER: FSR-12-1-LD4-1HI-35-UNV-93-94-EDD

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	493.6	493.6	493.6	493.6	493.6
2.5°	490.2	490.2	490.2	489.6	489.6
5°	485.0	484.5	484.5	483.9	483.9
7.5°	481.0	480.5	479.9	479.3	478.2
10°	475.3	475.3	474.8	471.9	471.3
12.5°	466.2	465.6	463.4	459.4	458.2
15°	453.7	453.7	449.1	444.5	442.8
17.5°	440.0	439.4	433.7	429.1	426.8
20°	425.1	424.0	418.3	410.9	406.9
22.5°	408.6	408.6	401.7	392.0	388.0
25°	393.2	390.9	384.6	370.9	360.6
27.5°	375.5	372.1	365.2	345.8	333.8
30°	356.1	354.4	344.7	319.6	310.4
32.5°	337.8	335.0	324.7	298.4	291.0
35°	319.0	316.7	301.3	278.5	271.6
37.5°	300.2	297.3	277.9	259.6	251.1
40°	281.3	277.9	256.8	240.2	231.1
42.5°	263.6	259.1	238.5	220.8	210.6
45°	244.8	239.7	219.1	200.9	192.9
47.5°	226.0	221.4	202.6	183.7	174.6
50°	206.0	202.0	184.9	166.1	156.4
52.5°	189.4	183.2	166.6	147.8	139.8
55°	170.0	164.9	149.5	131.8	125.0
57.5°	152.4	147.2	133.0	116.4	110.7
60°	135.8	128.4	116.4	102.1	97.6
62.5°	117.5	111.8	101.6	89.6	95.3
65°	101.0	95.3	86.2	87.9	73.0
67.5°	82.7	79.9	71.9	63.9	61.6
70°	67.3	63.9	61.1	52.5	50.2
72.5°	53.6	50.2	46.2	41.7	39.9
75°	40.5	37.7	35.4	33.7	37.1
77.5°	28.0	26.8	25.1	23.4	22.8
80°	18.3	17.7	17.1	16.5	16.0
82.5°	10.8	10.8	10.8	10.8	10.8
85°	5.7	6.3	6.8	7.4	8.0
87.5°	3.4	3.4	4.0	4.6	5.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)