

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P558531

Luminaire Tested: FSR-12-1-LD4-1HI-40-UNV-81-85-EDD

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-2019
Report Number: P558531
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FSR-12-1-LD4-1HI-40-UNV-81-85-EDD
Description: 1X1 FSR TROFFER WITH .156 CLEAR PC FIXTURE SIDE AND .187 CLEAR PC ENVIRONMENTAL SI
LENSES WITH, 80 CRI AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 908.0 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
CIE Type: Direct


Input Watts (W): 10.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P558531

CATALOG NUMBER: FSR-12-1-LD4-1HI-40-UNV-81-85-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P558531

CATALOG NUMBER: FSR-12-1-LD4-1HI-40-UNV-81-85-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4978	4978	4978
5°	4911	4905	4899
10°	4868	4863	4828
15°	4737	4689	4623
20°	4564	4489	4367
25°	4375	4280	4013
30°	4148	4015	3616
35°	3928	3710	3344
40°	3704	3381	3044
45°	3492	3125	2751
50°	3232	2900	2453
55°	2989	2629	2198
60°	2740	2349	1968
65°	2409	2055	1742
70°	1986	1800	1482
75°	1580	1381	1447
80°	1060	992	930
85°	655	790	926

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3492 cd/sqm

TEST NUMBER: P558531

CATALOG NUMBER: FSR-12-1-LD4-1HI-40-UNV-81-85-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.1	4.7
10°-20°	118.2	13.0
20°-30°	163.6	18.0
30°-40°	174.4	19.2
40°-50°	159.1	17.5
50°-60°	124.7	13.7
60°-70°	81.2	8.9
70°-80°	36.0	4.0
80°-90°	7.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	324.8	35.8
0°-40°	499.2	55.0
0°-60°	783.0	86.2
0°-90°	908.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	908.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	462	462	462	462	462	
5°	454	454	454	453	453	43
15°	425	425	421	416	415	120
25°	368	366	360	348	338	169
35°	299	297	282	261	254	187
45°	229	225	205	188	181	177
55°	159	154	140	124	117	143
65°	95	89	81	82	68	93
75°	38	35	33	32	35	41
85°	5	6	6	7	8	7
90°	0	0	0	0	0	



TEST NUMBER: P558531

CATALOG NUMBER: FSR-12-1-LD4-1HI-40-UNV-81-85-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	462.5	462.5	462.5	462.5	462.5
2.5°	459.3	459.3	459.3	458.8	458.8
5°	454.5	454.0	454.0	453.4	453.4
7.5°	450.8	450.2	449.7	449.2	448.1
10°	445.4	445.4	444.9	442.2	441.7
12.5°	436.9	436.3	434.2	430.4	429.4
15°	425.1	425.1	420.8	416.5	414.9
17.5°	412.3	411.7	406.4	402.1	400.0
20°	398.4	397.3	391.9	385.0	381.2
22.5°	382.9	382.9	376.4	367.3	363.6
25°	368.4	366.3	360.4	347.6	337.9
27.5°	351.8	348.6	342.2	324.0	312.8
30°	333.7	332.1	323.0	299.4	290.9
32.5°	316.5	313.9	304.2	279.7	272.7
35°	298.9	296.8	282.3	260.9	254.5
37.5°	281.3	278.6	260.4	243.3	235.3
40°	263.6	260.4	240.6	225.1	216.6
42.5°	247.0	242.8	223.5	206.9	197.3
45°	229.4	224.6	205.3	188.2	180.7
47.5°	211.7	207.5	189.8	172.2	163.6
50°	193.0	189.3	173.2	155.6	146.5
52.5°	177.5	171.6	156.1	138.5	131.0
55°	159.3	154.5	140.1	123.5	117.1
57.5°	142.8	138.0	124.6	109.1	103.7
60°	127.3	120.3	109.1	95.7	91.4
62.5°	110.2	104.8	95.2	83.9	89.3
65°	94.6	89.3	80.7	82.3	68.4
67.5°	77.5	74.9	67.4	59.9	57.7
70°	63.1	59.9	57.2	49.2	47.1
72.5°	50.3	47.1	43.3	39.0	37.4
75°	38.0	35.3	33.2	31.5	34.8
77.5°	26.2	25.1	23.5	21.9	21.4
80°	17.1	16.6	16.0	15.5	15.0
82.5°	10.2	10.2	10.2	10.2	10.2
85°	5.3	5.9	6.4	7.0	7.5
87.5°	3.2	3.2	3.7	4.3	4.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)