

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P558990

Luminaire Tested: FSR-12-1-LD4-1STD-50-UNV-81-97-EDD-90

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-2019
Report Number: P558990
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FSR-12-1-LD4-1STD-50-UNV-81-97-EDD-90
Description: 1X1 FSR TROFFER WITH .156 CLEAR PC FIXTURE SIDE AND .375 CLEAR TEMPERED GLASS ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 638.0 lumens
Efficiency: N/A
Efficacy: 76.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
CIE Type: Direct


Input Watts (W): 8.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P558990

CATALOG NUMBER: FSR-12-1-LD4-1STD-50-UNV-81-97-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P558990

CATALOG NUMBER: FSR-12-1-LD4-1STD-50-UNV-81-97-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20											20
RC	80								50											0
RW	70	50	30	10					70	50	30	10								0
RCR																				
0	119	119	119	119					116	116	116	116								100
1	110	106	102	99					108	104	100	97								87
2	101	94	88	83					99	92	87	82								75
3	93	84	77	71					91	82	76	70								65
4	86	75	67	61					84	74	66	61								56
5	80	68	60	54					78	67	59	53								50
6	74	62	53	48					72	61	53	47								44
7	69	56	48	43					67	56	48	42								40
8	65	52	44	38					63	51	44	38								36
9	61	48	40	35					59	47	40	35								33
10	57	44	37	32					56	44	37	32								30

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3498	3498	3498
5°	3451	3447	3442
10°	3421	3417	3392
15°	3329	3295	3249
20°	3206	3155	3069
25°	3075	3007	2820
30°	2913	2820	2541
35°	2759	2607	2349
40°	2602	2376	2139
45°	2454	2197	1933
50°	2271	2038	1723
55°	2102	1847	1544
60°	1925	1649	1382
65°	1694	1444	1225
70°	1394	1265	1042
75°	1110	969	1015
80°	744	700	651
85°	469	556	655

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2454 cd/sqm



TEST NUMBER: P558990

CATALOG NUMBER: FSR-12-1-LD4-1STD-50-UNV-81-97-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.3	4.7
10°-20°	83.0	13.0
20°-30°	114.9	18.0
30°-40°	122.6	19.2
40°-50°	111.8	17.5
50°-60°	87.6	13.7
60°-70°	57.1	8.9
70°-80°	25.3	4.0
80°-90°	5.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	228.2	35.8
0°-40°	350.8	55.0
0°-60°	550.2	86.2
0°-90°	638.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	638.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	325	325	325	325	325	
5°	319	319	319	319	319	30
15°	299	299	296	293	292	84
25°	259	257	253	244	237	119
35°	210	208	198	183	179	131
45°	161	158	144	132	127	124
55°	112	109	98	87	82	100
65°	66	63	57	58	48	66
75°	27	25	23	22	24	29
85°	4	4	4	5	5	5
90°	0	0	0	0	0	



TEST NUMBER: P558990

CATALOG NUMBER: FSR-12-1-LD4-1STD-50-UNV-81-97-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	325.0	325.0	325.0	325.0	325.0
2.5°	322.7	322.7	322.7	322.4	322.4
5°	319.4	319.0	319.0	318.6	318.6
7.5°	316.7	316.3	316.0	315.6	314.8
10°	313.0	313.0	312.6	310.7	310.3
12.5°	307.0	306.6	305.1	302.4	301.7
15°	298.7	298.7	295.7	292.7	291.6
17.5°	289.7	289.3	285.5	282.5	281.0
20°	279.9	279.2	275.4	270.5	267.9
22.5°	269.0	269.0	264.5	258.1	255.5
25°	258.9	257.4	253.2	244.2	237.4
27.5°	247.2	245.0	240.5	227.7	219.8
30°	234.4	233.3	226.9	210.4	204.4
32.5°	222.4	220.5	213.8	196.5	191.6
35°	210.0	208.5	198.4	183.3	178.8
37.5°	197.6	195.7	183.0	170.9	165.3
40°	185.2	183.0	169.1	158.2	152.2
42.5°	173.6	170.6	157.0	145.4	138.6
45°	161.2	157.8	144.3	132.2	127.0
47.5°	148.8	145.8	133.4	121.0	115.0
50°	135.6	133.0	121.7	109.3	102.9
52.5°	124.7	120.6	109.7	97.3	92.0
55°	112.0	108.6	98.4	86.8	82.3
57.5°	100.3	96.9	87.5	76.6	72.9
60°	89.4	84.5	76.6	67.3	64.2
62.5°	77.4	73.6	66.9	59.0	62.7
65°	66.5	62.7	56.7	57.9	48.1
67.5°	54.5	52.6	47.3	42.1	40.6
70°	44.3	42.1	40.2	34.6	33.1
72.5°	35.3	33.1	30.4	27.4	26.3
75°	26.7	24.8	23.3	22.2	24.4
77.5°	18.4	17.7	16.5	15.4	15.0
80°	12.0	11.6	11.3	10.9	10.5
82.5°	7.1	7.1	7.1	7.1	7.1
85°	3.8	4.1	4.5	4.9	5.3
87.5°	2.3	2.3	2.6	3.0	3.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)