

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P559035

Luminaire Tested: FSR-12-1-LD4-2HI-35-UNV-80-94-EDD

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-2019
Report Number: P559035
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FSR-12-1-LD4-2HI-35-UNV-80-94-EDD
Description: 1X1 FSR TROFFER WITH .125 PRISMATIC ACRYLIC FIXTURE SIDE AND .187 CLEAR TEMPERED G ENVIRONMENTAL SIDE LENSES WITH, 80 CRI AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1935.0 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
CIE Type: Direct

Input Watts (W): 21.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P559035
CATALOG NUMBER: FSR-12-1-LD4-2HI-35-UNV-80-94-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P559035

CATALOG NUMBER: FSR-12-1-LD4-2HI-35-UNV-80-94-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10610	10610	10610
5°	10466	10453	10441
10°	10375	10363	10287
15°	10095	9994	9853
20°	9724	9567	9307
25°	9324	9121	8554
30°	8837	8555	7705
35°	8370	7907	7127
40°	7894	7206	6485
45°	7441	6661	5862
50°	6889	6183	5228
55°	6373	5602	4682
60°	5838	5005	4196
65°	5137	4383	3716
70°	4233	3836	3157
75°	3365	2936	3082
80°	2263	2120	1977
85°	1408	1692	1976

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7441 cd/sqm



TEST NUMBER: P559035

CATALOG NUMBER: FSR-12-1-LD4-2HI-35-UNV-80-94-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.8	4.7
10°-20°	251.8	13.0
20°-30°	348.6	18.0
30°-40°	371.7	19.2
40°-50°	339.1	17.5
50°-60°	265.7	13.7
60°-70°	173.2	8.9
70°-80°	76.7	4.0
80°-90°	16.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	692.2	35.8
0°-40°	1063.9	55.0
0°-60°	1668.7	86.2
0°-90°	1935.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1935.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	986	986	986	986	986	
5°	969	967	967	966	966	92
15°	906	906	897	888	884	255
25°	785	781	768	741	720	360
35°	637	632	602	556	542	398
45°	489	479	438	401	385	377
55°	340	329	298	263	250	305
65°	202	190	172	176	146	199
75°	81	75	71	67	74	87
85°	11	12	14	15	16	16
90°	0	0	0	0	0	



TEST NUMBER: P559035

CATALOG NUMBER: FSR-12-1-LD4-2HI-35-UNV-80-94-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	985.7	985.7	985.7	985.7	985.7
2.5°	978.8	978.8	978.8	977.7	977.7
5°	968.6	967.4	967.4	966.3	966.3
7.5°	960.6	959.5	958.3	957.2	954.9
10°	949.2	949.2	948.1	942.4	941.2
12.5°	931.0	929.8	925.3	917.3	915.0
15°	905.9	905.9	896.8	887.7	884.2
17.5°	878.6	877.4	866.0	856.9	852.3
20°	848.9	846.6	835.2	820.4	812.5
22.5°	815.9	815.9	802.2	782.8	774.9
25°	785.1	780.6	768.0	740.7	720.2
27.5°	749.8	743.0	729.3	690.5	666.6
30°	711.0	707.6	688.3	638.1	619.9
32.5°	674.6	668.9	648.4	596.0	581.1
35°	637.0	632.4	601.7	556.1	542.4
37.5°	599.4	593.7	554.9	518.5	501.4
40°	561.8	554.9	512.8	479.7	461.5
42.5°	526.4	517.3	476.3	441.0	420.5
45°	488.8	478.6	437.6	401.1	385.1
47.5°	451.2	442.1	404.5	366.9	348.7
50°	411.4	403.4	369.2	331.6	312.2
52.5°	378.3	365.8	332.7	295.1	279.2
55°	339.6	329.3	298.5	263.2	249.5
57.5°	304.2	294.0	265.5	232.5	221.1
60°	271.2	256.4	232.5	204.0	194.9
62.5°	234.7	223.3	202.8	178.9	190.3
65°	201.7	190.3	172.1	175.5	145.9
67.5°	165.2	159.5	143.6	127.6	123.1
70°	134.5	127.6	121.9	104.8	100.3
72.5°	107.1	100.3	92.3	83.2	79.8
75°	80.9	75.2	70.6	67.2	74.1
77.5°	55.8	53.6	50.1	46.7	45.6
80°	36.5	35.3	34.2	33.0	31.9
82.5°	21.7	21.7	21.7	21.7	21.7
85°	11.4	12.5	13.7	14.8	16.0
87.5°	6.8	6.8	8.0	9.1	10.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)