

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P559041

Luminaire Tested: FSR-12-1-LD4-2HI-35-UNV-81-84-EDD

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-2019
Report Number: P559041
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FSR-12-1-LD4-2HI-35-UNV-81-84-EDD
Description: 1X1 FSR TROFFER WITH .156 CLEAR PC FIXTURE SIDE AND .125 CLEAR PC ENVIRONMENTAL SI
LENSES WITH, 80 CRI AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1834.0 lumens
Efficiency: N/A
Efficacy: 84.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
CIE Type: Direct


Input Watts (W): 21.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P559041

CATALOG NUMBER: FSR-12-1-LD4-2HI-35-UNV-81-84-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P559041

CATALOG NUMBER: FSR-12-1-LD4-2HI-35-UNV-81-84-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10056	10056	10056
5°	9919	9907	9896
10°	9834	9822	9751
15°	9568	9472	9339
20°	9216	9069	8821
25°	8837	8645	8107
30°	8376	8108	7302
35°	7933	7493	6755
40°	7481	6829	6146
45°	7053	6313	5556
50°	6529	5859	4955
55°	6039	5311	4438
60°	5533	4743	3976
65°	4870	4154	3520
70°	4009	3638	2990
75°	3190	2786	2920
80°	2145	2008	1872
85°	1334	1606	1865

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7053 cd/sqm



TEST NUMBER: P559041

CATALOG NUMBER: FSR-12-1-LD4-2HI-35-UNV-81-84-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	4.7
10°-20°	238.7	13.0
20°-30°	330.4	18.0
30°-40°	352.3	19.2
40°-50°	321.4	17.5
50°-60°	251.8	13.7
60°-70°	164.1	8.9
70°-80°	72.7	4.0
80°-90°	15.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	656.0	35.8
0°-40°	1008.4	55.0
0°-60°	1581.6	86.2
0°-90°	1834.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1834.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	934	934	934	934	934	
5°	918	917	917	916	916	87
15°	859	859	850	841	838	241
25°	744	740	728	702	683	342
35°	604	599	570	527	514	377
45°	463	454	415	380	365	357
55°	322	312	283	250	236	289
65°	191	180	163	166	138	188
75°	77	71	67	64	70	82
85°	11	12	13	14	15	15
90°	0	0	0	0	0	

TEST NUMBER: P559041

CATALOG NUMBER: FSR-12-1-LD4-2HI-35-UNV-81-84-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	934.2	934.2	934.2	934.2	934.2
2.5°	927.7	927.7	927.7	926.7	926.7
5°	918.0	916.9	916.9	915.9	915.9
7.5°	910.5	909.4	908.3	907.2	905.1
10°	899.7	899.7	898.6	893.2	892.1
12.5°	882.4	881.3	877.0	869.4	867.3
15°	858.6	858.6	850.0	841.3	838.1
17.5°	832.7	831.6	820.8	812.2	807.9
20°	804.6	802.5	791.7	777.6	770.1
22.5°	773.3	773.3	760.3	742.0	734.4
25°	744.1	739.8	727.9	702.0	682.6
27.5°	710.7	704.2	691.2	654.5	631.8
30°	673.9	670.7	652.3	604.8	587.5
32.5°	639.4	634.0	614.5	564.8	550.8
35°	603.7	599.4	570.2	527.0	514.1
37.5°	568.1	562.7	526.0	491.4	475.2
40°	532.4	526.0	486.0	454.7	437.4
42.5°	499.0	490.3	451.4	418.0	398.5
45°	463.3	453.6	414.7	380.2	365.0
47.5°	427.7	419.0	383.4	347.8	330.5
50°	389.9	382.3	349.9	314.3	295.9
52.5°	358.6	346.7	315.4	279.7	264.6
55°	321.8	312.1	283.0	249.5	236.5
57.5°	288.4	278.6	251.6	220.3	209.5
60°	257.0	243.0	220.3	193.3	184.7
62.5°	222.5	211.7	192.2	169.6	180.4
65°	191.2	180.4	163.1	166.3	138.2
67.5°	156.6	151.2	136.1	121.0	116.6
70°	127.4	121.0	115.6	99.4	95.0
72.5°	101.5	95.0	87.5	78.8	75.6
75°	76.7	71.3	67.0	63.7	70.2
77.5°	52.9	50.8	47.5	44.3	43.2
80°	34.6	33.5	32.4	31.3	30.2
82.5°	20.5	20.5	20.5	20.5	20.5
85°	10.8	11.9	13.0	14.0	15.1
87.5°	6.5	6.5	7.6	8.6	9.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)