

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P559037

Luminaire Tested: FSR-12-1-LD4-2HI-35-UNV-80-96-EDD

Issue Date: 7/20/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P559037  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/20/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: FAIL-SAFE  
Catalog Number: FSR-12-1-LD4-2HI-35-UNV-80-96-EDD  
Description: 1X1 FSR TROFFER WITH .125 PRISMATIC ACRYLIC FIXTURE SIDE AND .250 CLEAR TEMPERED G ENVIRONMENTAL SIDE LENSES WITH, 80 CRI AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1913.0 lumens  
Efficiency: N/A  
Efficacy: 88.6 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P559037

CATALOG NUMBER: FSR-12-1-LD4-2HI-35-UNV-80-96-EDD

### Luminous Intensity Polar Plot





TEST NUMBER: P559037

CATALOG NUMBER: FSR-12-1-LD4-2HI-35-UNV-80-96-EDD

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10489	10489	10489
5°	10347	10334	10322
10°	10257	10245	10170
15°	9980	9880	9742
20°	9614	9459	9200
25°	9219	9018	8456
30°	8738	8457	7617
35°	8274	7816	7046
40°	7804	7123	6410
45°	7357	6585	5797
50°	6810	6112	5169
55°	6300	5540	4630
60°	5772	4947	4146
65°	5079	4332	3673
70°	4183	3792	3119
75°	3327	2903	3044
80°	2232	2095	1953
85°	1396	1667	1951

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7357 cd/sqm



TEST NUMBER: P559037

CATALOG NUMBER: FSR-12-1-LD4-2HI-35-UNV-80-96-EDD

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.7	4.7
10°-20°	248.9	13.0
20°-30°	344.6	18.0
30°-40°	367.5	19.2
40°-50°	335.3	17.5
50°-60°	262.6	13.7
60°-70°	171.2	8.9
70°-80°	75.8	4.0
80°-90°	16.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	684.3	35.8
0°-40°	1051.8	55.0
0°-60°	1649.7	86.2
0°-90°	1913.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1913.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	974	974	974	974	974	
5°	958	956	956	955	955	91
15°	896	896	887	878	874	252
25°	776	772	759	732	712	356
35°	630	625	595	550	536	394
45°	483	473	433	396	381	372
55°	336	326	295	260	247	301
65°	199	188	170	174	144	196
75°	80	74	70	66	73	86
85°	11	12	14	15	16	16
90°	0	0	0	0	0	



TEST NUMBER: P559037

CATALOG NUMBER: FSR-12-1-LD4-2HI-35-UNV-80-96-EDD

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	974.5	974.5	974.5	974.5	974.5
2.5°	967.7	967.7	967.7	966.6	966.6
5°	957.6	956.4	956.4	955.3	955.3
7.5°	949.7	948.5	947.4	946.3	944.0
10°	938.4	938.4	937.3	931.6	930.5
12.5°	920.4	919.3	914.8	906.9	904.6
15°	895.6	895.6	886.6	877.6	874.2
17.5°	868.6	867.4	856.2	847.2	842.7
20°	839.3	837.0	825.8	811.1	803.2
22.5°	806.6	806.6	793.1	773.9	766.0
25°	776.2	771.7	759.3	732.3	712.0
27.5°	741.3	734.5	721.0	682.7	659.0
30°	703.0	699.6	680.4	630.9	612.8
32.5°	666.9	661.3	641.0	589.2	574.5
35°	629.7	625.2	594.8	549.8	536.2
37.5°	592.6	586.9	548.6	512.6	495.7
40°	555.4	548.6	506.9	474.3	456.2
42.5°	520.5	511.4	470.9	436.0	415.7
45°	483.3	473.1	432.6	396.5	380.8
47.5°	446.1	437.1	399.9	362.7	344.7
50°	406.7	398.8	365.0	327.8	308.7
52.5°	374.0	361.6	328.9	291.8	276.0
55°	335.7	325.6	295.2	260.2	246.7
57.5°	300.8	290.6	262.5	229.8	218.5
60°	268.1	253.5	229.8	201.7	192.6
62.5°	232.1	220.8	200.5	176.9	188.1
65°	199.4	188.1	170.1	173.5	144.2
67.5°	163.3	157.7	141.9	126.2	121.7
70°	132.9	126.2	120.5	103.6	99.1
72.5°	105.9	99.1	91.2	82.2	78.9
75°	80.0	74.4	69.8	66.5	73.2
77.5°	55.2	52.9	49.6	46.2	45.1
80°	36.0	34.9	33.8	32.7	31.5
82.5°	21.4	21.4	21.4	21.4	21.4
85°	11.3	12.4	13.5	14.6	15.8
87.5°	6.8	6.8	7.9	9.0	10.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)