

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P559195

Luminaire Tested: FSR-12-1-LD4-2HI-50-UNV-82-94-EDD

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-2019
Report Number: P559195
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FSR-12-1-LD4-2HI-50-UNV-82-94-EDD
Description: 1X1 FSR TROFFER WITH .187 CLEAR PC FIXTURE SIDE AND .187 CLEAR TEMPERED GLASS ENVIRONMENTAL SIDE LENSES WITH, 80 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1848.0 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
CIE Type: Direct


Input Watts (W): 21.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P559195

CATALOG NUMBER: FSR-12-1-LD4-2HI-50-UNV-82-94-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P559195

CATALOG NUMBER: FSR-12-1-LD4-2HI-50-UNV-82-94-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87					87			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75					75			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65					65			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56					56			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50					50			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44					44			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40					40			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36					36			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33					33			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30					30			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10132	10132	10132
5°	9995	9983	9971
10°	9908	9896	9825
15°	9641	9545	9411
20°	9287	9137	8888
25°	8905	8712	8169
30°	8441	8170	7358
35°	7993	7550	6807
40°	7539	6881	6192
45°	7107	6361	5599
50°	6579	5905	4994
55°	6086	5350	4472
60°	5576	4779	4006
65°	4905	4185	3548
70°	4041	3663	3015
75°	3215	2807	2940
80°	2157	2021	1891
85°	1346	1618	1877

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7107 cd/sqm

TEST NUMBER: P559195

CATALOG NUMBER: FSR-12-1-LD4-2HI-50-UNV-82-94-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.6	4.7
10°-20°	240.5	13.0
20°-30°	332.9	18.0
30°-40°	355.0	19.2
40°-50°	323.9	17.5
50°-60°	253.7	13.7
60°-70°	165.4	8.9
70°-80°	73.3	4.0
80°-90°	15.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	661.0	35.8
0°-40°	1016.1	55.0
0°-60°	1593.7	86.2
0°-90°	1848.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1848.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	941	941	941	941	941	
5°	925	924	924	923	923	88
15°	865	865	856	848	844	243
25°	750	746	734	707	688	344
35°	608	604	575	531	518	380
45°	467	457	418	383	368	360
55°	324	314	285	251	238	291
65°	193	182	164	168	139	190
75°	77	72	68	64	71	83
85°	11	12	13	14	15	15
90°	0	0	0	0	0	



TEST NUMBER: P559195

CATALOG NUMBER: FSR-12-1-LD4-2HI-50-UNV-82-94-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	941.3	941.3	941.3	941.3	941.3
2.5°	934.8	934.8	934.8	933.7	933.7
5°	925.0	923.9	923.9	922.8	922.8
7.5°	917.4	916.3	915.2	914.1	912.0
10°	906.5	906.5	905.4	900.0	898.9
12.5°	889.1	888.0	883.7	876.1	873.9
15°	865.2	865.2	856.5	847.8	844.5
17.5°	839.0	838.0	827.1	818.4	814.0
20°	810.8	808.6	797.7	783.5	775.9
22.5°	779.2	779.2	766.1	747.6	740.0
25°	749.8	745.5	733.5	707.4	687.8
27.5°	716.1	709.5	696.5	659.5	636.6
30°	679.1	675.8	657.3	609.4	592.0
32.5°	644.3	638.8	619.2	569.2	555.0
35°	608.3	604.0	574.6	531.1	518.0
37.5°	572.4	567.0	530.0	495.2	478.8
40°	536.5	530.0	489.7	458.2	440.7
42.5°	502.8	494.1	454.9	421.2	401.6
45°	466.9	457.1	417.9	383.1	367.8
47.5°	431.0	422.2	386.3	350.4	333.0
50°	392.9	385.2	352.6	316.7	298.2
52.5°	361.3	349.3	317.8	281.9	266.6
55°	324.3	314.5	285.1	251.4	238.3
57.5°	290.6	280.8	253.6	222.0	211.1
60°	259.0	244.9	222.0	194.8	186.1
62.5°	224.2	213.3	193.7	170.9	181.7
65°	192.6	181.7	164.3	167.6	139.3
67.5°	157.8	152.4	137.1	121.9	117.5
70°	128.4	121.9	116.4	100.1	95.8
72.5°	102.3	95.8	88.1	79.4	76.2
75°	77.3	71.8	67.5	64.2	70.7
77.5°	53.3	51.1	47.9	44.6	43.5
80°	34.8	33.7	32.6	31.6	30.5
82.5°	20.7	20.7	20.7	20.7	20.7
85°	10.9	12.0	13.1	14.1	15.2
87.5°	6.5	6.5	7.6	8.7	9.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)