

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P559551

Luminaire Tested: FSR-12-1-LD4-2STD-50-UNV-80-97-EDD

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-2019
Report Number: P559551
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FSR-12-1-LD4-2STD-50-UNV-80-97-EDD
Description: 1X1 FSR TROFFER WITH .125 PRISMATIC ACRYLIC FIXTURE SIDE AND .375 CLEAR TEMPERED G ENVIRONMENTAL SIDE LENSES WITH, 80 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1545.0 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
CIE Type: Direct


Input Watts (W): 16.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P559551

CATALOG NUMBER: FSR-12-1-LD4-2STD-50-UNV-80-97-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P559551

CATALOG NUMBER: FSR-12-1-LD4-2STD-50-UNV-80-97-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|-----|---|--|---|
| RF | 20 | | | | | 20 | | | | | 20 | | | | | 20 | | | | | 20 | | | | | |
| RC | 80 | | | | | 70 | | | | | 50 | | | | | 30 | | | | | 10 | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | 100 | | | |
| 1 | 110 | 106 | 102 | 99 | 108 | 104 | 100 | 97 | 100 | 97 | 94 | 96 | 94 | 91 | 92 | 90 | 89 | 87 | | | | | 87 | | | |
| 2 | 101 | 94 | 88 | 83 | 99 | 92 | 87 | 82 | 89 | 84 | 80 | 86 | 82 | 78 | 83 | 79 | 77 | 75 | | | | | 75 | | | |
| 3 | 93 | 84 | 77 | 71 | 91 | 82 | 76 | 70 | 79 | 74 | 69 | 77 | 72 | 68 | 74 | 70 | 67 | 65 | | | | | 65 | | | |
| 4 | 86 | 75 | 67 | 61 | 84 | 74 | 66 | 61 | 72 | 65 | 60 | 69 | 64 | 59 | 67 | 62 | 58 | 56 | | | | | 56 | | | |
| 5 | 80 | 68 | 60 | 54 | 78 | 67 | 59 | 53 | 65 | 58 | 53 | 63 | 57 | 52 | 61 | 56 | 52 | 50 | | | | | 50 | | | |
| 6 | 74 | 62 | 53 | 48 | 72 | 61 | 53 | 47 | 59 | 52 | 47 | 57 | 51 | 47 | 56 | 50 | 46 | 44 | | | | | 44 | | | |
| 7 | 69 | 56 | 48 | 43 | 67 | 56 | 48 | 42 | 54 | 47 | 42 | 53 | 46 | 42 | 51 | 46 | 42 | 40 | | | | | 40 | | | |
| 8 | 65 | 52 | 44 | 38 | 63 | 51 | 44 | 38 | 50 | 43 | 38 | 49 | 42 | 38 | 48 | 42 | 38 | 36 | | | | | 36 | | | |
| 9 | 61 | 48 | 40 | 35 | 59 | 47 | 40 | 35 | 46 | 39 | 35 | 45 | 39 | 34 | 44 | 38 | 34 | 33 | | | | | 33 | | | |
| 10 | 57 | 44 | 37 | 32 | 56 | 44 | 37 | 32 | 43 | 36 | 32 | 42 | 36 | 32 | 41 | 36 | 32 | 30 | | | | | 30 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 45° | 90° |
|-----|------|------|------|
| 0° | 8471 | 8471 | 8471 |
| 5° | 8357 | 8346 | 8336 |
| 10° | 8284 | 8274 | 8214 |
| 15° | 8060 | 7979 | 7867 |
| 20° | 7764 | 7639 | 7431 |
| 25° | 7445 | 7283 | 6829 |
| 30° | 7056 | 6830 | 6151 |
| 35° | 6683 | 6313 | 5691 |
| 40° | 6302 | 5753 | 5178 |
| 45° | 5941 | 5319 | 4681 |
| 50° | 5499 | 4937 | 4175 |
| 55° | 5088 | 4474 | 3740 |
| 60° | 4661 | 3996 | 3350 |
| 65° | 4101 | 3500 | 2967 |
| 70° | 3380 | 3065 | 2521 |
| 75° | 2687 | 2346 | 2458 |
| 80° | 1804 | 1692 | 1581 |
| 85° | 1124 | 1346 | 1568 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5941 cd/sqm



TEST NUMBER: P559551

CATALOG NUMBER: FSR-12-1-LD4-2STD-50-UNV-80-97-EDD

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 73.3 | 4.7 |
| 10°-20° | 201.1 | 13.0 |
| 20°-30° | 278.3 | 18.0 |
| 30°-40° | 296.8 | 19.2 |
| 40°-50° | 270.8 | 17.5 |
| 50°-60° | 212.1 | 13.7 |
| 60°-70° | 138.2 | 8.9 |
| 70°-80° | 61.3 | 4.0 |
| 80°-90° | 13.2 | 0.9 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 552.7 | 35.8 |
| 0°-40° | 849.5 | 55.0 |
| 0°-60° | 1332.4 | 86.2 |
| 0°-90° | 1545.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1545.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 22.5° | 45° | 67.5° | 90° | Flux |
|-----|-----|-------|-----|-------|-----|------|
| 0° | 787 | 787 | 787 | 787 | 787 | |
| 5° | 773 | 772 | 772 | 772 | 772 | 73 |
| 15° | 723 | 723 | 716 | 709 | 706 | 203 |
| 25° | 627 | 623 | 613 | 591 | 575 | 288 |
| 35° | 509 | 505 | 480 | 444 | 433 | 318 |
| 45° | 390 | 382 | 349 | 320 | 308 | 301 |
| 55° | 271 | 263 | 238 | 210 | 199 | 243 |
| 65° | 161 | 152 | 137 | 140 | 116 | 159 |
| 75° | 65 | 60 | 56 | 54 | 59 | 69 |
| 85° | 9 | 10 | 11 | 12 | 13 | 13 |
| 90° | 0 | 0 | 0 | 0 | 0 | |



TEST NUMBER: P559551

CATALOG NUMBER: FSR-12-1-LD4-2STD-50-UNV-80-97-EDD

CANDELA DISTRIBUTION (FULL):

| | 0° | 22.5° | 45° | 67.5° | 90° |
|-------|-------|-------|-------|-------|-------|
| 0° | 787.0 | 787.0 | 787.0 | 787.0 | 787.0 |
| 2.5° | 781.5 | 781.5 | 781.5 | 780.6 | 780.6 |
| 5° | 773.4 | 772.4 | 772.4 | 771.5 | 771.5 |
| 7.5° | 767.0 | 766.1 | 765.2 | 764.3 | 762.4 |
| 10° | 757.9 | 757.9 | 757.0 | 752.4 | 751.5 |
| 12.5° | 743.3 | 742.4 | 738.8 | 732.4 | 730.6 |
| 15° | 723.3 | 723.3 | 716.0 | 708.8 | 706.0 |
| 17.5° | 701.5 | 700.6 | 691.5 | 684.2 | 680.6 |
| 20° | 677.8 | 676.0 | 666.9 | 655.1 | 648.7 |
| 22.5° | 651.4 | 651.4 | 640.5 | 625.1 | 618.7 |
| 25° | 626.9 | 623.2 | 613.2 | 591.4 | 575.0 |
| 27.5° | 598.7 | 593.2 | 582.3 | 551.4 | 532.3 |
| 30° | 567.7 | 565.0 | 549.5 | 509.5 | 494.9 |
| 32.5° | 538.6 | 534.1 | 517.7 | 475.8 | 464.0 |
| 35° | 508.6 | 505.0 | 480.4 | 444.0 | 433.1 |
| 37.5° | 478.6 | 474.0 | 443.1 | 414.0 | 400.3 |
| 40° | 448.5 | 443.1 | 409.4 | 383.0 | 368.5 |
| 42.5° | 420.3 | 413.1 | 380.3 | 352.1 | 335.7 |
| 45° | 390.3 | 382.1 | 349.4 | 320.3 | 307.5 |
| 47.5° | 360.3 | 353.0 | 323.0 | 293.0 | 278.4 |
| 50° | 328.4 | 322.1 | 294.8 | 264.8 | 249.3 |
| 52.5° | 302.1 | 292.1 | 265.7 | 235.6 | 222.9 |
| 55° | 271.1 | 262.9 | 238.4 | 210.2 | 199.3 |
| 57.5° | 242.9 | 234.7 | 212.0 | 185.6 | 176.5 |
| 60° | 216.5 | 204.7 | 185.6 | 162.9 | 155.6 |
| 62.5° | 187.4 | 178.3 | 161.9 | 142.8 | 151.9 |
| 65° | 161.0 | 151.9 | 137.4 | 140.1 | 116.5 |
| 67.5° | 131.9 | 127.4 | 114.6 | 101.9 | 98.3 |
| 70° | 107.4 | 101.9 | 97.4 | 83.7 | 80.1 |
| 72.5° | 85.5 | 80.1 | 73.7 | 66.4 | 63.7 |
| 75° | 64.6 | 60.0 | 56.4 | 53.7 | 59.1 |
| 77.5° | 44.6 | 42.8 | 40.0 | 37.3 | 36.4 |
| 80° | 29.1 | 28.2 | 27.3 | 26.4 | 25.5 |
| 82.5° | 17.3 | 17.3 | 17.3 | 17.3 | 17.3 |
| 85° | 9.1 | 10.0 | 10.9 | 11.8 | 12.7 |
| 87.5° | 5.5 | 5.5 | 6.4 | 7.3 | 8.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

(END OF REPORT)