

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P559561

Luminaire Tested: FSR-12-1-LD4-2STD-50-UNV-81-88-EDD

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-2019
Report Number: P559561
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FSR-12-1-LD4-2STD-50-UNV-81-88-EDD
Description: 1X1 FSR TROFFER WITH .156 CLEAR PC FIXTURE SIDE AND .500 CLEAR PC ENVIRONMENTAL SI
LENSES WITH, 80 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1297.0 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
CIE Type: Direct


Input Watts (W): 16.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P559561

CATALOG NUMBER: FSR-12-1-LD4-2STD-50-UNV-81-88-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P559561

CATALOG NUMBER: FSR-12-1-LD4-2STD-50-UNV-81-88-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87									87																			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75									75																			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65									65																			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56									56																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50									50																			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44									44																			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40									40																			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36									36																			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33									33																			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30									30																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7112	7112	7112
5°	7015	7007	6998
10°	6954	6946	6896
15°	6766	6698	6605
20°	6518	6413	6238
25°	6250	6114	5733
30°	5924	5734	5164
35°	5611	5299	4778
40°	5290	4829	4346
45°	4988	4465	3930
50°	4617	4145	3505
55°	4271	3755	3140
60°	3914	3354	2812
65°	3443	2937	2491
70°	2836	2571	2115
75°	2254	1971	2063
80°	1512	1420	1327
85°	939	1136	1321

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4988 cd/sqm

TEST NUMBER: P559561

CATALOG NUMBER: FSR-12-1-LD4-2STD-50-UNV-81-88-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.5	4.7
10°-20°	168.8	13.0
20°-30°	233.7	18.0
30°-40°	249.2	19.2
40°-50°	227.3	17.5
50°-60°	178.1	13.7
60°-70°	116.1	8.9
70°-80°	51.4	4.0
80°-90°	11.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	464.0	35.8
0°-40°	713.1	55.0
0°-60°	1118.5	86.2
0°-90°	1297.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1297.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	661	661	661	661	661	
5°	649	648	648	648	648	62
15°	607	607	601	595	593	171
25°	526	523	515	496	483	242
35°	427	424	403	373	364	267
45°	328	321	293	269	258	252
55°	228	221	200	176	167	204
65°	135	128	115	118	98	133
75°	54	50	47	45	50	58
85°	8	8	9	10	11	11
90°	0	0	0	0	0	



TEST NUMBER: P559561

CATALOG NUMBER: FSR-12-1-LD4-2STD-50-UNV-81-88-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	660.7	660.7	660.7	660.7	660.7
2.5°	656.1	656.1	656.1	655.3	655.3
5°	649.2	648.5	648.5	647.7	647.7
7.5°	643.9	643.1	642.3	641.6	640.1
10°	636.2	636.2	635.5	631.7	630.9
12.5°	624.0	623.2	620.2	614.8	613.3
15°	607.2	607.2	601.1	595.0	592.7
17.5°	588.9	588.1	580.5	574.4	571.3
20°	569.0	567.5	559.9	549.9	544.6
22.5°	546.9	546.9	537.7	524.7	519.4
25°	526.2	523.2	514.8	496.5	482.7
27.5°	502.6	498.0	488.8	462.9	446.8
30°	476.6	474.3	461.3	427.7	415.5
32.5°	452.2	448.3	434.6	399.5	389.5
35°	427.0	423.9	403.3	372.7	363.6
37.5°	401.8	397.9	372.0	347.5	336.1
40°	376.5	372.0	343.7	321.6	309.3
42.5°	352.9	346.8	319.3	295.6	281.8
45°	327.7	320.8	293.3	268.9	258.2
47.5°	302.5	296.3	271.1	245.9	233.7
50°	275.7	270.4	247.5	222.3	209.3
52.5°	253.6	245.2	223.0	197.8	187.1
55°	227.6	220.7	200.1	176.4	167.3
57.5°	203.9	197.1	178.0	155.8	148.2
60°	181.8	171.9	155.8	136.7	130.6
62.5°	157.3	149.7	136.0	119.9	127.6
65°	135.2	127.6	115.3	117.6	97.8
67.5°	110.7	106.9	96.2	85.5	82.5
70°	90.1	85.5	81.7	70.3	67.2
72.5°	71.8	67.2	61.9	55.8	53.5
75°	54.2	50.4	47.4	45.1	49.6
77.5°	37.4	35.9	33.6	31.3	30.6
80°	24.4	23.7	22.9	22.1	21.4
82.5°	14.5	14.5	14.5	14.5	14.5
85°	7.6	8.4	9.2	9.9	10.7
87.5°	4.6	4.6	5.3	6.1	6.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)