

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P559797

Luminaire Tested: FSR-12-2-LD4-1LO-35-UNV-80-86-EDD

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-2019
Report Number: P559797
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FSR-12-2-LD4-1LO-35-UNV-80-86-EDD
Description: 1X2 FSR TROFFER WITH .125 PRISMATIC ACRYLIC FIXTURE SIDE AND .250 CLEAR PC ENVIRON
SIDE LENSES WITH, 80 CRI AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1104.0 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 2' x H: 0')
CIE Type: Direct


Input Watts (W): 11.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P559797

CATALOG NUMBER: FSR-12-2-LD4-1LO-35-UNV-80-86-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P559797

CATALOG NUMBER: FSR-12-2-LD4-1LO-35-UNV-80-86-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	47	56	50	46	44
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3027	3027	3027
5°	2985	2982	2978
10°	2960	2956	2935
15°	2880	2851	2811
20°	2774	2729	2655
25°	2660	2602	2440
30°	2521	2440	2198
35°	2388	2256	2033
40°	2252	2056	1850
45°	2123	1901	1672
50°	1965	1763	1491
55°	1818	1598	1336
60°	1665	1427	1197
65°	1466	1251	1060
70°	1207	1095	900
75°	961	838	880
80°	645	604	564
85°	401	482	562

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2123 cd/sqm



TEST NUMBER: P559797

CATALOG NUMBER: FSR-12-2-LD4-1LO-35-UNV-80-86-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	4.7
10°-20°	143.7	13.0
20°-30°	198.9	18.0
30°-40°	212.1	19.2
40°-50°	193.5	17.5
50°-60°	151.6	13.7
60°-70°	98.8	8.9
70°-80°	43.8	4.0
80°-90°	9.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	394.9	35.8
0°-40°	607.0	55.0
0°-60°	952.0	86.2
0°-90°	1104.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1104.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	562	562	562	562	562	
5°	553	552	552	551	551	52
15°	517	517	512	506	504	145
25°	448	445	438	423	411	206
35°	363	361	343	317	310	227
45°	279	273	250	229	220	215
55°	194	188	170	150	142	174
65°	115	109	98	100	83	113
75°	46	43	40	38	42	49
85°	6	7	8	8	9	9
90°	0	0	0	0	0	



TEST NUMBER: P559797

CATALOG NUMBER: FSR-12-2-LD4-1LO-35-UNV-80-86-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	562.4	562.4	562.4	562.4	562.4
2.5°	558.5	558.5	558.5	557.8	557.8
5°	552.6	552.0	552.0	551.3	551.3
7.5°	548.1	547.4	546.8	546.1	544.8
10°	541.6	541.6	540.9	537.7	537.0
12.5°	531.2	530.5	527.9	523.4	522.1
15°	516.9	516.9	511.7	506.5	504.5
17.5°	501.3	500.6	494.1	488.9	486.3
20°	484.3	483.0	476.5	468.1	463.5
22.5°	465.5	465.5	457.7	446.6	442.1
25°	447.9	445.3	438.2	422.6	410.9
27.5°	427.8	423.9	416.1	394.0	380.3
30°	405.7	403.7	392.7	364.1	353.7
32.5°	384.9	381.6	369.9	340.0	331.6
35°	363.4	360.8	343.3	317.3	309.5
37.5°	342.0	338.7	316.6	295.8	286.1
40°	320.5	316.6	292.6	273.7	263.3
42.5°	300.4	295.2	271.8	251.6	239.9
45°	278.9	273.1	249.7	228.8	219.7
47.5°	257.5	252.3	230.8	209.3	198.9
50°	234.7	230.1	210.6	189.2	178.1
52.5°	215.8	208.7	189.8	168.4	159.3
55°	193.7	187.9	170.3	150.2	142.4
57.5°	173.6	167.7	151.5	132.6	126.1
60°	154.7	146.3	132.6	116.4	111.2
62.5°	133.9	127.4	115.7	102.1	108.6
65°	115.1	108.6	98.2	100.1	83.2
67.5°	94.3	91.0	81.9	72.8	70.2
70°	76.7	72.8	69.6	59.8	57.2
72.5°	61.1	57.2	52.7	47.5	45.5
75°	46.2	42.9	40.3	38.4	42.3
77.5°	31.9	30.6	28.6	26.7	26.0
80°	20.8	20.2	19.5	18.9	18.2
82.5°	12.4	12.4	12.4	12.4	12.4
85°	6.5	7.2	7.8	8.5	9.1
87.5°	3.9	3.9	4.6	5.2	5.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)