

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P560184

Luminaire Tested: FSR-12-2-LD4-2HI-35-UNV-80-88-EDD-90

Issue Date: 7/20/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P560184  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/20/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: FAIL-SAFE  
Catalog Number: FSR-12-2-LD4-2HI-35-UNV-80-88-EDD-90  
Description: 1X2 FSR TROFFER WITH .125 PRISMATIC ACRYLIC FIXTURE SIDE AND .500 CLEAR PC ENVIRON  
SIDE LENSES WITH, 90 CRI AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2644.0 lumens  
Efficiency: N/A  
Efficacy: 61.2 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15  
Luminous Opening: Rectangular (W 1' x L: 2' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 43.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P560184

CATALOG NUMBER: FSR-12-2-LD4-2HI-35-UNV-80-88-EDD-90

### Luminous Intensity Polar Plot





TEST NUMBER: P560184

CATALOG NUMBER: FSR-12-2-LD4-2HI-35-UNV-80-88-EDD-90

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7248	7248	7248
5°	7150	7142	7133
10°	7088	7079	7029
15°	6897	6828	6732
20°	6644	6537	6359
25°	6371	6232	5843
30°	6038	5844	5264
35°	5719	5401	4869
40°	5393	4923	4430
45°	5084	4551	4006
50°	4706	4224	3572
55°	4354	3827	3200
60°	3989	3419	2865
65°	3510	2994	2538
70°	2891	2622	2156
75°	2298	2007	2104
80°	1543	1447	1351
85°	963	1155	1346

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5084 cd/sqm



TEST NUMBER: P560184

CATALOG NUMBER: FSR-12-2-LD4-2HI-35-UNV-80-88-EDD-90

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	125.4	4.7
10°-20°	344.1	13.0
20°-30°	476.3	18.0
30°-40°	507.9	19.2
40°-50°	463.4	17.5
50°-60°	363.0	13.7
60°-70°	236.6	8.9
70°-80°	104.8	4.0
80°-90°	22.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	945.8	35.8
0°-40°	1453.7	55.0
0°-60°	2280.1	86.2
0°-90°	2644.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2644.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1347	1347	1347	1347	1347	
5°	1324	1322	1322	1320	1320	126
15°	1238	1238	1225	1213	1208	348
25°	1073	1067	1049	1012	984	493
35°	870	864	822	760	741	544
45°	668	654	598	548	526	515
55°	464	450	408	360	341	416
65°	276	260	235	240	199	272
75°	110	103	96	92	101	118
85°	16	17	19	20	22	22
90°	0	0	0	0	0	



TEST NUMBER: P560184

CATALOG NUMBER: FSR-12-2-LD4-2HI-35-UNV-80-88-EDD-90

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1346.8	1346.8	1346.8	1346.8	1346.8
2.5°	1337.5	1337.5	1337.5	1335.9	1335.9
5°	1323.5	1321.9	1321.9	1320.3	1320.3
7.5°	1312.6	1311.0	1309.4	1307.9	1304.8
10°	1297.0	1297.0	1295.4	1287.7	1286.1
12.5°	1272.1	1270.5	1264.3	1253.4	1250.3
15°	1237.8	1237.8	1225.4	1212.9	1208.2
17.5°	1200.5	1198.9	1183.3	1170.9	1164.6
20°	1160.0	1156.9	1141.3	1121.1	1110.2
22.5°	1114.8	1114.8	1096.1	1069.7	1058.8
25°	1072.8	1066.6	1049.4	1012.1	984.0
27.5°	1024.5	1015.2	996.5	943.6	910.9
30°	971.6	966.9	940.4	871.9	847.0
32.5°	921.8	914.0	885.9	814.3	794.1
35°	870.4	864.1	822.1	759.8	741.1
37.5°	819.0	811.2	758.3	708.4	685.1
40°	767.6	758.3	700.7	655.5	630.6
42.5°	719.3	706.9	650.8	602.6	574.5
45°	668.0	653.9	597.9	548.1	526.3
47.5°	616.6	604.1	552.7	501.4	476.4
50°	562.1	551.2	504.5	453.1	426.6
52.5°	516.9	499.8	454.6	403.3	381.5
55°	464.0	450.0	407.9	359.7	341.0
57.5°	415.7	401.7	362.8	317.6	302.1
60°	370.6	350.3	317.6	278.7	266.2
62.5°	320.7	305.2	277.1	244.5	260.0
65°	275.6	260.0	235.1	239.8	199.3
67.5°	225.8	218.0	196.2	174.4	168.2
70°	183.7	174.4	166.6	143.2	137.0
72.5°	146.4	137.0	126.1	113.7	109.0
75°	110.5	102.8	96.5	91.9	101.2
77.5°	76.3	73.2	68.5	63.8	62.3
80°	49.8	48.3	46.7	45.2	43.6
82.5°	29.6	29.6	29.6	29.6	29.6
85°	15.6	17.1	18.7	20.2	21.8
87.5°	9.3	9.3	10.9	12.5	14.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)