

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P560662

Luminaire Tested: FSR-12-2-LD4-2STD-40-UNV-82-87-EDD-90

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-2019
Report Number: P560662
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FSR-12-2-LD4-2STD-40-UNV-82-87-EDD-90
Description: 1X2 FSR TROFFER WITH .187 CLEAR PC FIXTURE SIDE AND .375 CLEAR PC ENVIRONMENTAL SI
LENSES WITH, 90 CRI AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2258.0 lumens
Efficiency: N/A
Efficacy: 67.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 2' x H: 0')
CIE Type: Direct


Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P560662

CATALOG NUMBER: FSR-12-2-LD4-2STD-40-UNV-82-87-EDD-90

Luminous Intensity Polar Plot





TEST NUMBER: P560662

CATALOG NUMBER: FSR-12-2-LD4-2STD-40-UNV-82-87-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87					87			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75					75			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65					65			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56					56			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50					50			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44					44			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40					40			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36					36			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33					33			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30					30			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6190	6190	6190
5°	6106	6099	6092
10°	6053	6046	6002
15°	5890	5831	5750
20°	5674	5582	5430
25°	5441	5322	4991
30°	5156	4991	4496
35°	4884	4613	4158
40°	4605	4204	3783
45°	4341	3886	3420
50°	4019	3607	3050
55°	3719	3269	2732
60°	3407	2920	2448
65°	2998	2557	2167
70°	2469	2239	1841
75°	1963	1713	1797
80°	1320	1237	1153
85°	821	988	1149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4341 cd/sqm

TEST NUMBER: P560662

CATALOG NUMBER: FSR-12-2-LD4-2STD-40-UNV-82-87-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.1	4.7
10°-20°	293.8	13.0
20°-30°	406.8	18.0
30°-40°	433.8	19.2
40°-50°	395.7	17.5
50°-60°	310.0	13.7
60°-70°	202.1	8.9
70°-80°	89.5	4.0
80°-90°	19.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	807.7	35.8
0°-40°	1241.5	55.0
0°-60°	1947.2	86.2
0°-90°	2258.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2258.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1150	1150	1150	1150	1150	
5°	1130	1129	1129	1128	1128	107
15°	1057	1057	1046	1036	1032	297
25°	916	911	896	864	840	421
35°	743	738	702	649	633	465
45°	570	558	511	468	449	439
55°	396	384	348	307	291	355
65°	235	222	201	205	170	232
75°	94	88	82	78	86	101
85°	13	15	16	17	19	18
90°	0	0	0	0	0	



TEST NUMBER: P560662

CATALOG NUMBER: FSR-12-2-LD4-2STD-40-UNV-82-87-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1150.2	1150.2	1150.2	1150.2	1150.2
2.5°	1142.2	1142.2	1142.2	1140.9	1140.9
5°	1130.2	1128.9	1128.9	1127.6	1127.6
7.5°	1120.9	1119.6	1118.3	1117.0	1114.3
10°	1107.6	1107.6	1106.3	1099.7	1098.3
12.5°	1086.4	1085.0	1079.7	1070.4	1067.8
15°	1057.1	1057.1	1046.5	1035.8	1031.9
17.5°	1025.2	1023.9	1010.6	999.9	994.6
20°	990.6	988.0	974.7	957.4	948.1
22.5°	952.1	952.1	936.1	913.5	904.2
25°	916.2	910.8	896.2	864.3	840.4
27.5°	874.9	867.0	851.0	805.8	777.9
30°	829.7	825.7	803.1	744.6	723.4
32.5°	787.2	780.5	756.6	695.4	678.1
35°	743.3	738.0	702.1	648.9	632.9
37.5°	699.4	692.8	647.6	605.0	585.1
40°	655.5	647.6	598.4	559.8	538.5
42.5°	614.3	603.7	555.8	514.6	490.7
45°	570.4	558.5	510.6	468.1	449.4
47.5°	526.6	515.9	472.0	428.2	406.9
50°	480.0	470.7	430.8	386.9	364.3
52.5°	441.5	426.8	388.3	344.4	325.8
55°	396.3	384.3	348.4	307.2	291.2
57.5°	355.0	343.1	309.8	271.3	258.0
60°	316.5	299.2	271.3	238.0	227.4
62.5°	273.9	260.6	236.7	208.8	222.1
65°	235.4	222.1	200.8	204.8	170.2
67.5°	192.8	186.2	167.5	148.9	143.6
70°	156.9	148.9	142.3	122.3	117.0
72.5°	125.0	117.0	107.7	97.1	93.1
75°	94.4	87.8	82.4	78.5	86.4
77.5°	65.2	62.5	58.5	54.5	53.2
80°	42.6	41.2	39.9	38.6	37.2
82.5°	25.3	25.3	25.3	25.3	25.3
85°	13.3	14.6	16.0	17.3	18.6
87.5°	8.0	8.0	9.3	10.6	12.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)