

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P560945

Luminaire Tested: FSR-12-4-LD4-1LO-35-UNV-80-84-EDD

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-2019
Report Number: P560945
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FSR-12-4-LD4-1LO-35-UNV-80-84-EDD
Description: 1X4 FSR TROFFER WITH .125 PRISMATIC ACRYLIC FIXTURE SIDE AND .125 CLEAR PC ENVIRONM
SIDE LENSES WITH, 80 CRI AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2480.0 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 23.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P560945
CATALOG NUMBER: FSR-12-4-LD4-1LO-35-UNV-80-84-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P560945

CATALOG NUMBER: FSR-12-4-LD4-1LO-35-UNV-80-84-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3400	3400	3400
5°	3353	3349	3346
10°	3324	3320	3296
15°	3234	3202	3157
20°	3116	3066	2982
25°	2988	2923	2741
30°	2832	2741	2469
35°	2682	2533	2284
40°	2529	2309	2078
45°	2384	2134	1878
50°	2207	1981	1675
55°	2042	1795	1500
60°	1871	1603	1344
65°	1646	1404	1190
70°	1356	1230	1011
75°	1078	941	987
80°	724	679	634
85°	451	540	630

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2384 cd/sqm



TEST NUMBER: P560945

CATALOG NUMBER: FSR-12-4-LD4-1LO-35-UNV-80-84-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.6	4.7
10°-20°	322.7	13.0
20°-30°	446.8	18.0
30°-40°	476.4	19.2
40°-50°	434.6	17.5
50°-60°	340.5	13.7
60°-70°	221.9	8.9
70°-80°	98.3	4.0
80°-90°	21.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	887.1	35.8
0°-40°	1363.5	55.0
0°-60°	2138.6	86.2
0°-90°	2480.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2480.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1263	1263	1263	1263	1263	
5°	1241	1240	1240	1238	1238	118
15°	1161	1161	1149	1138	1133	326
25°	1006	1000	984	949	923	462
35°	816	810	771	713	695	510
45°	626	613	561	514	494	483
55°	435	422	383	337	320	390
65°	258	244	220	225	187	255
75°	104	96	90	86	95	111
85°	15	16	18	19	20	20
90°	0	0	0	0	0	



TEST NUMBER: P560945

CATALOG NUMBER: FSR-12-4-LD4-1LO-35-UNV-80-84-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1263.3	1263.3	1263.3	1263.3	1263.3
2.5°	1254.5	1254.5	1254.5	1253.1	1253.1
5°	1241.4	1239.9	1239.9	1238.5	1238.5
7.5°	1231.1	1229.7	1228.2	1226.8	1223.8
10°	1216.5	1216.5	1215.1	1207.8	1206.3
12.5°	1193.2	1191.7	1185.9	1175.7	1172.7
15°	1161.0	1161.0	1149.4	1137.7	1133.3
17.5°	1126.0	1124.5	1109.9	1098.2	1092.4
20°	1088.0	1085.1	1070.5	1051.5	1041.3
22.5°	1045.7	1045.7	1028.1	1003.3	993.1
25°	1006.2	1000.4	984.3	949.3	923.0
27.5°	961.0	952.2	934.7	885.0	854.4
30°	911.3	906.9	882.1	817.8	794.5
32.5°	864.6	857.3	831.0	763.8	744.8
35°	816.4	810.5	771.1	712.7	695.2
37.5°	768.2	760.9	711.2	664.5	642.6
40°	720.0	711.2	657.2	614.8	591.5
42.5°	674.7	663.0	610.5	565.2	538.9
45°	626.5	613.4	560.8	514.1	493.6
47.5°	578.3	566.6	518.5	470.3	446.9
50°	527.2	517.0	473.2	425.0	400.2
52.5°	484.9	468.8	426.4	378.3	357.8
55°	435.2	422.1	382.6	337.4	319.8
57.5°	389.9	376.8	340.3	297.9	283.3
60°	347.6	328.6	297.9	261.4	249.7
62.5°	300.9	286.2	260.0	229.3	243.9
65°	258.5	243.9	220.5	224.9	186.9
67.5°	211.8	204.5	184.0	163.6	157.7
70°	172.3	163.6	156.3	134.4	128.5
72.5°	137.3	128.5	118.3	106.6	102.2
75°	103.7	96.4	90.5	86.2	94.9
77.5°	71.6	68.6	64.3	59.9	58.4
80°	46.7	45.3	43.8	42.4	40.9
82.5°	27.7	27.7	27.7	27.7	27.7
85°	14.6	16.1	17.5	19.0	20.4
87.5°	8.8	8.8	10.2	11.7	13.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)