

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P561160

Luminaire Tested: FSR-12-4-LD4-1STD-35-UNV-81-88-EDD-90

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-2019
Report Number: P561160
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FSR-12-4-LD4-1STD-35-UNV-81-88-EDD-90
Description: 1X4 FSR TROFFER WITH .156 CLEAR PC FIXTURE SIDE AND .500 CLEAR PC ENVIRONMENTAL SI
LENSES WITH, 90 CRI AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2229.0 lumens
Efficiency: N/A
Efficacy: 66.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561160

CATALOG NUMBER: FSR-12-4-LD4-1STD-35-UNV-81-88-EDD-90

Luminous Intensity Polar Plot





TEST NUMBER: P561160

CATALOG NUMBER: FSR-12-4-LD4-1STD-35-UNV-81-88-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3055	3055	3055
5°	3014	3010	3007
10°	2988	2984	2963
15°	2907	2878	2838
20°	2800	2755	2680
25°	2685	2627	2463
30°	2545	2463	2219
35°	2411	2277	2053
40°	2273	2075	1867
45°	2143	1918	1689
50°	1984	1780	1506
55°	1835	1613	1349
60°	1681	1441	1208
65°	1479	1262	1070
70°	1219	1105	909
75°	969	846	887
80°	651	611	570
85°	404	488	568

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2143 cd/sqm



TEST NUMBER: P561160

CATALOG NUMBER: FSR-12-4-LD4-1STD-35-UNV-81-88-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.7	4.7
10°-20°	290.1	13.0
20°-30°	401.6	18.0
30°-40°	428.2	19.2
40°-50°	390.6	17.5
50°-60°	306.0	13.7
60°-70°	199.5	8.9
70°-80°	88.4	4.0
80°-90°	19.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	797.3	35.8
0°-40°	1225.5	55.0
0°-60°	1922.2	86.2
0°-90°	2229.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2229.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1135	1135	1135	1135	1135	
5°	1116	1114	1114	1113	1113	106
15°	1044	1044	1033	1022	1019	293
25°	904	899	885	853	830	415
35°	734	728	693	641	625	459
45°	563	551	504	462	444	434
55°	391	379	344	303	288	351
65°	232	219	198	202	168	229
75°	93	87	81	77	85	100
85°	13	14	16	17	18	18
90°	0	0	0	0	0	



TEST NUMBER: P561160

CATALOG NUMBER: FSR-12-4-LD4-1STD-35-UNV-81-88-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1135.4	1135.4	1135.4	1135.4	1135.4
2.5°	1127.5	1127.5	1127.5	1126.2	1126.2
5°	1115.7	1114.4	1114.4	1113.1	1113.1
7.5°	1106.5	1105.2	1103.9	1102.6	1100.0
10°	1093.4	1093.4	1092.1	1085.5	1084.2
12.5°	1072.4	1071.1	1065.9	1056.7	1054.0
15°	1043.5	1043.5	1033.0	1022.5	1018.6
17.5°	1012.0	1010.7	997.6	987.1	981.8
20°	977.9	975.3	962.2	945.1	935.9
22.5°	939.8	939.8	924.1	901.8	892.6
25°	904.4	899.1	884.7	853.2	829.6
27.5°	863.7	855.8	840.1	795.5	767.9
30°	819.1	815.1	792.8	735.1	714.1
32.5°	777.1	770.5	746.9	686.5	669.4
35°	733.8	728.5	693.1	640.6	624.8
37.5°	690.4	683.9	639.2	597.2	577.6
40°	647.1	639.2	590.7	552.6	531.6
42.5°	606.4	595.9	548.7	508.0	484.4
45°	563.1	551.3	504.0	462.0	443.7
47.5°	519.8	509.3	466.0	422.7	401.7
50°	473.9	464.7	425.3	382.0	359.7
52.5°	435.8	421.4	383.3	340.0	321.6
55°	391.2	379.3	343.9	303.2	287.5
57.5°	350.5	338.7	305.8	267.8	254.6
60°	312.4	295.3	267.8	235.0	224.5
62.5°	270.4	257.3	233.6	206.1	219.2
65°	232.3	219.2	198.2	202.1	168.0
67.5°	190.3	183.8	165.4	147.0	141.8
70°	154.9	147.0	140.5	120.8	115.5
72.5°	123.4	115.5	106.3	95.8	91.9
75°	93.2	86.6	81.4	77.4	85.3
77.5°	64.3	61.7	57.8	53.8	52.5
80°	42.0	40.7	39.4	38.1	36.8
82.5°	24.9	24.9	24.9	24.9	24.9
85°	13.1	14.4	15.8	17.1	18.4
87.5°	7.9	7.9	9.2	10.5	11.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)