

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P561299

Luminaire Tested: FSR-12-4-LD4-1STD-50-UNV-82-85-EDD

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-2019
Report Number: P561299
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FSR-12-4-LD4-1STD-50-UNV-82-85-EDD
Description: 1X4 FSR TROFFER WITH .187 CLEAR PC FIXTURE SIDE AND .187 CLEAR PC ENVIRONMENTAL SI
LENSES WITH, 80 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3110.0 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561299

CATALOG NUMBER: FSR-12-4-LD4-1STD-50-UNV-82-85-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P561299

CATALOG NUMBER: FSR-12-4-LD4-1STD-50-UNV-82-85-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89					87				
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77					75				
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67					65				
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58					56				
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52					50				
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46					44				
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42					40				
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38					36				
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34					33				
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32					30				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4263	4263	4263
5°	4205	4200	4195
10°	4169	4164	4134
15°	4056	4015	3959
20°	3907	3844	3739
25°	3747	3665	3437
30°	3551	3437	3096
35°	3363	3177	2864
40°	3172	2895	2605
45°	2990	2676	2356
50°	2768	2484	2101
55°	2561	2251	1882
60°	2346	2011	1686
65°	2064	1761	1493
70°	1700	1542	1268
75°	1352	1180	1237
80°	908	851	795
85°	565	679	790

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2990 cd/sqm



TEST NUMBER: P561299

CATALOG NUMBER: FSR-12-4-LD4-1STD-50-UNV-82-85-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.5	4.7
10°-20°	404.7	13.0
20°-30°	560.3	18.0
30°-40°	597.4	19.2
40°-50°	545.0	17.5
50°-60°	427.0	13.7
60°-70°	278.3	8.9
70°-80°	123.3	4.0
80°-90°	26.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1112.5	35.8
0°-40°	1709.9	55.0
0°-60°	2681.9	86.2
0°-90°	3110.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3110.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1584	1584	1584	1584	1584	
5°	1557	1555	1555	1553	1553	148
15°	1456	1456	1441	1427	1421	409
25°	1262	1254	1234	1190	1158	579
35°	1024	1016	967	894	872	640
45°	786	769	703	645	619	605
55°	546	529	480	423	401	490
65°	324	306	276	282	234	319
75°	130	121	114	108	119	139
85°	18	20	22	24	26	25
90°	0	0	0	0	0	



TEST NUMBER: P561299

CATALOG NUMBER: FSR-12-4-LD4-1STD-50-UNV-82-85-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1584.2	1584.2	1584.2	1584.2	1584.2
2.5°	1573.2	1573.2	1573.2	1571.4	1571.4
5°	1556.7	1554.9	1554.9	1553.1	1553.1
7.5°	1543.9	1542.1	1540.2	1538.4	1534.7
10°	1525.6	1525.6	1523.8	1514.6	1512.8
12.5°	1496.3	1494.5	1487.1	1474.3	1470.6
15°	1456.0	1456.0	1441.3	1426.7	1421.2
17.5°	1412.0	1410.2	1391.9	1377.2	1369.9
20°	1364.4	1360.8	1342.4	1318.6	1305.8
22.5°	1311.3	1311.3	1289.3	1258.2	1245.4
25°	1261.9	1254.5	1234.4	1190.4	1157.5
27.5°	1205.1	1194.1	1172.1	1109.9	1071.4
30°	1142.8	1137.3	1106.2	1025.6	996.3
32.5°	1084.2	1075.1	1042.1	957.8	934.0
35°	1023.8	1016.4	967.0	893.7	871.8
37.5°	963.3	954.2	891.9	833.3	805.8
40°	902.9	891.9	824.1	771.0	741.7
42.5°	846.1	831.5	765.5	708.8	675.8
45°	785.7	769.2	703.3	644.7	619.0
47.5°	725.2	710.6	650.2	589.7	560.4
50°	661.1	648.3	593.4	532.9	501.8
52.5°	608.0	587.9	534.8	474.3	448.7
55°	545.8	529.3	479.8	423.1	401.1
57.5°	489.0	472.5	426.7	373.6	355.3
60°	435.9	412.1	373.6	327.8	313.2
62.5°	377.3	359.0	326.0	287.5	305.8
65°	324.2	305.8	276.5	282.0	234.4
67.5°	265.6	256.4	230.8	205.1	197.8
70°	216.1	205.1	196.0	168.5	161.2
72.5°	172.2	161.2	148.3	133.7	128.2
75°	130.0	120.9	113.5	108.1	119.0
77.5°	89.7	86.1	80.6	75.1	73.3
80°	58.6	56.8	54.9	53.1	51.3
82.5°	34.8	34.8	34.8	34.8	34.8
85°	18.3	20.1	22.0	23.8	25.6
87.5°	11.0	11.0	12.8	14.7	16.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)