

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P562441

Luminaire Tested: FSR-24-4-LD4-1STD-50-UNV-81-88-EDD

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-2019
Report Number: P562441
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FSR-24-4-LD4-1STD-50-UNV-81-88-EDD
Description: 2X4 FSR TROFFER WITH .156 CLEAR PC FIXTURE SIDE AND .500 CLEAR PC ENVIRONMENTAL SI
LENSES WITH, 80 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3215.0 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562441

CATALOG NUMBER: FSR-24-4-LD4-1STD-50-UNV-81-88-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P562441

CATALOG NUMBER: FSR-24-4-LD4-1STD-50-UNV-81-88-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87					87			
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75					75			
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65					65			
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56					56			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50					50			
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44					44			
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40					40			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36					36			
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33					33			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30					30			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2204	2204	2204
5°	2174	2171	2168
10°	2155	2152	2137
15°	2097	2076	2047
20°	2020	1987	1933
25°	1937	1894	1776
30°	1835	1777	1600
35°	1738	1642	1480
40°	1639	1496	1347
45°	1545	1383	1218
50°	1431	1284	1086
55°	1323	1164	973
60°	1213	1039	871
65°	1067	910	771
70°	879	797	655
75°	699	610	640
80°	470	440	411
85°	292	350	409

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1545 cd/sqm



TEST NUMBER: P562441

CATALOG NUMBER: FSR-24-4-LD4-1STD-50-UNV-81-88-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.4	4.7
10°-20°	418.4	13.0
20°-30°	579.2	18.0
30°-40°	617.6	19.2
40°-50°	563.4	17.5
50°-60°	441.4	13.7
60°-70°	287.7	8.9
70°-80°	127.5	4.0
80°-90°	27.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1150.0	35.8
0°-40°	1767.6	55.0
0°-60°	2772.5	86.2
0°-90°	3215.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3215.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1638	1638	1638	1638	1638	
5°	1609	1607	1607	1606	1606	153
15°	1505	1505	1490	1475	1469	423
25°	1304	1297	1276	1231	1196	599
35°	1058	1051	1000	924	901	662
45°	812	795	727	666	640	626
55°	564	547	496	437	415	506
65°	335	316	286	292	242	330
75°	134	125	117	112	123	144
85°	19	21	23	25	26	26
90°	0	0	0	0	0	



TEST NUMBER: P562441

CATALOG NUMBER: FSR-24-4-LD4-1STD-50-UNV-81-88-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1626.3	1626.3	1626.3	1624.4	1624.4
5°	1609.3	1607.4	1607.4	1605.5	1605.5
7.5°	1596.0	1594.1	1592.2	1590.3	1586.6
10°	1577.1	1577.1	1575.2	1565.7	1563.8
12.5°	1546.8	1544.9	1537.3	1524.1	1520.3
15°	1505.1	1505.1	1490.0	1474.9	1469.2
17.5°	1459.7	1457.8	1438.9	1423.7	1416.2
20°	1410.5	1406.7	1387.8	1363.2	1349.9
22.5°	1355.6	1355.6	1332.9	1300.7	1287.4
25°	1304.5	1296.9	1276.1	1230.6	1196.5
27.5°	1245.8	1234.4	1211.7	1147.3	1107.6
30°	1181.4	1175.7	1143.5	1060.2	1029.9
32.5°	1120.8	1111.3	1077.3	990.2	965.6
35°	1058.3	1050.8	999.6	923.9	901.2
37.5°	995.9	986.4	922.0	861.4	833.0
40°	933.4	922.0	852.0	797.1	766.8
42.5°	874.7	859.5	791.4	732.7	698.6
45°	812.2	795.2	727.0	666.4	639.9
47.5°	749.7	734.6	672.1	609.6	579.3
50°	683.5	670.2	613.4	550.9	518.8
52.5°	628.6	607.7	552.8	490.4	463.9
55°	564.2	547.2	496.0	437.3	414.6
57.5°	505.5	488.5	441.1	386.2	367.3
60°	450.6	426.0	386.2	338.9	323.7
62.5°	390.0	371.1	337.0	297.2	316.2
65°	335.1	316.2	285.9	291.6	242.3
67.5°	274.5	265.1	238.6	212.0	204.5
70°	223.4	212.0	202.6	174.2	166.6
72.5°	178.0	166.6	153.4	138.2	132.5
75°	134.4	125.0	117.4	111.7	123.1
77.5°	92.8	89.0	83.3	77.6	75.7
80°	60.6	58.7	56.8	54.9	53.0
82.5°	36.0	36.0	36.0	36.0	36.0
85°	18.9	20.8	22.7	24.6	26.5
87.5°	11.4	11.4	13.3	15.1	17.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)