

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P562980

Luminaire Tested: FSR-24-4-LD4-2STD-40-UNV-93-86-EDD-90

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-2019
Report Number: P562980
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FSR-24-4-LD4-2STD-40-UNV-93-86-EDD-90
Description: 2X4 FSR TROFFER WITH .156 CLEAR TEMPERED GLASS FIXTURE SIDE AND .250 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6431.0 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562980

CATALOG NUMBER: FSR-24-4-LD4-2STD-40-UNV-93-86-EDD-90

Luminous Intensity Polar Plot





TEST NUMBER: P562980

CATALOG NUMBER: FSR-24-4-LD4-2STD-40-UNV-93-86-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87																												
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75																												
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65																												
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56																												
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																												
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44																												
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40																												
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																												
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33																												
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4408	4408	4408
5°	4348	4343	4338
10°	4310	4305	4274
15°	4194	4152	4094
20°	4040	3975	3866
25°	3874	3789	3553
30°	3672	3554	3201
35°	3477	3284	2961
40°	3279	2993	2694
45°	3091	2767	2436
50°	2862	2568	2172
55°	2647	2327	1946
60°	2425	2079	1743
65°	2134	1821	1543
70°	1758	1594	1311
75°	1398	1221	1280
80°	939	880	821
85°	585	701	818

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3091 cd/sqm



TEST NUMBER: P562980

CATALOG NUMBER: FSR-24-4-LD4-2STD-40-UNV-93-86-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	304.9	4.7
10°-20°	836.9	13.0
20°-30°	1158.6	18.0
30°-40°	1235.4	19.2
40°-50°	1127.1	17.5
50°-60°	883.0	13.7
60°-70°	575.5	8.9
70°-80°	255.0	4.0
80°-90°	54.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2300.4	35.8
0°-40°	3535.8	55.0
0°-60°	5545.8	86.2
0°-90°	6431.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6431.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3276	3276	3276	3276	3276	
5°	3219	3215	3215	3212	3212	306
15°	3011	3011	2980	2950	2939	846
25°	2609	2594	2552	2462	2394	1198
35°	2117	2102	2000	1848	1803	1324
45°	1625	1591	1454	1333	1280	1251
55°	1129	1094	992	875	829	1012
65°	670	632	572	583	485	661
75°	269	250	235	223	246	288
85°	38	42	45	49	53	53
90°	0	0	0	0	0	



TEST NUMBER: P562980

CATALOG NUMBER: FSR-24-4-LD4-2STD-40-UNV-93-86-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3275.9	3275.9	3275.9	3275.9	3275.9
2.5°	3253.1	3253.1	3253.1	3249.4	3249.4
5°	3219.1	3215.3	3215.3	3211.5	3211.5
7.5°	3192.5	3188.8	3185.0	3181.2	3173.6
10°	3154.7	3154.7	3150.9	3132.0	3128.2
12.5°	3094.1	3090.3	3075.1	3048.6	3041.1
15°	3010.8	3010.8	2980.5	2950.2	2938.8
17.5°	2919.9	2916.1	2878.2	2847.9	2832.8
20°	2821.4	2813.8	2776.0	2726.7	2700.2
22.5°	2711.6	2711.6	2666.1	2601.8	2575.2
25°	2609.3	2594.2	2552.5	2461.6	2393.5
27.5°	2491.9	2469.2	2423.8	2295.0	2215.5
30°	2363.2	2351.8	2287.4	2120.8	2060.2
32.5°	2242.0	2223.0	2154.9	1980.7	1931.4
35°	2117.0	2101.9	1999.6	1848.1	1802.7
37.5°	1992.0	1973.1	1844.3	1723.1	1666.3
40°	1867.1	1844.3	1704.2	1594.4	1533.8
42.5°	1749.7	1719.4	1583.0	1465.6	1397.5
45°	1624.7	1590.6	1454.3	1333.1	1280.0
47.5°	1499.7	1469.4	1344.4	1219.5	1158.9
50°	1367.2	1340.6	1227.0	1102.1	1037.7
52.5°	1257.3	1215.7	1105.8	980.9	927.8
55°	1128.6	1094.5	992.2	874.8	829.4
57.5°	1011.2	977.1	882.4	772.6	734.7
60°	901.3	852.1	772.6	677.9	647.6
62.5°	780.1	742.3	674.1	594.6	632.5
65°	670.3	632.5	571.9	583.2	484.8
67.5°	549.1	530.2	477.2	424.2	409.0
70°	446.9	424.2	405.2	348.4	333.3
72.5°	356.0	333.3	306.8	276.5	265.1
75°	268.9	250.0	234.8	223.4	246.2
77.5°	185.6	178.0	166.6	155.3	151.5
80°	121.2	117.4	113.6	109.8	106.0
82.5°	72.0	72.0	72.0	72.0	72.0
85°	37.9	41.7	45.4	49.2	53.0
87.5°	22.7	22.7	26.5	30.3	34.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)