

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P563368

Luminaire Tested: FSR-24-4-LD4-3LO-40-UNV-93-88-EDD-90

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-2019
Report Number: P563368
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FSR-24-4-LD4-3LO-40-UNV-93-88-EDD-90
Description: 2X4 FSR TROFFER WITH .156 CLEAR TEMPERED GLASS FIXTURE SIDE AND .500 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6277.0 lumens
Efficiency: N/A
Efficacy: 89.4 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 70.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563368

CATALOG NUMBER: FSR-24-4-LD4-3LO-40-UNV-93-88-EDD-90

Luminous Intensity Polar Plot





TEST NUMBER: P563368

CATALOG NUMBER: FSR-24-4-LD4-3LO-40-UNV-93-88-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87																												
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75																												
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65																												
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56																												
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																												
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44																												
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40																												
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36																												
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33																												
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4302	4302	4302
5°	4244	4239	4234
10°	4207	4202	4172
15°	4093	4052	3996
20°	3943	3880	3774
25°	3781	3699	3468
30°	3584	3469	3124
35°	3394	3206	2890
40°	3201	2922	2630
45°	3017	2701	2377
50°	2793	2507	2120
55°	2584	2272	1899
60°	2368	2029	1701
65°	2083	1777	1506
70°	1716	1556	1280
75°	1364	1192	1249
80°	917	859	802
85°	571	685	800

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3017 cd/sqm



TEST NUMBER: P563368

CATALOG NUMBER: FSR-24-4-LD4-3LO-40-UNV-93-88-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	297.6	4.7
10°-20°	816.8	13.0
20°-30°	1130.9	18.0
30°-40°	1205.8	19.2
40°-50°	1100.1	17.5
50°-60°	861.8	13.7
60°-70°	561.7	8.9
70°-80°	248.9	4.0
80°-90°	53.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2245.3	35.8
0°-40°	3451.2	55.0
0°-60°	5413.0	86.2
0°-90°	6277.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6277.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3197	3197	3197	3197	3197	
5°	3142	3138	3138	3135	3135	298
15°	2939	2939	2909	2880	2868	826
25°	2547	2532	2491	2403	2336	1169
35°	2066	2052	1952	1804	1760	1292
45°	1586	1552	1419	1301	1249	1222
55°	1102	1068	968	854	810	988
65°	654	617	558	569	473	645
75°	262	244	229	218	240	281
85°	37	41	44	48	52	51
90°	0	0	0	0	0	



TEST NUMBER: P563368

CATALOG NUMBER: FSR-24-4-LD4-3LO-40-UNV-93-88-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3197.4	3197.4	3197.4	3197.4	3197.4
2.5°	3175.2	3175.2	3175.2	3171.5	3171.5
5°	3142.0	3138.3	3138.3	3134.6	3134.6
7.5°	3116.1	3112.4	3108.7	3105.0	3097.6
10°	3079.1	3079.1	3075.4	3057.0	3053.3
12.5°	3020.0	3016.3	3001.5	2975.6	2968.2
15°	2938.7	2938.7	2909.1	2879.5	2868.4
17.5°	2850.0	2846.3	2809.3	2779.7	2764.9
20°	2753.8	2746.5	2709.5	2661.4	2635.6
22.5°	2646.7	2646.7	2602.3	2539.5	2513.6
25°	2546.8	2532.1	2491.4	2402.7	2336.1
27.5°	2432.3	2410.1	2365.7	2240.0	2162.4
30°	2306.6	2295.5	2232.6	2070.0	2010.9
32.5°	2188.3	2169.8	2103.3	1933.2	1885.2
35°	2066.3	2051.5	1951.7	1803.9	1759.5
37.5°	1944.3	1925.8	1800.2	1681.9	1626.4
40°	1822.3	1800.2	1663.4	1556.2	1497.1
42.5°	1707.8	1678.2	1545.1	1430.5	1364.0
45°	1585.8	1552.5	1419.4	1301.1	1249.4
47.5°	1463.8	1434.2	1312.2	1190.3	1131.1
50°	1334.4	1308.5	1197.6	1075.7	1012.8
52.5°	1227.2	1186.6	1079.4	957.4	905.6
55°	1101.5	1068.3	968.5	853.9	809.5
57.5°	986.9	953.7	861.3	754.1	717.1
60°	879.8	831.7	754.1	661.7	632.1
62.5°	761.5	724.5	658.0	580.3	617.3
65°	654.3	617.3	558.2	569.3	473.1
67.5°	536.0	517.5	465.8	414.0	399.2
70°	436.2	414.0	395.5	340.1	325.3
72.5°	347.5	325.3	299.4	269.8	258.8
75°	262.4	244.0	229.2	218.1	240.3
77.5°	181.1	173.7	162.6	151.6	147.9
80°	118.3	114.6	110.9	107.2	103.5
82.5°	70.2	70.2	70.2	70.2	70.2
85°	37.0	40.7	44.4	48.1	51.8
87.5°	22.2	22.2	25.9	29.6	33.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)