

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P559590

Luminaire Tested: FSR-12-1-LD4-2STD-50-UNV-93-87-EDD-90

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-2019
Report Number: P559590
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FSR-12-1-LD4-2STD-50-UNV-93-87-EDD-90
Description: 1X1 FSR TROFFER WITH .156 CLEAR TEMPERED GLASS FIXTURE SIDE AND .375 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1321.0 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
CIE Type: Direct


Input Watts (W): 16.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P559590

CATALOG NUMBER: FSR-12-1-LD4-2STD-50-UNV-93-87-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P559590

CATALOG NUMBER: FSR-12-1-LD4-2STD-50-UNV-93-87-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	99	108	104	100	97	100	97	94	96	94	91	92	90	89	87		
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75		
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65		
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56		
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50		
6	74	62	53	48	72	61	53	47	59	52	47	57	51	47	56	50	46	44		
7	69	56	48	43	67	56	48	42	54	47	42	53	46	42	51	46	42	40		
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36		
9	61	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	33		
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7243	7243	7243
5°	7144	7137	7128
10°	7083	7074	7024
15°	6891	6822	6727
20°	6638	6531	6354
25°	6366	6227	5839
30°	6033	5840	5260
35°	5715	5397	4866
40°	5389	4919	4428
45°	5080	4547	4002
50°	4702	4220	3569
55°	4350	3825	3198
60°	3985	3416	2863
65°	3507	2993	2537
70°	2889	2618	2156
75°	2296	2005	2104
80°	1543	1444	1351
85°	963	1149	1346

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5080 cd/sqm

TEST NUMBER: P559590

CATALOG NUMBER: FSR-12-1-LD4-2STD-50-UNV-93-87-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.6	4.7
10°-20°	171.9	13.0
20°-30°	238.0	18.0
30°-40°	253.8	19.2
40°-50°	231.5	17.5
50°-60°	181.4	13.7
60°-70°	118.2	8.9
70°-80°	52.4	4.0
80°-90°	11.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	472.5	35.8
0°-40°	726.3	55.0
0°-60°	1139.2	86.2
0°-90°	1321.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1321.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	673	673	673	673	673	
5°	661	660	660	660	660	63
15°	618	618	612	606	604	174
25°	536	533	524	506	492	246
35°	435	432	411	380	370	272
45°	334	327	299	274	263	257
55°	232	225	204	180	170	208
65°	138	130	118	120	100	136
75°	55	51	48	46	51	59
85°	8	9	9	10	11	11
90°	0	0	0	0	0	

TEST NUMBER: P559590

CATALOG NUMBER: FSR-12-1-LD4-2STD-50-UNV-93-87-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	672.9	672.9	672.9	672.9	672.9
2.5°	668.2	668.2	668.2	667.5	667.5
5°	661.2	660.5	660.5	659.7	659.7
7.5°	655.8	655.0	654.2	653.5	651.9
10°	648.0	648.0	647.2	643.3	642.6
12.5°	635.6	634.8	631.7	626.2	624.7
15°	618.4	618.4	612.2	606.0	603.7
17.5°	599.8	599.0	591.2	585.0	581.9
20°	579.5	578.0	570.2	560.1	554.7
22.5°	557.0	557.0	547.7	534.4	529.0
25°	536.0	532.9	524.3	505.6	491.6
27.5°	511.9	507.2	497.9	471.4	455.1
30°	485.4	483.1	469.9	435.6	423.2
32.5°	460.5	456.6	442.6	406.9	396.7
35°	434.9	431.7	410.7	379.6	370.3
37.5°	409.2	405.3	378.8	354.0	342.3
40°	383.5	378.8	350.1	327.5	315.1
42.5°	359.4	353.2	325.2	301.1	287.1
45°	333.7	326.7	298.7	273.8	262.9
47.5°	308.1	301.8	276.2	250.5	238.0
50°	280.8	275.4	252.0	226.4	213.1
52.5°	258.3	249.7	227.2	201.5	190.6
55°	231.8	224.8	203.8	179.7	170.4
57.5°	207.7	200.7	181.3	158.7	150.9
60°	185.1	175.0	158.7	139.2	133.0
62.5°	160.3	152.5	138.5	122.1	129.9
65°	137.7	129.9	117.5	119.8	99.6
67.5°	112.8	108.9	98.0	87.1	84.0
70°	91.8	87.1	83.2	71.6	68.5
72.5°	73.1	68.5	63.0	56.8	54.5
75°	55.2	51.3	48.2	45.9	50.6
77.5°	38.1	36.6	34.2	31.9	31.1
80°	24.9	24.1	23.3	22.6	21.8
82.5°	14.8	14.8	14.8	14.8	14.8
85°	7.8	8.6	9.3	10.1	10.9
87.5°	4.7	4.7	5.4	6.2	7.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)