

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P562166

Luminaire Tested: FSR-24-4-LD4-1LO-40-UNV-80-87-EDD-90

Issue Date: 7/20/2021

Test Information

Test Method: LM-79-2019
Report Number: P562166
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-135-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FSR-24-4-LD4-1LO-40-UNV-80-87-EDD-90
Description: 2X4 FSR TROFFER WITH .125 PRISMATIC ACRYLIC FIXTURE SIDE AND .375 CLEAR PC ENVIRONMENTAL SIDE LENSES WITH, 90 CRI AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2319.0 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1 / 1.15
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 23.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562166

CATALOG NUMBER: FSR-24-4-LD4-1LO-40-UNV-80-87-EDD-90

Luminous Intensity Polar Plot



TEST NUMBER: P562166

CATALOG NUMBER: FSR-24-4-LD4-1LO-40-UNV-80-87-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	108	104	100	97	100	97	94		96	94	91		92
2	101	94	88	83	99	92	87	82	89	84	80		86	82	78		83
3	93	84	77	71	91	82	76	70	79	74	69		77	72	68		74
4	86	75	67	61	84	74	66	61	72	65	60		69	64	59		67
5	80	68	60	54	78	67	59	53	65	58	53		63	57	52		61
6	74	62	53	48	72	61	53	47	59	52	47		57	51	47		56
7	69	56	48	43	67	56	48	42	54	47	42		53	46	42		51
8	65	52	44	38	63	51	44	38	50	43	38		49	42	38		48
9	61	48	40	35	59	47	40	35	46	39	35		45	39	34		44
10	57	44	37	32	56	44	37	32	43	36	32		42	36	32		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1589	1589	1589
5°	1568	1566	1564
10°	1554	1552	1541
15°	1512	1497	1476
20°	1457	1433	1394
25°	1397	1366	1281
30°	1324	1281	1154
35°	1254	1184	1068
40°	1183	1079	971
45°	1115	998	878
50°	1032	926	783
55°	955	839	702
60°	875	750	628
65°	770	656	557
70°	634	575	473
75°	504	440	462
80°	339	318	296
85°	211	253	295

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1115 cd/sqm

TEST NUMBER: P562166

CATALOG NUMBER: FSR-24-4-LD4-1LO-40-UNV-80-87-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.0	4.7
10°-20°	301.8	13.0
20°-30°	417.8	18.0
30°-40°	445.5	19.2
40°-50°	406.4	17.5
50°-60°	318.4	13.7
60°-70°	207.5	8.9
70°-80°	91.9	4.0
80°-90°	19.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	829.5	35.8
0°-40°	1275.0	55.0
0°-60°	1999.8	86.2
0°-90°	2319.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2319.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1181	1181	1181	1181	1181	
5°	1161	1159	1159	1158	1158	110
15°	1086	1086	1075	1064	1060	305
25°	941	936	920	888	863	432
35°	763	758	721	666	650	477
45°	586	574	524	481	462	451
55°	407	395	358	316	299	365
65°	242	228	206	210	175	238
75°	97	90	85	81	89	104
85°	14	15	16	18	19	19
90°	0	0	0	0	0	

TEST NUMBER: P562166

CATALOG NUMBER: FSR-24-4-LD4-1LO-40-UNV-80-87-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1181.3	1181.3	1181.3	1181.3	1181.3
2.5°	1173.1	1173.1	1173.1	1171.7	1171.7
5°	1160.8	1159.4	1159.4	1158.1	1158.1
7.5°	1151.2	1149.9	1148.5	1147.1	1144.4
10°	1137.6	1137.6	1136.2	1129.4	1128.0
12.5°	1115.7	1114.4	1108.9	1099.3	1096.6
15°	1085.7	1085.7	1074.7	1063.8	1059.7
17.5°	1052.9	1051.5	1037.9	1027.0	1021.5
20°	1017.4	1014.7	1001.0	983.3	973.7
22.5°	977.8	977.8	961.4	938.2	928.6
25°	940.9	935.5	920.4	887.7	863.1
27.5°	898.6	890.4	874.0	827.6	798.9
30°	852.2	848.1	824.8	764.8	742.9
32.5°	808.5	801.6	777.0	714.2	696.5
35°	763.4	757.9	721.1	666.4	650.0
37.5°	718.3	711.5	665.1	621.4	600.9
40°	673.3	665.1	614.5	574.9	553.1
42.5°	630.9	620.0	570.8	528.5	503.9
45°	585.9	573.6	524.4	480.7	461.6
47.5°	540.8	529.9	484.8	439.7	417.9
50°	493.0	483.4	442.5	397.4	374.2
52.5°	453.4	438.4	398.8	353.7	334.6
55°	407.0	394.7	357.8	315.5	299.1
57.5°	364.6	352.3	318.2	278.6	264.9
60°	325.0	307.3	278.6	244.4	233.5
62.5°	281.3	267.7	243.1	214.4	228.1
65°	241.7	228.1	206.2	210.3	174.8
67.5°	198.0	191.2	172.1	153.0	147.5
70°	161.1	153.0	146.1	125.6	120.2
72.5°	128.4	120.2	110.6	99.7	95.6
75°	97.0	90.1	84.7	80.6	88.8
77.5°	66.9	64.2	60.1	56.0	54.6
80°	43.7	42.3	41.0	39.6	38.2
82.5°	25.9	25.9	25.9	25.9	25.9
85°	13.7	15.0	16.4	17.8	19.1
87.5°	8.2	8.2	9.6	10.9	12.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)